








VIEW A-A


mat'l. code				surface		tolerance		projection		product family				
				ISO1302 ✓		ISO1101 ISO406				MOD JACK				
ltr ecn nodr date				tolerances unless otherwise				specified		title				
T	ECR	S00022	BC LOH	26JAN.00	angle	0.X±0.3				8 POS HORIZONTAL P.C.B. MOD JACK ASSY				
U	ECR	V10424	LUNOW	12FEB.01		0.XX±0.15								
V	N05-0002	YS	06JAN.01	0.XXX±0.05										
					0°±2'			scale 2.0						
W	N08-0074	SH MMD	30APR.08	dr		JANET	15JUN.98			dwg no				
X	ELX-N-010667	SH MMD	13MAR.12	engr		JANET	15JUN.98			sheet 1 of 3				
					chr	M CHENG	19FEB.01			size				
					appd	M CHENG	19FEB.01			68899				
											A4			
											type Product Customer Drawing			
sheet		revision		X	X	X								
index		sheet		1	2	3								

RECOMMENDED BOARD LAYOUT
VIEWED FROM TOP

KEYED STYLE



LEFT EAR MOUNTING



SECTION D-D

NOTE :

- 1 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 2 THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.60mm MINIMUM THICK CIRCUIT BOARD.
- 3 IF LF P/N PACKAGING MEETS GS-14-920 SPECIFICATION.

mat'l. code				surface		tolerance	projection	product family	
ISO1302				ISO1101		ISO406	mm	MOD JACK	
tolerances unless otherwise specified				angle		0°±2'	scale	title	
T ECR S00022 BC LOH 26JAN.00				0°±2'		0°±2'	2.0	8 POS HORIZONTAL	
U ECR V10424 12FEB.01				0°±2'		0°±2'	2.0	P.C.B. MOD JACK ASSY	
V N05-0002 YS 06JAN.01				0°±2'		0°±2'	2.0	dwg no	
W N08-0074 SH MMD 30APR.08				0°±2'		0°±2'	2.0	sheet 2 of 3	
X ELX-N-010667 SH MMD 13MAR.12				0°±2'		0°±2'	2.0	size	
				0°±2'		0°±2'	2.0	A4	
				0°±2'		0°±2'	2.0	type	
				0°±2'		0°±2'	2.0	Product Customer Drawing	
sheet				revision					
index				sheet					



1 | 2

FCIconnect.com

3 |

4

PRODUCT NO.	DIM. A	DIM. B	STYLE	POSITIONS LOADED	CONTACT PLATING	HOUSING COLOR	MOUNTING EARS	REMARKS
68899-001 -001LF	-	-	UNKEYED	ALL	0.76um /30*u GXT	BLACK	YES	-
-002 -002LF	1.25 /0.050	2.69 /0.106	KEYED	ALL	5u' Au + high performance lubricant	BLACK	YES	-
-003 -003LF	-	-	UNKEYED	2,3,4,5,6,7	5u' Au + high performance lubricant	BLACK	YES	-
-004 -004LF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	BLACK	NO	-
-004RLF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	RED	NO	-
-004GLF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	GREEN	NO	-
-005 -005LF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	GRAY	NO	-
-006 -006LF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	BLACK	YES	-
-007 -007LF	1.25 /0.050	2.69 /0.106	KEYED	ALL	5u' Au + high performance lubricant	BLACK	NO	-
-008 -008LF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	BLACK	LEFT ONLY	-
-009 -009LF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	BLACK	RIGHT ONLY	-
-010 -010LF	-	-	UNKEYED	ALL	1,27um /50*u GXT	BLACK	YES	-
-011 -011LF	-	-	UNKEYED	1,4,5,8	5u' Au + high performance lubricant	BLACK	YES	-
-012 -012LF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	BLACK	NO	-
-013 -013LF	-	-	UNKEYED	ALL	1,27um /50*u GXT	BLACK	NO	-
-014 -014LF	1.25 /0.050	2.69 /0.106	KEYED	ALL	5u' Au + high performance lubricant	BLACK	NO	-
-015 -015LF	1.25 /0.050	2.69 /0.106	KEYED	ALL	1,27um /50*u GXT	BLACK	NO	-

LEAD FREE PRODUCT NO.

mat'l. code		surface ISO1302 ✓		tolerance ISO1101 ISO406		projection 		product family MOD JACK	
l tr ecn nodr		date		tolerances unless otherwise specified		mm		title	
T	ECR S00022	BC LOH	26JAN.00	0.X±0.3		mm		8 POS HORIZONTAL	
U	ECR V10424	UNREVR	12FEB.01	0.XX±0.15		mm		P.C.B. MOD JACK ASSY	
V	N05-0002	YS	06JAN.01	0'±2'		scale 2.0			
W	N08-0074	SH MMD	30APR.08	dr	JANET	15JUN.98	dwg no sheet 3 of 3 size		
X	ELX-N-010667	SH MMD	13MAR.12	engr	JANET	15JUN.98	68899 A4		
				chr	M CHENG	19FEB.01	type Product Customer Drawing		
				appd	M CHENG	19FEB.01			
sheet	revision								
index	sheet								