




HEAT SHRINK TUBING



✓ Active

TE CONNECTIVITY (TE)

RNF-100-1/8-X-SP

Raychem | RNF-100

RNF-100-1/8-X-SP

TE Internal Number: 5070044032

Alias ID: 1193961-4

EU RoHS Compliant

EU ELV Compliant

Wall Type Single

Resistant To Abrasion, Fluids, Mechanical Damage, Strain

Low Outgassing No

Product Source Czech Republic

Packaging Method Spool

DOCUMENTATION

Catalog Pages/Data Sheets

RNF-100 Pages From 9-1773447-9

PDF

English

At-Application-Tooling-For-Raychem-Heat-Shrink-Product-2-1773452-8

PDF

English

Product Specifications

Product Specification

RNF-100 Sleeving

PDF

English

Product Environmental Compliance

Safety Data Sheet

Thermofit Heat-Shrinkable Polymeric Products

PDF

English

Thermofit Heat-Shrinkable Polymeric Products

PDF

Danish

Thermofit Heat-Shrinkable Polymeric Products

PDF

Dutch

Thermofit Heat-Shrinkable Polymeric Products

PDF

English

Thermofit Heat-Shrinkable Polymeric Products

PDF

French

Thermofit Heat-Shrinkable Polymeric Products

PDF

German

Thermofit Heat-Shrinkable Polymeric Products

PDF

Italian

Thermofit Heat-Shrinkable Polymeric Products

PDF

Norwegian

Thermofit Heat-Shrinkable Polymeric Products

PDF

Spanish

Thermofit Heat-Shrinkable Polymeric Products

PDF

Swedish

Thermofit Heat-Shrinkable Polymeric Products

PDF

Spanish

Thermofit Heat-Shrinkable Polymeric Products

PDF

English

Thermofit Heat-Shrinkable Polymeric Products

PDF

English

Instruction Sheets

Instruction Sheet (U.S.)

Global Dimensional Life For RAYCHEM Heat Shrink Tubing Standard Size Products (Customer Distribution)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Wall Type Single

Product Family RNF-100

Electrical Characteristics

Voltage (Max) (kV) .6

Body Features

Shrink Ratio 2:1

Color Clear

Flexibility Flexible

Material Irradiated Modified Polyolefin

Fluid Type Gasoline, Hydraulic Fluid, Lubricating Oil, Water

Dimensions

Expanded Inside Diameter (Min) 3.2 mm [.126 in]

Recovered Wall Thickness (Nominal) .5 mm [.02 in]

Recovered Inside Diameter (Max) 1.6 mm [.063 in]

Recovered Wall Thickness (Tolerance) .2 mm [.008 in]

Usage Conditions

Shrink Temperature (Min) (°C) 95

Resistant To Abrasion, Fluids, Mechanical Damage, Strain

Recovery Temperature (°C) 121

Operating Temperature Range (°C) -55 – 135

Flammability Non-Flame-Retardant

Fluid Resistance Splash Protection

Product Availability

Applicable Region Global

Packaging Features

Packaging Method Spool

Other

Low Outgassing No

Product Source Czech Republic

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
