



P.C.B LAYOUT



N=Number of contacts



Material

Terminal body
(metal housing): Brass(CuZn)
Terminal screw: Steel Zinc plating "-" slot type
Contacts: Brass
Surface of solder tail: Tin plated
Insulator (housing): Thermoplastic (UL94V-0), Green

Electrical

Voltage rating: 300V/AC
Current rating: 20A
Solid wire(AWG): 12-30
Stranded wire(AWG): 12-30
Torque(Lb-In): 3.5
Screw: M3
Wire strip length: 6-7mm
Withstanding Voltage: 1.6KV
Operating temperature: -40°C to +115°C
Soldering temperature: 250°C±10°C/5 Sec
Safety Approval: us

RoHS compliant
 File No.: E349947

Scale	1:1
TOLERANCE	
X.	±0.50
X.X	±0.30
X.XX	±0.10
DIM	TOL
X. °	±1°
X.X°	±X°
Angle	TOL

②	Add the UL File No.	19.04.2016	Winnie
①	Drawn	29.07.2009	Dean
	Modification		
	Date		
	Name		

Drawn	Date	Name
Approved	19.04.2016	Winnie

Customer-No.	
ASSMANN WSW-No.	A-TB508-VJXH
Drawing-No.	ASS 3595 CO
Replace	rev02
Sheet	

1 2 3 4 5 6 7

SVXXXX