




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—		F	ADDED PACKING INFORMATION	27JUN2012	Y.U	T.K

- NOTES:
- 1 CONNECTOR IS DESIGNED FOR FLAT RIBBON CABLE ON 1,27 CENTERS .
FOR CABLE REQUIREMENTS SEE AMP APPLICATION SPECIFICATION 114—19022.
 - 2 THESE RECEPTACLE CONNECTORS MATE WITH 0,64^{±0,05} mm SQUARE OR ROUND POSTS ON 2,54mm GRID.
 - 3 MARK INDICATING FIRST CABLE POSITION REFERRING TO CONTACT POSITION.
 - 4 THERE IS NO POLARIZATION—SLOT AT THIS END IN 6, 10 AND 14 POS CONNECTORS.
 - 5 THESE CONNECTORS CAN BE USED IN CONJUNCTION WITH STRAIN—RELIEF COVERS OF PARTNR: 100103.
 - 6 THERE IS NO POLARIZATION—SLOT AT THIS END IN 6 POS CONNECTORS.
 - 7 PRODUCT SPECIFICATION 108—19033.
 - 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	85,9	64	32	6-215882-4	E
	80,8	60	30	6-215882-0	E
	68,1	50	25	5-215882-0	E
	60,5	44	22	4-215882-4	E
	55,4	40	20	4-215882-0	E
	47,8	34	17	3-215882-4	E
8 OBSOLETE	42,7	30	15	3-215882-0	E
	37,6	26	13	2-215882-6	E
	30,0	20	10	2-215882-0	E
	24,9	16	8	1-215882-6	E
	22,4	14	7	1-215882-4	E
	17,3	10	5	1-215882-0	E
OBSOLETE	14,8	8	4	0-215882-8	C
	12,2	6	3	0-215882-6	E
OBSOLETE	9,7	4	2	0-215882-4	C
	DIM."C"	"B" CABLE POS.	"A" DUAL POS.	PARTNUMBER	PART REV.

3 RECEPTACLE CONTACT	PHOSPHORBRONZE Cu Sn6	AT CONTACT—PLACE: 0,8µm GOLD AT WIRING END: 2,5µm TIN ENTIRE UNDERCOATING: 1,27µm NICKEL
2 COVER	THERMOPLASTIC POLYESTER GF UL 94 -V0	GREY RAL 7032 (ONLY FOR REF.)
1 HOUSING		
COMPONENT NAME	MATERIAL	PLATING / COLOUR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W.R.VERBEET 02FEB1988	TE Connectivity		
		CHK R.VERSTIJNEN 03FEB1988			
		APVD L.V.SOEST 03FEB1988	NAME		
DIMENSIONS: mm		PRODUCT SPEC	AMP—LATCH_MIL—TYPE RECEPTACLE_CONNECTOR ASSEMBLY_(SYMMETRIC_COVER)		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		—	A3	00779	C-215882
MATERIAL SEE TABLE		FINISH SEE TABLE	WEIGHT	RESTRICTED TO	
			—	—	
CUSTOMER DRAWING			SCALE	SHEET	REV
			4:1	1 of 2	F

4

3

2

1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION




COPYRIGHT - By -

ALL RIGHTS RESERVED.


PACKAGING SPECIFICATION



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
J	—	—	—	SEE SHEET 1	—	—




TRAY A COVER




TRAY B COVER

SHOWN AS 1-215882-6



TRAY A BOTTOM


SHOWN AS 4-215882-0



TRAY B BOTTOM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL

-

FINISH

-

DWN
W.R.VERBEET 02FEB1988

CHK
R.VERSTIJNEN 03FEB1988

APVD
L.V.SOEST 03FEB1988

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME
AMP-LATCH_MIL-TYPE
RECEPTACLE_CONNECTOR
ASSEMBLY_(SYMMETRIC_COVER)

SIZE CAGE CODE DRAWING NO RESTRICTED TO
A3 00779 C-215882 -

SCALE SHEET 2 OF 2 REV F