



Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

A FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	SIGNAL								POWER											E2	
		E1	1	2	3	4	5	6	7	8	P1	P2	P3	P4	P5	P6	P7	P8	P9	P10		P11
51939-125LF	D C B A		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	

NOTE: NO CONTACTS ARE LOADED



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
X	OMITTED	OMITTED

mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		A FCI		www.fciconnect.com	
lir	ecn no.	dr	date	linear	linear	linear	linear	projection	projection	title	title	product family	code
A	V04-0651	TAB	06/21/04	linear	.XX±.01/0.X±0.3	.XXX±.005/0.XX±0.13	.XXX±.0020/0.XXX±0.051	0°±2°	0°±2°	32S + 11P	RIGHT ANGLE HEADER	PwrBlade	213
B	DG06-0013	RYAN	01/11/06	linear									
				angles									
				dr	T. BRUNGARD	06/21/04							
				engr	M. GRAY	06/21/04							
				chr	M. GRAY	06/21/04							
				appd	M. GRAY	06/21/04							
sheet index	revision	sheet	sheet	sheet	sheet	sheet	sheet	sheet	sheet	sheet	sheet	sheet	sheet
	B	B	B	B	B	B	B	B	B	B	B	B	B
	1	2	3	4	5	6	7	8	9	10	11	12	13

Pro/E

code code 22526


Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

A FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

A

B



NOTES:



1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

2. HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY
3. MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.
4. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.
5. PACKAGED IN TRAYS.

PRODUCT MEETS EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

THE HOUSING WILL WITHSTAND EXPOSURE TO 260° PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A CIRCUIT BOARD.



mat'l code				tolerances unless otherwise specified		CUSTOMER		A FCI	
lir	ecn no.	dr	date	linear	.XX±.01/0.X±0.3	projection	COPY	title	www.fciconnect.com
B					.XXX±.005/0.XX±0.13			32S + 11P	
				angles	.XXX±.0020/0.XXX±0.051			RIGHT ANGLE HEADER	
				dr	T. BRUNGARD 06/21/04			product family	PwrBlade
				engr	M. GRAY 06/21/04			size	213
				chr	M. GRAY 06/21/04			dwg no	51939-125
				appd	M. GRAY 06/21/04			code	2 of 2
sheet index	revision	sheet							

Pro/E

code code 22526