


DIMENSIONS: mm (in.)**Electrical Specifications:**

- Rating: 50mA/12VDC
- Life: 500,000 cycles
- Contact resistance: 100m Ω max.
- Insulation resistance: 100M Ω min. @ 500VDC
- Dielectric Strength: 250VAC for 1 minute

Mechanical Specifications:

- Type: SPST surface mount, tactile
- Operating force: 160 $\pm$ 50g
- Operating temperature: -25 $^\circ$ ~+70 $^\circ$ C
- Storage temperature: -30 $^\circ$ ~+80 $^\circ$ C
- Travel: .012 $\pm$.004"(.30 $\pm$.10mm)

Materials:

- Cover: tin plated steel
- Contacts: silver clad phosphor bronze
- Terminals: silver clad brass
- Base: nylon, brown
- Stem: nylon, brown

Note:

- RoHS Compliant and are also process compatible with 260 $^\circ$ solder

Tactile Switch (SMT)
101-0124-EV

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-0124-EV](#)