





P	LTR	DESCRIPTION	DATE	DWN	APVD
J		REVISED PER ECO-15-015252	11NOV2015	BJ	FY
J1		REVISED PER ECO-16-003656	10MAR2016	B.J	S.Y



RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.K. SEIFRIED CHK F. KIBLER APVD DAVE HOFFMAN	03/23/90 8-17-92 8-17-92	TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0 PLC ± -		1 PLC ± -		2 PLC ± -	
3 PLC ± 0.13 [.005]		4 PLC ± -		APPLICATION SPEC	
ANGLES ± -		FINISH		SIZE	
MATERIAL		WEIGHT		CAGE CODE	
DRAWING NO		RESTRICTED TO		CUSTOMER DRAWING	
SCALE		SHEET		REV	
4:1		1 of 2		J1	

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

1

HOUSING MATERIAL: THERMOPLASTIC, COLOR—NATURAL.

2

CONTACT MATERIAL: PHOSPHOR BRONZE.

3

FINISH:
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108—9063; BASED ON TELCORDIA DR—1217—CORE APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
TIN—LEAD PLATED POSTS.

4

ACTION PIN POSTS REQUIRE 2.36 [.093] MIN THICK P.C. BOARD. RECOMMENDED P.C. BOARD HOLES ARE 1.151 [.0453] DIA PLATED THRU WITH 0.025—0.076 [.001—.003] COPPER, WITH 0.0076 [.0003] MIN TIN—LEAD PLATING; FINISHED HOLE AFTER PLATING 0.94—1.09 [.037—.043] DIA.

5.

DIMENSIONS IN BRACKETS ARE IN INCHES.

6

PART NUMBER IS OBSOLETE.

6

—

—

—

—

—

—

1—532429—9

6

—

—

—

—

—

—

1—532429—8

6

—

—

—

—

—

—

1—532429—7

6

—

—

—

—

—

—

1—532429—6

6

—

—

—

—

—

—

1—532429—5

6

187.96
[7.400]

74

191.77
[7.550]

201.93
[7.950]

209.55
[8.250]

150

1—532429—4

6

175.26
[6.900]

69

179.07
[7.050]

189.23
[7.450]

196.85
[7.750]

140

1—532429—3

6

—

—

—

—

—

—

1—532429—2

6

—

—

—

—

—

—

1—532429—1

6

—

—

—

—

—

—

1—532429—0

6

—

—

—

—

—

—

532429—9

6

—

—

—

—

—

—

532429—8

6

—

—

—

—

—

—

532429—7

6

86.36
[3.400]

34

90.17
[3.550]

100.33
[3.950]

107.95
[4.250]

70

532429—6

6

73.66
[2.900]

29

77.47
[3.050]

87.63
[3.450]

95.25
[3.750]

60

532429—5

6

—

—

—

—

—

—

532429—4

6

—

—

—

—

—

—

532429—3

6

—

—

—

—

—

—

532429—2

6

—

—

—

—

—

—

532429—1

E

D

C

B

A

POSN

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC

± —
± —
± —
± 0.13 [.005]
± — ± —

ANGLES

FINISH

DWN
R. K. SEIFRIED
8—17—92

CHK
F. KIBLER
8—17—92

APVD
DAVE HOFFMAN
8—17—92

PRODUCT SPEC

APPLICATION SPEC

—

SIZE
A1

CAGE CODE
00779

DRAWING NO
532429

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
4:1

SHEET
2

OF
2

REV
J1

TE Connectivity

HDI, 2 ROW, PIN ASSEMBLY,
18.62 [.733] LONG ACTION PINS

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

—

—

SEE SHEET 1

—

—

—

4805 (1/15)