






DO NOT SCALE
DIMENSIONS IN mm

METRIC


THIRD ANGLE
PROJECTION



COLOR CODE: BLUE



SECTION A-A



SECTION B-B

WIRE RANGE : 0,75-1,50 mm² (18-16 AWG)
INSUL. RANGE : 2,0 -2,5 mm (.080-.100)

OBSOLETE 6	5-163081-3	5	1	BRASS	ECON. GOLD	21
	5-163081-2	1	5	BRASS	SEL. GOLD	22
	5-163081-1	1	5	BRASS	EL. TIN	20
OBSOLETE 6	1-163081-8	1	8	BRASS	TIN/LEAD	30
	1-163081-7	1	7	BRASS	SILVER	28
	1-163081-6	1	6	BRASS	SILVER	28
OBSOLETE 6	1-163081-5	1	5	PH. BRONZE	PRE-TIN	
	1-163081-4	1	4	PH. BRONZE	PRE-TIN	
	1-163081-3	1	3	BRASS	PRE-TIN	
	1-163081-2	1	2	BRASS	PRE-TIN	
	1-163081-1	1	1	BRASS	ECON. GOLD	21
	1-163081-0	1	0	BRASS	ECON. GOLD	21
	163081-9	1	9	BRASS	EL. TIN	31 20
	163081-8	1	8	BRASS	EL. TIN	20
	163081-7	1	7	BRASS	SEL. GOLD	22
	163081-2	1	2	BRASS	SEL. GOLD	22
	163081-1	1	1	BRASS	EL. TIN	20
PARTNUMBER		DIRECTION OF REEL		LOOSE-PIECE	MATERIAL	PLATING

DIRECTION OFF TOP OF REEL	
AMPOMATOR + MINI-APPL. 107-3-F16.1	A
107-3-F16.2	B
107-3-F16.4	C

NOTES	MATERIAL	THICKNESS	AREA
21	TIN	2,0 μm	ALL OVER
22	NICKEL GOLD TIN/LEAD	0,8 μm	ALL OVER CONTACT AREA BARREL
23	NICKEL GOLD GOLD	0,8 μm	ALL OVER CONTACT AREA ALL OVER
24	NICKEL GOLD GOLD	1,2 μm	ALL OVER CONTACT AREA ALL OVER
25	NICKEL SILVER TIN/LEAD	2,5 μm	ALL OVER CONTACT AREA BARREL
26	SILVER NICKEL	1,5-2,5 μm 0,76 μm	ALL OVER ALL OVER
29	SILVER	2,5 μm	ALL OVER
30	NICKEL TIN/LEAD	1,27 μm 1,27 μm	ALL OVER ALL OVER
31	LUBRICATED		

—	—	—	—	—	
AW1	REVISED PER ECO-10-000444	KK	AEG	11JAN10	
AW	EBD0-0335-04	JMS	FWK	02-08-04	
W	EH-1347-96	JvL	RV	21-11-96	
V	EH-0302-94	JvL	MvD	03-05-94	
U	ECN H-9813	JvdH	RD	18-05-92	
T	ECN H-9192	MvD	RD	09-10-91	
LTR.	REVISION RECORD		DR.	CHK. DATE	
DR.:	—	CHK.:	—	APP.:	—
DATE:	—	DATE:	—	DATE:	—

CUSTOMER DRAWING FOR REFERENCE ONLY
WILL NOT BE UPDATED

© COPYRIGHT 19- BY AMP HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE
COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.
THIS DRAWING IS UNPUBLISHED
RELEASED FOR PUBLICATION 19

AMP AMP HOLLAND B.V.
's-Hertogenbosch,
The Netherlands.

PIN TYPE III CONTACT
SIZE 16

- NOTES :
- 1 U.L. RECOGNIZED UNDER FILE E28476 VOL. VI SEC. I .
 - 2 FOR CRIMP DETAILS SEE AMP-SPEC. 114-19.000 .
 - 3 MEETS PRODUCT SPECIFICATION 108-10042.
 - 4 0,40 MAX. GAP BETWEEN SPRING-NOSE AND CONTACT BODY.
 - 5 SPECIAL REEL WITH 200 PCS FOR REEL-FED HANDTOOL.
 - 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI