




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		J	REVISED PER ECO-15-004633	18JUN2015	NK	JO



- 1
- .000030 GOLD ON CONTACT AREA, GOLD FLASH ON REMINDER OVER .000050 NICKEL.
- 2
- RELEED FOR MIN APPLICATOR.
- 3
- GOLD PLATING IS NOT REQUIRED IN THIS AREA.
- 4
- HAND TOOL MUSED FOR CRIMPING L.P. CONTACT IS #90358-1.
- 5
- .0000150 GOLD ON CONTACT AREA, .00010-.000200 93/7 BRIGHT TIN-LEAD IN AREA K, ALL OVER .000050 NICKEL.
- 6
- .000030 GOLD ON CONTACT AREA, .00010-.000200 93/7 BRIGHT TIN-LEAD IN AREA K, ALL OVER .000050 NICKEL.
- 7
- CUT-OUTS ON THE BOX ARE AT MANUFACTURERS OPTION.
- 8
- POINT OF MEASUREMENT FOR PLATING THICKNESS(INSIDE BEAMS).
- 9
- OBSOLETE PART NUMBER.

SUPERCEDED BY 102918-1	LOOSE PIECE	4	6	9	102918-6
	_____		6	9	102918-5
	LOOSE PIECE	4	5	9	102918-4
	_____		5	9	102918-3
	LOOSE PIECE	4	1		102918-2
	_____		1		102918-1
	REMARKS		FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KATE HELM 03MAY89		 TE Connectivity			
DIMENSIONS: INCHES		CHK C. OBERMAN 02JUN89					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. GESFORD 02JUN89		NAME CONTACT, MOD IV 1/2, RECEPTACLE, CRIMP SNAP-IN		
			PRODUCT SPEC 108-25021				
			APPLICATION SPEC 114-25003				
			SIZE A2				
			CAGE CODE 00779				
MATERIAL CU-NI-SI		FINISH SEE TABLE		DRAWING NO C-102918		RESTRICTED TO —	
		CUSTOMER DRAWING		SCALE 10:1		SHEET 1 of 1	REV J