



- NOTES:
- 1) DRAWINGS IN ACCORDANCE WITH STANDARD ANSI Y14.5M-1994.
 - 2) UNTOLERANCED DIMENSIONS LOCATING TRUE POSITION ARE BASIC.
 - 3) THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND IS COPYRIGHTED. EXCEPT WITH THE WRITTEN PERMISSION OF SPECTRUM CONTROL, INC. OR ITS SUBSIDIARIES, SUCH INFORMATION SHALL NOT BE PUBLISHED OR DISCLOSED TO OTHERS, OR USED FOR ANY PURPOSE AND THIS DOCUMENT SHALL NOT BE DUPLICATED IN WHOLE OR IN PART.
 - 4) SUGGESTED MOUNTING HOLE: 4.2 mm
 - 5) HARDWARE NOT INCLUDED
 - 6) MAXIMUM MOUNTING TORQUE: 0.45 Nm



BUSHING FINISH	SILVER
LEAD FINISH	SILVER
CAPACITANCE	12000pF GMV
TEMP. RANGE	-55°C TO +125°C
CURRENT	10 AMPS
WORKING VOLTAGE	125°C 100 VDC
DC RESISTANCE	N / A

I.L. PER MIL-STD-220 @ 25°C (NO LOAD)				
MHz	10	100	1 G	10 G
dB	18	65	70	70



MARKING:

PART: 51-831-015

BAG:

51-831-015

DATE CODE

QTY./BAG (200 MAX.)

										00	REV	NO	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED DECIMAL X ± 1.0 DECIMAL X.X ± .2 DECIMAL X.XX ± ANGLES ± 0° 30'	DO NOT SCALE THIRD ANGLE PROJECTION	CODE IDENT. NUMBER 0LSP2	FAIRVIEW PENNSYLVANIA SPECTRUM CONTROL INC. DWN. D. REILLY DATE 03-26-07 ENGR. D. REILLY SHEET 1 OF 1	DESCRIPTION: M4 X 0.7 FILTER 51-831-015
										CN 33880-CPD	CHANGE NOTICE	NO						

