


Small Signal Product

5% Tolerance SMD Zener Diode

FEATURES

- Wide zener voltage range selection : 2.4V to 75V
- Surface Mount Device Type
- Moisture sensitivity level 1
- Pb free and RoHS compliant
- Green compound (Halogen free) with suffix "G" on packing code and prefix "G" on date code
- VZ Tolerance Selection of $\pm 5\%$
- Matte Tin(Sn) lead finish


SOD-123F


MECHANICAL DATA


- Case: Flat lead SOD-123F small outline plastic package
- Terminal: Matte tin plated, lead free, solderable per MIL-STD-202, Method 208 guaranteed
- High temperature soldering guaranteed: 260°C/10s
- Polarity: Indicated by cathode band
- Weight : $8.85 \pm 0.5\text{mg}$

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS ($T_A=25^\circ\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	VALUE	UNIT
Forward Voltage @ $I_F = 10\text{mA}$	V_F	1	V
Power Dissipation	P_D	500	mW
Thermal Resistance from Junction to Ambient (Note 1)	$R_{\theta JA}$	350	$^\circ\text{C/W}$
Junction and Storage Temperature Range	T_J, T_{STG}	-65 to +150	$^\circ\text{C}$

Note 1: Valid provided that electrodes are kept at ambient temperature.

Zener I vs. V Characteristics



- V_{BR} : Voltage at I_{ZK}
- I_{ZK} : Test current for voltage V_{BR}
- Z_{ZK} : Dynamic impedance at I_{ZK}
- I_{ZT} : Test current for voltage V_Z
- V_Z : Voltage at current I_{ZT}
- Z_{ZT} : Dynamic impedance at I_{ZT}
- I_{ZM} : Maximum steady state current
- V_{ZM} : Voltage at I_{ZM}

Small Signal Product

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Part Number	Device Marking	V_Z @ I_{ZT} (Volt)			I_{ZT} (mA)	Z_{ZT} @ I_{ZT} (Ω) Max	I_{ZK} (mA)	Z_{ZK} @ I_{ZK} (Ω) Max	I_R @ V_R (μA) Max	V_R (V)
		Min	Nom	Max						
BZT52C2V4	2V4Z	2.28	2.40	2.52	5	100	1	564	45	1.0
BZT52C2V7	2V7Z	2.57	2.70	2.84	5	100	1	564	18	1.0
BZT52C3V0	3V0Z	2.85	3.00	3.15	5	100	1	564	9	1.0
BZT52C3V3	3V3Z	3.14	3.30	3.47	5	95	1	564	4.5	1.0
BZT52C3V6	3V6Z	3.42	3.60	3.78	5	90	1	564	4.5	1.0
BZT52C3V9	3V9Z	3.71	3.90	4.10	5	90	1	564	2.7	1.0
BZT52C4V3	4V3Z	4.09	4.30	4.52	5	90	1	564	2.7	1.0
BZT52C4V7	4V7Z	4.47	4.70	4.94	5	80	1	470	2.7	2.0
BZT52C5V1	5V1Z	4.85	5.10	5.36	5	60	1	451	1.8	2.0
BZT52C5V6	5V6Z	5.32	5.60	5.88	5	40	1	376	0.9	2.0
BZT52C6V2	6V2Z	5.89	6.20	6.51	5	10	1	141	2.7	4.0
BZT52C6V8	6V8Z	6.46	6.80	7.14	5	15	1	75	1.8	4.0
BZT52C7V5	7V5Z	7.11	7.50	7.86	5	15	1	75	0.9	5.0
BZT52C8V2	8V2Z	7.79	8.20	8.61	5	15	1	75	0.63	5.0
BZT52C9V1	9V1Z	8.65	9.10	9.56	5	15	1	94	0.45	6.0
BZT52C10	10VZ	9.50	10.00	10.50	5	20	1	141	0.18	7.0
BZT52C11	11VZ	10.45	11.00	11.55	5	20	1	141	0.09	8.0
BZT52C12	12VZ	11.40	12.00	12.60	5	25	1	141	0.09	8.0
BZT52C13	13VZ	12.35	13.00	13.65	5	30	1	160	0.09	8.0
BZT52C15	15VZ	14.25	15.00	15.75	5	30	1	188	0.045	10.5
BZT52C16	16VZ	15.20	16.00	16.80	5	40	1	188	0.045	11.2
BZT52C18	18VZ	17.10	18.00	18.90	5	45	1	212	0.045	12.6
BZT52C20	20VZ	19.00	20.00	21.00	5	55	1	212	0.045	14.0
BZT52C22	22VZ	20.90	22.00	23.10	5	55	1	235	0.045	15.4
BZT52C24	24VZ	22.80	24.00	25.20	5	70	1	235	0.045	16.8
BZT52C27	27VZ	25.65	27.00	28.35	2	80	0.5	282	0.045	18.9
BZT52C30	30VZ	28.50	30.00	31.50	2	80	0.5	282	0.045	21.0
BZT52C33	33VZ	31.35	33.00	34.65	2	80	0.5	306	0.045	23.0
BZT52C36	36VZ	34.20	36.00	37.80	2	90	0.5	329	0.045	25.2
BZT52C39	39VZ	37.05	39.00	40.95	2	130	0.5	329	0.045	27.3
BZT52C43	43VZ	40.85	43.00	45.15	2	150	0.5	353	0.045	30.1
BZT52C47	47VZ	44.65	47.00	49.35	2	170	0.5	353	0.045	33.0
BZT52C51	51VZ	48.45	51.00	53.55	2	180	0.5	376	0.045	35.7
BZT52C56	56VZ	53.20	56.00	58.80	2	200	0.5	400	0.045	39.2
BZT52C62	62VZ	58.90	62.00	65.10	2	215	0.5	423	0.045	43.4
BZT52C68	68VZ	64.60	68.00	71.40	2	240	0.5	447	0.045	47.6
BZT52C75	75VZ	71.25	75.00	78.75	2	255	0.5	470	0.045	52.5

Notes : 1. The Zener Voltage (V_Z) is tested under pulse condition of 10ms.

2. The device numbers listed have a standard tolerance on the nominal zener voltage of $\pm 5\%$.

3. For detailed information on price, availability and delivery of nominal zener voltages between the voltages shown and tighter voltage tolerances, contact your nearest Taiwan Semiconductor representative.

4. The zener impedance is derived from the 60-cycle ac voltage, which results when an ac current having an RMS value equal to 10% of the dc zener current (I_{ZT} or I_{ZK}) is superimposed to I_{ZT} or I_{ZK} .

Small Signal Product

RATINGS AND CHARACTERISTICS CURVES

($T_A=25^\circ\text{C}$ unless otherwise noted)

Fig. 1 Typical Forward Characteristics




Fig. 2 Zener Breakdown Characteristics




Fig. 3 Zener Breakdown Characteristics




Fig. 4 Power Dissipation Curve




Fig. 5 Typical Capacitance





Fig. 6 Effect of Zener Voltage on Impedance



Small Signal Product

ORDERING INFORMATION

PART NO.	MANUFACTURE CODE	PACKING CODE	GREEN COMPOUND CODE	PACKAGE	PACKING
BZT52Cxxx (Note 1)	(Note 2)	RH	G	SOD-123F	3K / 7" Reel

Note 1: "xxx" defines voltage from 2.4V (BZT52C2V4) to 75V (BZT52C75)


Note 2: Manufacture special control, if empty means no special control requirement.

EXAMPLE

PREFERRED P/N	PART NO.	MANUFACTURE CODE	PACKING CODE	GREEN COMPOUND CODE	DESCRIPTION
BZT52C75 RHG	BZT52C75		RH	G	Green compound
BZT52C75-L0 RHG	BZT52C75	L0	RH	G	Green compound
BZT52C75-B0 RHG	BZT52C75	B0	RH	G	Green compound


PACKAGE OUTLINE DIMENSIONS

SOD-123F



DIM.	Unit (mm)		Unit (inch)	
	Min	Max	Min	Max
A	1.50	1.70	0.059	0.067
B	3.30	3.90	0.130	0.154
C	0.50	0.70	0.020	0.028
D	2.50	2.70	0.098	0.106
E	0.80	1.15	0.031	0.045
F	0.05	0.20	0.002	0.008

SUGGEST PAD LAYOUT



DIM.	Unit (mm)	Unit (inch)
	Typ.	Typ.
C	2.86	0.113
G	1.52	0.060
X	1.34	0.053
X1	4.20	0.165
Y	1.80	0.071

Small Signal Product**Notice**

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors in accuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[BZT52C62](#) [BZT52C68](#) [BZT52C75](#) [BZT52C10](#) [BZT52C11](#) [BZT52C12](#) [BZT52C13](#) [BZT52C15](#) [BZT52C16](#)
[BZT52C18](#) [BZT52C20](#) [BZT52C22](#) [BZT52C24](#) [BZT52C27](#) [BZT52C2V4](#) [BZT52C2V7](#) [BZT52C30](#) [BZT52C33](#)
[BZT52C36](#) [BZT52C39](#) [BZT52C3V0](#) [BZT52C3V3](#) [BZT52C3V6](#) [BZT52C3V9](#) [BZT52C43](#) [BZT52C47](#) [BZT52C4V3](#)
[BZT52C4V7](#) [BZT52C51](#) [BZT52C56](#) [BZT52C5V1](#) [BZT52C5V6](#) [BZT52C6V2](#) [BZT52C6V8](#) [BZT52C7V5](#) [BZT52C8V2](#)
[BZT52C9V1](#) [BZT52C62 RHG](#) [BZT52C3V3 RHG](#) [BZT52C8V2 RHG](#) [BZT52C10 RHG](#) [BZT52C4V7 RHG](#) [BZT52C30](#)
[RHG](#) [BZT52C4V3 RHG](#) [BZT52C36 RHG](#) [BZT52C75 RH](#) [BZT52C39 RHG](#) [BZT52C22 RHG](#) [BZT52C16 RHG](#)
[BZT52C12 RHG](#) [BZT52C15 RHG](#) [BZT52C68 RHG](#) [BZT52C13 RHG](#) [BZT52C27 RHG](#) [BZT52C75 RHG](#) [BZT52C2V7](#)
[RHG](#) [BZT52C7V5 RHG](#) [BZT52C68 RH](#) [BZT52C24 RHG](#) [BZT52C51 RHG](#) [BZT52C18 RHG](#) [BZT52C47 RHG](#)
[BZT52C62 RH](#) [BZT52C56 RHG](#) [BZT52C33 RHG](#) [BZT52C11 RHG](#) [BZT52C3V6 RHG](#) [BZT52C5V1 RHG](#)
[BZT52C3V9 RHG](#) [BZT52C2V4 RHG](#) [BZT52C20 RHG](#) [BZT52C5V6 RHG](#) [BZT52C9V1 RHG](#) [BZT52C43 RHG](#)
[BZT52C6V2 RHG](#) [BZT52C3V0 RHG](#) [BZT52C6V8 RHG](#) [BZT52C39 RH](#) [BZT52C7V5 RH](#) [BZT52C18 RH](#)
[BZT52C2V4 RH](#) [BZT52C56 RH](#) [BZT52C2V7 RH](#) [BZT52C9V1 RH](#) [BZT52C22 RH](#) [BZT52C3V9 RH](#) [BZT52C6V8 RH](#)
[BZT52C30 RH](#) [BZT52C5V6 RH](#) [BZT52C4V3 RH](#) [BZT52C10 RH](#) [BZT52C4V7 RH](#) [BZT52C5V1 RH](#) [BZT52C20 RH](#)
[BZT52C24 RH](#) [BZT52C27 RH](#) [BZT52C15 RH](#) [BZT52C51 RH](#) [BZT52C3V0 RH](#) [BZT52C12 RH](#)