






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION - - -
 © COPYRIGHT - By - ALL RIGHTS RESERVED.




LOC	DIST	REVISIONS					
—	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C2	REVISED PER ECO-11-005556	02MAR11	PSK	MW

			Materials
No	Component name	Base material	Plating
1	Housing	Diallyl phthalate resin	
2	End terminal	silver clad copper alloy	gold flash
3	Center terminal	copper alloy	gold flash
4	Rocker contact	silver clad copper alloy	gold flash
5	Actuator tip	Phenol resin, UL94 HB	
6	Actuator spring	music wire	
7	Actuator	Phenol resin, UL94 HB	
8	Actuator guide	polymer	
9	Frame	stainless steel 100-77	
10	Retainer/Stopper	polyamid resin	none
11	Plunger spring	music wire	
12	Plunger pin	brass	
13	Bushing	zinc	nickel
14	Plunger	brass	nickel
15	Mounting nuts (2)	brass	nickel
16	Locating ring	cold rolled steel	nickel
17	Internal tooth lockwasher	steel	nickel



Specifications			
Current rating UL & CSA	6A @ 125 VAC (resistive)		
	3A @ 250 VAC (resistive)		
	4A @ 28 VDC (resistive)		
Initial contact resistance	10 milliohms max @ 2–4 VDC, 1A		
Dielectric strength	1,000 megohms min.		
Withstanding voltage	1,500 VAC		
Travel	.140		
Actuation force	.4 to 2 kgf		
Operating temperature	–20C to +85C		
Storage temperature	–40C to +85C		
Contact timing	break before make		
Terminal seal	over molded		
Durability	Parameter	Push on/ Push off	Momentary
	250 VAC (3A resistive)	30,000	30,000
	125 VAC (6A resistive)	30,000	30,000
	28 VDC (4A resistive)	30,000	30,000



PART NUMBER	Alco P/N	Mark SWITCH 	Poles	Throws	Terminal	Function		Connected Terminals	
									
5-1437567-8	MPG406R	MPG 406R	4	2	Wire lug	ON	MOM	2-1, 5-4, 8-7, 11-10	2-3, 5-6, 8-9, 11-12
5-1437567-7	MPG406N	MPG 406N	4	2	Wire lug	ON	ON	2-1, 5-4, 8-7, 11-10	2-3, 5-6, 8-9, 11-12
5-1437567-6	MPG306F	MPG 306F	3	2	Wire lug	ON	MOM	2-1, 5-4, 8-7	2-3, 5-6, 8-9
5-1437567-5	MPG306D	MPG 306D	3	2	Wire lug	ON	ON	2-1, 5-4, 8-7	2-3, 5-6, 8-9
5-1437567-4	MPG206RPC	MPG 206RPC	2	2	PC	ON	MOM	2-1, 5-4	2-3, 5-6
5-1437567-3	MPG206R	MPG 206R	2	2	Wire lug	ON	MOM	2-1, 5-4	2-3, 5-6
5-1437567-2	MPG206NPC	MPG 206NPC	2	2	PC	ON	ON	2-1, 5-4	2-3, 5-6
5-1437567-1	MPG206N	MPG 206N	2	2	Wire lug	ON	ON	2-1, 5-4	2-3, 5-6
5-1437567-0	MPG106F	MPG 106F	1	2	Wire lug	ON	MOM	2-1	2-3
4-1437567-9	MPG106D	MPG 106D	1	2	Wire lug	ON	ON	2-1	2-3


NOTES:

1. TERMINAL NUMBERS ARE FOR REFERENCE ONLY AND DO NOT APPEAR ON THE SWITCHES.
2. EACH SWITCH SUPPLIED WITH THE FOLLOWING MOUNTING HARDWARE:
 - (2) 15/32-32 UNS-2B HEX NUTS
 - (1) INTERNAL TOOTH LOCKWASHER
 - (1) LOCATING RING





7. ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS).




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. M.BINNER CHK. M.ZITTO APVD. M.ZITTO	02MAR09 15NOV04 15NOV04	 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.012 4 PLC ± ANGLES ± FINISH —		NAME ALCO SWITCH GREEN SERIES PUSHBUTTON SWITCH, MPG SERIES PRODUCT SPEC APPLICATION SPEC	
MATERIAL —		WEIGHT —		SIZE CAGE CODE DRAWING NO A1 00779 C 4-1437567-9	
		CUSTOMER DRAWING		SCALE 3:1 SHEET 1 OF 3 REV C	


LOC	DIST	REVISIONS				
		REV	LTR	DESCRIPTION	DATE	APP'D
—	—	—	—	SEE SHEET 1	—	—





MPG-106



MPG-206





WIRE LUG TERMINAL




PC TERMINAL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. BINNER	02MAR09	 TE Connectivity			
DIMENSIONS: INCHES		CHK M. ZITTO	15NOV04				
	TOLERANCES, UNLESS OTHERWISE SPECIFIED:		AP'D M. ZITTO	15NOV04	NAME ALCOSWITCH GREEN SERIES PUSHBUTTON SWITCH, MPG SERIES		
	1 P L C ± .		PRODUCT SPEC				
	2 P L C ± .		APPLICATION SPEC				
	3 P L C ± .012		WEIGHT				
4 P L C ± .		FINISH		SIZE CAGE CODE DRAWING NO		RESTRICTED TO	
MATERIAL		WEIGHT		A1 00779 C 4-1437567-9			
		CUSTOMER DRAWING		SCALE 3:1		SHEET 2 OF 3	REV C2


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
—	—	—	—	SEE SHEET 1	—	—




MPG-306




MPG-406




COUNTRY OF ORGIN STAMPED HERE EITHER SIDE



WIRE LUG TERMINAL



PC TERMINAL



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. BINNER	02MAR09	 TE Connectivity	
DIMENSIONS: INCHES		CHK M. ZITTO	15NOV04		
	0. PLC	±	—	NAME ALCOSWITCH GREEN SERIES PUSHBUTTON SWITCH, MPG SERIES	SIZE A1
	1. PLC	±	—		
	2. PLC	±	—		
	3. PLC	±	—		
MATERIAL	FINISH	—	—	DRAWING NO 4-1437567-9	RESTRICTED TO —
	—	—	—		
CUSTOMER DRAWING		SCALE 3:1		SHEET 3 OF 3 REV C2	