


12 11 10 9 8 7 6 5 4 3 2 73404

MATERIALS AND FINISHES




BODY, OC, SLEEVE: BRASS
PLATED: GOLD

CENTER CONTACT: BeCu
PLATED: GOLD

INSULATOR: TEFLON



RECOMMENDED BOARD LAYOUT



PART # 73404-1390

MIL-STD-348A, FIG. 311-2

INTERFACE

SPECIFICATION

DESCRIPTION

- UNLESS OTHERWISE SPECIFIED DIMS
ARE INCHES AND ANGLES ARE DEGREES.
- SURFACE FINISH OF .63 ALL OVER.
 - NO CHATTER OR NON-UNIFORM
 - SURFACE FINISH ALLOWED.
 - PARTS TO BE FREE OF BURRS
& SHARP EDGES .005 MAX BREAK.
 - EXTERNAL THREADS TO BE ROLLED
OR SINGLE POINT.
 - DIAMETERS TO BE CONCENTRIC
WITHIN .003 TIR.

		CHG: NEW RELEASE		EC NO. URF-1802		DRWN: SSS 07/16/03		CHK: TEF 07/16/03		APPR: GMH 07/16/03		CHG: XXX		EC NO. URF-XXXX		DRWN: XXX 00/00/00		CHK: XXX 00/00/00		APPR: XXX 00/00/00		DESCRIPTION	
		A												A								REV	
		QUALITY SYMBOLS				GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE 6:1		DESIGN UNITS INCH		THIRD ANGLE PROJECTION		REVISE ON CAD ONLY									
		▽ .0				mm INCH		DIMENSION STYLE IN/MM		DRAWN BY DATE		TITLE		SMB PLUG RA PCB 50 OHM SMB-P/PCB									
		▽ .0				4 PLACES ± --- ± ---																	
						3 PLACES ± --- ± ---																	
						2 PLACES ± --- ± ---				TEF													
						1 PLACE ± --- ± ---				CHECKED BY DATE													
						ANGULAR ±1/2°				TEF 2003/07/16													
						DRAFT WHERE APPLICABLE				APPROVED BY DATE													
										GMH 2003/06/18													
						MUST REMAIN WITHIN DIMENSIONS																	

THIRD ANGLE PROJECTION		REVISE ON CAD ONLY	
TITLE		SMB PLUG RA PCB 50 OHM SMB-P/PCB	
MOLEX INCORPORATED		MATERIAL NO.	
DOCUMENT NO.		SHEET NO.	
SD-73404-139		1 OF 1	