




**Part Number : PTA 470/30**

**Proximity Switch - Reed Switch based**

**Threaded - Normally Open Contacts - Suggested Magnet: PRM**

**Product Data Sheet**

PICTURE	DIMENSIONS	Applications Include
		<ul style="list-style-type: none"> <li>• Position and limit sensing.</li> <li>• Linear actuators .</li> <li>• Security system switch.</li> <li>• Door Switch.</li> </ul>
		<b>Options</b> <ul style="list-style-type: none"> <li>• M6 Thread.</li> <li>• Custom cable lengths, strip lengths, cable types, terminations.</li> <li>• If you do not see what you need, just ask, as there is a strong possibility we can do it !</li> </ul>

Drawings not to scale  
All dimensions in mm(inches) nominal

SPECIFICATION	
Contact Form / Style	Normally Open
Switching Capacity (Resistive)	10 W/VA Max.
Switching Voltage	400 VAC Max.
Switching Current	0.5 A. Max.
Carry Current	1.0 A. Max.
Breakdown Voltage	600 VDC Min.
Contact Resistance	150 mOhms Max.
Switching Distance	3 mm Min.
Operating Temperature Range	-20°C +85°C
Storage temperature	-25°C +90°C
Case Material	Brass-Nickel Plated
Cable	2 x Round 0.22mm <sup>2</sup> PVC Insulated Blue

Rev. No.	Revision Note	Date	Signature
2	Datasheet Redesign	28-07-06	LG

FORM AE043 ISS.2



As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

Phone : +44 (0)1255 862236

www.assembletech.co.uk

Fax: +44 (0)1255 862014

©2006 Copyright Assembletech Europe Ltd, Unit 7, Rice Bridge Industrial Estate, Thorpe - Le - Soken, Essex, CO16 0HL, ENGLAND.  
USA: + 1 973 777 6900 - Belgium: + 32 (0)12 390400 - France: + 33 (0) 1 43 96 86 10