


5N Detector Switches

Japan

Type: **ESE11**

Standard type with a wide range of customizable features




■ Features

- Attachable type, wide range of customizable features including operational directions
- Light operating force
- Wide available range for reflow soldering

■ Recommended Applications

- Mechanism and detection for Car audio equipment

■ Explanation of Part Numbers



■ Specifications

Rating	50 μ A 3 Vdc to 10 mA 5 Vdc (Resistive load)
Contact Resistance	500 m Ω max.
Insulation Resistance	100 M Ω max. (100 Vdc)
Dielectric Withstanding Voltage	100 Vac for 1 minute
Operating Force	350 mN max. (Full Travel)
Mounting Height	· Type SV 4.9 mm · Type MV 4.9 mm (MV2, 7 : 5.4 mm) · Type SH 5.25 mm · Type MH 4.25 mm · Type HS, SF 3.6 mm
Poles and Throws	1-pole 1-throw
Full Travel (Pushing distance)	· Type SV 6.1 mm (2.4 mm) · Type MV 6.1 mm (2.4 mm) · Type SH 3.0 mm (2.4 mm) · Type MH 1.7 mm (2.4 mm) · Type HS, SF 6.3 mm (2.4 mm)
Operating Life	50000 cycles min.
Temperature Range	-10 °C to +70 °C
Heat Resistance	+80 °C for 96 hours
Low Temperature Resistance	-25 °C for 96 hours
Humidity Resistance	+40 °C 90 % to 95 % RH for 96 hours

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

Vertical Type	No. 3 ESE11MV9 For reflow soldering 1-pole 1-throw Recommended land pattern View from (A)	No. 4 ESE11MV2 For reflow soldering 1-pole 1-throw Recommended land pattern View from (A)
	No. 5 ESE11MV7 For reflow soldering 1-pole 1-throw Recommended land pattern View from (A)	No. 6 ESE11SH1C For wave soldering 1-pole 1-throw Gold plating ESE11SH5 Recommended PWB piercing plan View from (A)




■ Dimensions in mm (not to scale)

Horizontal Type	No. 7 ESE11SH2C For wave soldering 1-pole 1-throw Gold plating ESE11SH6 Full travel ON starting position Recommended PWB piercing plan View from (A)	No. 8 ESE11MH1 For reflow soldering 1-pole 1-throw Gold plating ESE11MH3 Recommended land pattern View from (A) Full travel ON starting position
	No. 9 ESE11MH2 For reflow soldering 1-pole 1-throw Gold plating ESE11MH4 Recommended land pattern View from (A) Full travel ON starting position	No. 10 ESE11MH5 For reflow soldering 1-pole 1-throw Recommended land pattern View from (A) Full travel ON starting position

■ Dimensions in mm (not to scale)

Horizontal Type	No. 11 ESE11MH6 For reflow soldering 1-pole 1-throw Recommended land pattern View from (A)	No. 12 ESE11HS1 With mounting hole 1-pole 1-throw View from side (A) View from side (B) Recommended piercing plan
	No. 13 ESE11HS2 With mounting hole 1-pole 1-throw View from side (A) View from side (B) Recommended piercing plan	No. 14 ESE11SF1A Snap-in type 1-pole 1-throw Recommended piercing plan (PWB thickness=0.80±0.05) View from (A)

■ Circuit Diagram

MH, SH Type	MV, SV Type	SF, HS Type
1-pole 1-throw (N.O)	1-pole 1-throw (N.O)	1-pole 1-throw (N.O)
		

■ Packaging Specifications

Standard Reel Dimensions in mm (not to scale)

