

0669 0669-0-15-XX-30-XX-10-0 Solder mount in 1,52 min. mounting hole	0670 0670-0-15-XX-30-XX-10-0 Solder mount in 1,52 min. mounting hole	0673 0673-0-15-XX-30-XX-10-0 Surface Mount	0666 0666-0-15-XX-32-XX-10-0 Solder mount in 1,63 min. mounting hole								
0341 0341-0-15-XX-30-XX-10-0 Solder mount in 1,85 mounting hole	0252 0252-0-15-XX-32-XX-10-0 Hex press-fit in 1,45 plated thru hole	0678 0678-0-15-XX-32-XX-10-0 Press-fit in 1,45 mounting hole	0676 0676-0-15-XX-30-XX-10-0 Press-fit in 1,45 mounting hole								
0697 0697-0-15-XX-30-XX-10-0 Press-fit in 1,45 mounting hole	0668 0668-0-15-XX-30-XX-10-0 Press-fit in 1,45 mounting hole	0253/1033 XXX3-0-15-XX-30-XX-10-0 Press-fit in 1,45 mounting hole <table><tr><th>Basic Part Number</th><th>Length L</th><th>Depth N</th></tr><tr><td>0253-0</td><td>4,39</td><td>3,76</td></tr><tr><td>1033-0</td><td>5,16</td><td>4,11</td></tr></table>	Basic Part Number	Length L	Depth N	0253-0	4,39	3,76	1033-0	5,16	4,11
Basic Part Number	Length L	Depth N									
0253-0	4,39	3,76									
1033-0	5,16	4,11									
SPECIFICATIONS SHELL MATERIAL: Brass Alloy 360, 1/2 Hard CONTACT MATERIAL: Beryllium Copper Alloy 172, HT PART MANUFACTURED IN INCHES, METRIC FOR REF ONLY TOLERANCES ON: LENGTHS: ± 0,13 DIAMETERS: ± 0,05 ANGLES: ± 2° ORDER CODE: XXXX - X - 15 - XX - 3X - XX - XX - 0 BASIC PART # SPECIFY SHELL FINISH: 01 5,08µm TIN/LEAD OVER NICKEL 80 5,08µm TIN OVER NICKEL 15 0,25µm GOLD OVER NICKEL SPECIFY CONTACT FINISH: 02 2,54µm TIN/LEAD OVER NICKEL 84 2,54µm TIN OVER NICKEL 27 0,76µm GOLD OVER NICKEL SELECT CONTACT #30 or #32 CONTACT (DATA ON PAGE 208) RoHS 2002/95/EC											