



SCC100AD4



Actual product appearance may vary.

Pressure Sensors: Measurement Type: Absolute; 0 psia to 100 psia Operating Pressure, Constant Current, "AD4" DIP package - Straight Port

Features

- Low Cost Sensor Element
- Internal Temperature Compensation
- Differential or Gage Pressures

Potential Applications

- Pneumatic Controls
- Automotive Diagnostics
- Medical Equipment
- Dental Equipment
- Environmental Controls

Description

The SCC Series sensors offer an extremely low cost sensor element with a temperature stable output when driven with a constant current source. These integrated circuit sensors were designed for extremely cost sensitive applications where precise accuracy over a wide temperature range is not required. This series is intended for use with non-corrosive, non-ionic working fluids such as air, and dry gases. Absolute devices have an internal vacuum reference and an output voltage proportional to applied pressure. The differential devices allow application of pressure to either side of the diaphragm and devices are thereby available to measure both differential and gage pressures. This product is packaged either in standard low cost chip carrier ? button? package or a DIP package. Both packages are designed for applications where the sensing element is to be integral to the OEM equipment. These packages can be o ring sealed, epoxied, and/or clamped onto a pressure fitting. A closed bridge four pin SIP configuration is provided for electrical connection to the button package. The DIP package offers a 5-pin open bridge configuration.

Supporting Documentation

-  [Dimensions](#)
-  [Electrical Connections](#)
-  [Equivalent circuit](#)


Product Specifications	
Measurement Type	Absolute
Signal Conditioning	Unamplified
Pressure Range	0 psia to 100 psia
Maximum Overpressure	150 psia
Supply Current	1.5 mA max.
Compensated	Yes
Output Calibration	No
Response Time	0.1 ms typ.
Termination	PCB
Port Style	Straight
Package Style	AD4 DIP
Full Scale Span	140 mV
Zero Pressure Offset	- 30.0 mV min., - 10.0 mV typ., 20.0 mV max.
Accuracy (% Best Fit Straight Line)	.5 %
Input Resistance	4.0 kOhm min., 5.0 kOhm typ., 6.5 kOhm max.
Output Resistance	4.0 kOhm min., 5.0 kOhm typ., 6.5 kOhm max.
Operating Temperature Range	- 40 °C to 85 °C [- 40 °F to 185 °F]
Compensated Temperature Range	0 °C to 50 °C [32 °F to 122 °F]
Storage Temperature Range	- 55 °C to 125 °C [- 67 °F to 257 ° F]
Media Compatibility	Clean, dry gases only.
UNSPSC Code	411121
UNSPSC Commodity	411121 Transducers
Availability	Global
Series Name	SCC

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control 

Product Search

Part number search:

Use (*) to expand search

Specification Search