


NOTES: UNLESS OTHERWISE SPECIFIED

1.

NOTICE:	THIS IS A RoHS COMPLIANT COMPONENT/PRODUCT.
RoHS 	ALL ENGINEERING CHANGES MUST HAVE PRIOR APPROVAL BY THE DESIGN CENTER.
2. PLASTIC: THERMAL PLASTIC MATERIAL WITH FLAMMABILITY RATING UL 94V-0 OR BETTER.
3. SOLDERABILITY: CONFORMS TO ANSI/J-STD-002, 245°C REFLOW PEAK TEMPERATURE PER IPC/EIA J-STD-003A.
4. OPERATING TEMPERATURE: 0°C TO +70°C
5. STORAGE TEMPERATURE: -20°C TO +125°C
6. JEDEC MOISTURE: LEVEL 1.
7. DIMENSIONS ARE IN INCHES, TOLERANCES:
.XX = ± 0.01 .XXX = ± 0.005

ELECTRICAL CHARACTERISTICS AT +25°C UNLESS OTHERWISE SPECIFIED
(FOR REFERENCE ONLY. USED FOR CUSTOMER INFORMATION.)

PARAMETER	SPECIFICATIONS
OPERATING TEMP	0°C - 70°C
URNS RATIO	1 : 1 $\pm 2\%$
POLARITY	PER SCHEMATIC
COUPLING CAPACITANCE (1-3) TO (6-4)	15 pF MAX (AT 100 KHz 20 mVRMS)
LEAKAGE INDUCTANCE (6-4) WITH (1-3) SHORTED	.18 uH MAX (AT 100KHz 20mVRMS)
PRIMARY INDUCTANCE (1-3), (6-4)	80 uH MIN (AT 100KHz 20mVRMS 25°C)
DC RESISTANCE (1-3), (6-4)	.2 OHM MAX
BETWEEN CHANNEL ISOLATION	700 VRMS MIN @ 60 SECONDS



SCHEMATIC

