



# DUAL-IN-LINE SOCKETS

## SERIES 115...001 • VERY LOW PROFILE • OPEN FRAME



- Low profile DIP socket, sits only .122" above the PCB
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details
- Series 115 uses MM #0501 pins. See page 162 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



| Total number of pins                     |     |     |     | Quantity per tube | ORDERING INFORMATION |                                  |
|------------------------------------------|-----|-----|-----|-------------------|----------------------|----------------------------------|
|                                          | A   | B   | C   |                   |                      |                                  |
| 10                                       | 0.5 | 0.2 | 0.3 | 41                | 115-XX-210-41-001000 |                                  |
| 4                                        | 0.2 | 0.3 | 0.4 | 102               | 115-XX-304-41-001000 |                                  |
| 6                                        | 0.3 | 0.3 | 0.4 | 67                | 115-XX-306-41-001000 |                                  |
| 8                                        | 0.4 | 0.3 | 0.4 | 50                | 115-XX-308-41-001000 |                                  |
| 10                                       | 0.5 | 0.3 | 0.4 | 40                | 115-XX-310-41-001000 |                                  |
| 14                                       | 0.7 | 0.3 | 0.4 | 28                | 115-XX-314-41-001000 |                                  |
| 16                                       | 0.8 | 0.3 | 0.4 | 25                | 115-XX-316-41-001000 |                                  |
| 18                                       | 0.9 | 0.3 | 0.4 | 22                | 115-XX-318-41-001000 |                                  |
| 20                                       | 1.0 | 0.3 | 0.4 | 20                | 115-XX-320-41-001000 |                                  |
| 22                                       | 1.1 | 0.3 | 0.4 | 18                | 115-XX-322-41-001000 |                                  |
| 24                                       | 1.2 | 0.3 | 0.4 | 16                | 115-XX-324-41-001000 |                                  |
| 28                                       | 1.4 | 0.3 | 0.4 | 14                | 115-XX-328-41-001000 |                                  |
| 20                                       | 1.0 | 0.4 | 0.5 | 20                | 115-XX-420-41-001000 |                                  |
| 22                                       | 1.1 | 0.4 | 0.5 | 18                | 115-XX-422-41-001000 |                                  |
| 24                                       | 1.2 | 0.4 | 0.5 | 16                | 115-XX-424-41-001000 |                                  |
| 28                                       | 1.4 | 0.4 | 0.5 | 14                | 115-XX-428-41-001000 |                                  |
| 32                                       | 1.6 | 0.4 | 0.5 | 12                | 115-XX-432-41-001000 |                                  |
| 24                                       | 1.2 | 0.6 | 0.7 | 16                | 115-XX-624-41-001000 |                                  |
| 28                                       | 1.4 | 0.6 | 0.7 | 14                | 115-XX-628-41-001000 |                                  |
| 32                                       | 1.6 | 0.6 | 0.7 | 12                | 115-XX-632-41-001000 |                                  |
| 36                                       | 1.8 | 0.6 | 0.7 | 11                | 115-XX-636-41-001000 |                                  |
| 40                                       | 2.0 | 0.6 | 0.7 | 10                | 115-XX-640-41-001000 |                                  |
| 42                                       | 2.1 | 0.6 | 0.7 | 9                 | 115-XX-642-41-001000 |                                  |
| 48                                       | 2.4 | 0.6 | 0.7 | 8                 | 115-XX-648-41-001000 |                                  |
| 50                                       | 2.5 | 0.6 | 0.7 | 8                 | 115-XX-650-41-001000 |                                  |
| 52                                       | 2.6 | 0.6 | 0.7 | 7                 | 115-XX-652-41-001000 |                                  |
| 50                                       | 2.5 | 0.9 | 1.0 | 8                 | 115-XX-950-41-001000 |                                  |
| 52                                       | 2.6 | 0.9 | 1.0 | 7                 | 115-XX-952-41-001000 |                                  |
| 64                                       | 3.2 | 0.9 | 1.0 | 6                 | 115-XX-964-41-001000 |                                  |
| <div>XX=Plating Code<br/>See Below</div> |     |     |     |                   |                      | <div>RoHS-2<br/>2011/65/EU</div> |
| SPECIFY PLATING CODE XX =                |     |     |     |                   |                      |                                  |
| Sleeve (Pin)                             |     |     |     |                   |                      |                                  |
| Contact (Clip)                           |     |     |     |                   |                      |                                  |