


## ● Features :

1. 0.56 inch (14.20mm) Digit Height.
2. Continuous uniform segments.
3. Low power requirement.
4. Excellent characters appearance.
5. Solid state reliability.
6. Categorized for luminous intensity.
7. Direct drive common cathode.

## ● Description :

1. The BS-C514RD is a 14.20mm (0.56") high single digit seven segments display.
2. This product use hi-eff red chips, which are made from GaAsP on GaP substrate.
3. This product have a black face and white segments.



## ● Package Dimensions :



### Notes:

1. All dimensions are in millimeters(inches).
2. Tolerance is  $\pm 0.25\text{mm} (.01")$  unless otherwise specified.
3. Specifications are subject to change without notice.

## ● Internal Circuit Diagram :



● **Absolute Maximum Ratings(Ta=25°C)**

Parameter	Symbol	Rating	Unit
Power Dissipation Per Segment	Pd	80	mW
Forward Current Per Segment	I <sub>F</sub>	30	mA
Peak Forward Current Per Segment (Duty 1/10, 1KHZ)	I <sub>FP</sub>	150	mA
Reverse Voltage Per Segment	V <sub>R</sub>	5	V
Operating Temperature	T <sub>opr</sub>	-40°C~80°C	-
Storage Temperature	T <sub>stg</sub>	-40°C~85°C	-
Soldering Temperature (1/16" From Body)	T <sub>sol</sub>	260°C For 5 Seconds	-

● **Electrical And Optical Characteristics(Ta=25°C)**

Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Forward Voltage Per Segment	V <sub>f</sub>	I <sub>F</sub> =10mA	-	1.9	2.5	V
Luminous Intensity Per Segment	I <sub>v</sub>	I <sub>F</sub> =10mA	-	3.0	-	mcd
Reverse Current Per Segment	I <sub>R</sub>	V <sub>R</sub> =5V	-	-	100	μA
Peak Wave Length	λ <sub>p</sub>	I <sub>F</sub> =10mA	-	635	-	nm
Dominant Wave Length	λ <sub>d</sub>	I <sub>F</sub> =10mA	-	630	-	nm
Spectral Line Half-width	Δλ	I <sub>F</sub> =10mA	-	45	-	nm

## ● Typical Electro-Optical Characteristics Curves

(25°C Ambient Temperature Unless Otherwise Noted)

Fig.1 Relative Radiant Intensity VS. Wavelength




Fig.2 Forward Current VS.  
Forward Voltage




Fig.3 Relative Luminous  
Intensity VS.  
Ambient Temperature




Fig.4 Relative Luminous  
Intensity VS.  
Forward Current




Fig.5 Forward Current  
Derating Curve VS.  
Ambient Temperature

