



Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207
Tel: 1-800-52 ALPHA (25742), Web: www.alphawire.com

Customer Specification

PART NO. 6020C

Construction

			Diameters (In)			
1) Component 1		19 X 1 PAIR				
a) Conductor		22 (7/30) AWG TC				
b) Insulation		0.010" Wall, Nom. FRPP				
(1) Color Code		Alpha Wire Color Code A				
Pair	Color	Pair	Color	Pair		
1	BLACK-RED	8	RED-GREEN	15		
2	BLACK-WHITE	9	RED-WHITE	16		
3	BLACK-GREEN	10	RED-BLUE	17		
4	BLACK-BLUE	11	RED-YELLOW	18		
5	BLACK-BROWN	12	RED-BROWN	19		
6	BLACK-YELLOW	13	RED-ORANGE			
7	BLACK-ORANGE	14	GREEN-BLUE			
c) Pair		2/Cond Cabled Together				
(1) Twists:		8.0 Twists/foot (min)				
Individually Applied:						
d) Shield:		Foil Free Alum/Mylar Tape, 25% Overlap, Min.				
(1) Foil Direction		Foil Facing In				
(2) Drain Wire		22 (7/30) AWG TC				
2) Cable Assembly		19 Components Cabled				
a) Twists:		1.7 Twists/foot (min)				
b) Core Wrap		Clear Mylar Tape, 25% Overlap, Min.				
3) Jacket		0.063" Wall, Nom.,PVC		0.593 (0.621 Max.)		
a) Color(s)		SLATE				
b) Print		ALPHA WIRE-* P/N 6020C 19PR 22 AWG SHIELDED 75C (UL) C(UL) TYPE CMG FT4 OR AWM 2493 ROHS * = Factory Code [Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]				

Applicable Specifications

1) UL	AWM/STYLE 2493	60°C
	VW-1	
	CMG	75°C
2) CSA International	FT4	
	C(UL) TYPE CMG	75°C

Environmental

1) EU Directive 2002/95/EC(RoHS):	All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.
2) REACH Regulation (EC 1907/2006):	This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item. For up-to-date information, please see Alpha's REACH SVHC Declaration.
3) California Proposition 65:	The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

Properties

Physical & Mechanical Properties	
1) Temperature Range	-20 to 75°C
2) Bend Radius	10X Cable Diameter
3) Pull Tension	313 Lbs, Maximum
Electrical Properties	(For Engineering purposes only)
1) Voltage Rating	300 V _{RMS}
2) Characteristic Impedance	60
3) Inductance	0.18 µH/ft, Nominal
4) Mutual Capacitance	28 pf/ft @1 kHz, Nominal
5) Ground Capacitance	50 pf/ft @1 kHz, Nominal
6) Conductor DCR	16.6 /1000ft @20°C, Nominal
7) Ind. Shield DC Resistance	14.4 /1000ft @20°C, Nominal

Other

Packaging	Flange x Traverse x Barrel (inches)
a) 1000 FT	30 x 14 x 12 Continuous length
b) 500 FT	24 x 14 x 12 Continuous length
c) 100 FT	16 x 11 x 8 Continuous length
<i>[Spool dimensions may vary slightly]</i>	

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.



Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207
Tel: 1-800-52 ALPHA (25742), Web: www.alphawire.com

RoHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number:6020C

6020C , RoHS-Compliant Commencing With 11/1/2004 Production

This document certifies that the Alpha part numbers cited above are manufactured in accordance with Directive 2002/95/EC of the European Parliament and of the Council of 27 January 2003, better known as the RoHS Directives, with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. The reader is referred to these Directives for the specific definitions and extents of these Directives. No Exemptions are required for RoHS Compliance on this item.

Substance	Maximum Control Value
Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.01% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm)
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE)	0.1% by weight (1000 ppm)
Including Deca-BDE	0.1% by weight (1000 ppm)

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire Company:

A handwritten signature in black ink, appearing to read "Dave Watson".

Dave Watson, Director of Engineering & QA

11/1/2012

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha Wire:](#)

[6020C SL005](#)