

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

P

F


ZONE

LTR

DESCRIPTION

DATE

APPD



				0.64—1.02mm DIA [22—18] AWG		63649—1				
				MAGNET WIRE RANGE		PART NO				
F	2.79 [.110]	1.47 [058]	0.8 ² MM [18]	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.25 [.010] 3 PLC DEC ± — ANGLES ± —		DR 5/6/92 P FORTNEY		AMP AMP Incorporated Harrisburg, PA 17105—3608		
		1.40 [055]	0.6 ² MM [20]			CHK 5/6/92 MS FEHER				
		1.35 [053]	0.3 ² MM [22]			APPD 5/6/92 G YETTER				
TYPE	WIDTH	±0.051 [±.002]	HEIGHT	WIRE	MATERIAL		APPD 5/6/92 R WEAVILL		NAME RING,AMPLIVAR	
WIRE BARREL CRIMP				BRASS		PRODUCT SPEC —				
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				FINISH		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO
				0.002032 [.000080] MIN TIN PL PER MIL—T—10727		—		B	00779	C—63649
						WEIGHT —		SCALE 8:1		SHEET 1 OF 1