



FXx^{*1)}P1GY^{*2)}
e.g. F25P1G1

*1) xx No. of contacts 09, 15, 25 or 37
*2) y for performance classes 1, 2 or 3
(contact cycle for G1/G2/G3 = 500/200/50)

xx	A [mm]	B [mm]	C [mm]	*E [mm]
09	30.8	16.9	25	ø1
15	39.1	25.2	33.3	
25	53	38.9	47.04	
37	69.3	55.3	63.5	

RoHS compliant

*PCB hole patterns, øE on supplement AM0023

3	xx	Signal contact	P1 / Brass	G1/G2/G3
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C - +125°C)	white
No.	St.	Part	Type Description/Material Surface plating/Colour/Class	

Measurement without tolerance acc. to ISO 2768-m		SCALE 2:1		TITLE	
NAME / DATE		SCHREF		D-Sub Miniature Connector	
DRAWN 02-09-2002		CHECKED Flößmann 02-09-2002		DWG.NO.	
1		DATE		CH.-NO.	
REV.		FxxP1Gy		REPLACEMENT FOR: FxxP1Gy a	
1		REV.		PAGES 1	

