

Tpcm[™] 780 is a high performance, inherently tacky, easy to rework phase change thermal interface material. Developed specifically to meet the high thermal conductivity and low thermal resistance requirements of today's demanding processors.

This silicone-free material is so soft that it begins to flow as the temperature is elevated by just a small amount. Also, since no tabs are required, Tpcm[™] 780 eliminates the need for expensive converting.

FEATURES AND BENEFITS

- Minimizes contact thermal resistance by filling the microscopic irregularities of the components it contacts. Begins to soften and flow at approximately 45°C
- Designed to minimize migration (pump out) at CPU operating temperatures using a unique material formulation that softens, but does not fully change phase
- Silicone-free for applications that are silicone sensitive
- Outstanding thermal performance helps to ensure CPU/application reliability
- No mess due to thixotropic characteristics which prevent flow outside of interface
- Very soft at room temperature, therefore less stress on board during assembly
- Tabless parts make for easier handling in the manufacturing environment
- RoHS Compliant
- 94V0 UL Flammability Rating
- Naturally tacky at room temperature, requiring no adhesive
- Heat sink preheating not required
- Exceptionally high reliability during storage and after installation

APPLICATIONS




- Graphics Cards
- Notebooks
- Desktops
- Servers
- Memory Modules
- Automotive
- IGBTs

TABLESS PARTS	TABBED PARTS
Easy handling in manufacturing environment/rapid handling	Marked tab reduces risk of top tab being left in place during assembly
Eliminating risk of top tab being left in place during assembly	Tab provides protection from dust and other contamination during application of pads and shipping of applied pads
Minimum part size is 8mm x 8mm (smaller size may be available via engineering approval)	Minimum part size is 10mm x 10mm (smaller size may be available via engineering approval)
Thicknesses are 0.016 inch (0.406mm) and 0.025 inch (0.635mm)	Thicknesses are 0.008 inch (0.203mm) and 0.010 inch (0.254mm)


Americas: +1.800.323.3757
LHP.Sales@lairdtech.com
Europe: +46.8.555.722.00
LHP.Sales@lairdtech.com
Asia: +86.10.5933.3682
LHP-ChinaSales@lairdtech.com

PROPERTIES	Tpcm TM 780	TEST METHOD
Color	Grey	Visual
Thickness, inches (mm)	0.008" (0.203), 0.010" (0.254) 0.016" (0.406), 0.025" (0.635)	
Thickness Tolerance, inches (mm)	± 0.0008" (0.0203), ± 0.0010" (0.0254) ± 0.0016" (0.0406), ± 0.0025" (0.0635)	
Construction & Composition	Non-reinforced Film	
Specific Gravity, g/cc	2.48	Helium Pycnometer
Phase Change Softening Range, °C	~45°C to 70°C	
Thermal Conductivity, W/mK	5.4	Hot Disk Thermal Constants Analyzer
Hardness (Shore 00)	85 3 sec @ 21 C	ASTM D2240
Thermal Resistance 70°C, 345 kPa, °C-cm ² /W (50 psi, °C-in ² /W)	0.025 (0.004)	ASTM D5470 (modified)
Outgassing TML	0.51%	ASTM E595
Outgassing CVCm	0.20%	ASTM E595

Bond Line Thickness Vs Pressure at 70°C



Thermal Resistance Vs Pressure



THR-DS-TPCM-780 0613

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Technologies materials rests with the end user, since Laird Technologies and its agents cannot be aware of all potential uses. Laird Technologies makes no warranties as to the fitness, merchantability or suitability of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential damages of any kind. All Laird Technologies products are sold pursuant to the Laird Technologies' Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2013 Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Technologies Logo, and other marks are trade marks or registered trade marks of Laird Technologies, Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird Technologies or any third party intellectual property rights. Document A15585-00 Rev C 06/2013

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Laird:

[A16001-00](#) [A16001-01](#) [A16001-02](#)