


High Efficiency Dual Output Quarter Brick DC-DC Converters

Features

- ◆ Industry Standard Package
- ◆ Low voltage outputs to 1.8V
- ◆ Output Currents up to 17A
- ◆ Designed for telecom standards
- ◆ Output voltage adjustment - independent or tracking (/C)
- ◆ Remote On / Off
- ◆ High Efficiency
- ◆ ASIC Design
- ◆ No minimum load



Key Market Segments & Applications

Specifications											
		PAQ65D482518		PAQ65D483318		PAQ65D483325		PAQ65D485033			
Model		V01	V02	V01	V02	V01	V02	V01	V02		
Nominal Output Voltage	VDC	2.5	1.8	3.3	1.8	3.3	2.5	5.0	3.3		
Output Current (Max)	A	15	17	15	17	15	17	13	16		
Output Current (Max total)	A	Io1 + Io2 = 18									
Max Output Power	W	37.5		49.5		49.5		65.0			
Efficiency (Typ)	%	86.0		86.0		87.0		90.0			
Input Voltage range	VDC	36 - 76V									
Input Current (typ)	A	0.82		0.97		1.10		1.36			
Output Voltage Accuracy	%	±2									
Output Voltage Trim Range (1)	VDC	2.25-2.75	1.62-1.98	2.97-3.63	1.62-1.98	2.97-3.63	2.25-2.75	4.50-5.50	2.97-3.63		
Max Ripple & Noise	mV	75	75	100	75	100	75	100	100		
Max Line Regulation	mV	± 6.6							± 10	± 6.6	
Max Load Regulation	mV	± 16.5							± 25	± 16.5	
Overcurrent Protection (OCP) (2)	%	105 - 160% (See options table for either manual or automatic reset)									
Overvoltage Protection (OVP)	%	120 - 140% (See options table for either manual or automatic reset)									
Remote On / Off	%	Low = ON, Open = OFF /P option; Low = OFF, Open = ON (See options)									
Operating Temperature	°C	-40°C to +85°C									
Operating & Storage Humidity	-	5 - 95% RH, Non condensing									
Storage Temperature	°C	-40°C to +100°C									
Cooling	-	Convection, or forced air									
I/O Isolation Voltage	-	Input to Output 1.5k VDC for 1 min.									
Vibration (non operating)	-	10 - 55Hz (1 minute), amplitude 0.825mm (49m/s ² max), X, Y, Z 1 hour each									
Shock	m/s ²	196.1 m/s ²									
Safety Agency Approvals	-	UL1950, CSA950, EN60950, & CE									
Weight (Typ)	g	40									
Size (WxHxD)	mm	36.8 x 8.9 x 57.9 (36.8 x 10.2 x 57.9 /C version)									
Warranty	yr	2 Years									


Note: See Installation Manual for full details, test methods of parameters and application notes.

1. Specify /C option for one trim pin - tracking outputs, leave blank for individual adjustment


2. Io1 + Io2

Not recommended for new designs

Outline Drawing (non /C versions)



Options



X	10, 15, & 20W 24V & 48VDC input DC-DC converters
PAF	500 & 600W Full brick DC-DC
PAH	50W to 200W Half brick DC-DC, single & dual outputs
PAQ	Up to 100W Quarter brick DC-DC, single outputs
SX	20W surface mount 24V & 48VDC-DC



Not recommended for new designs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TDK-Lambda:

[PAQ65D482518](#) [PAQ65D482518/C](#) [PAQ65D482518/CP](#) [PAQ65D482518/CPV](#) [PAQ65D482518/P](#)
[PAQ65D482518/PV](#) [PAQ65D482518/V](#) [PAQ65D483318/C](#) [PAQ65D483318/CP](#) [PAQ65D483318/CPV](#)
[PAQ65D483318/CV](#) [PAQ65D483318/P](#) [PAQ65D483318/PV](#) [PAQ65D483318/V](#) [PAQ65D483325](#) [PAQ65D483325/CP](#)
[PAQ65D483325/CPV](#) [PAQ65D483325/P](#) [PAQ65D483325/PV](#) [PAQ65D483325/V](#) [PAQ65D485033](#)
[PAQ65D485033/CP](#) [PAQ65D485033/CPV](#) [PAQ65D485033/CV](#) [PAQ65D485033/P](#) [PAQ65D485033/PV](#)
[PAQ65D485033/V](#) [PAQ65D482518/CV](#) [PAQ65D483325/C](#) [PAQ65D483318](#) [PAQ65D485033/C](#) [PAQ65D483325/CV](#)