


## Bulk Metal® Foil Technology Tubular Axial-Lead Resistors, Meets or Exceed MIL-R-39005 Requirements



### Any value and tolerance available within resistance range

This series of axial leaded resistors is made using the same foil technology as the S102C. The difference is axial versus radial leads. Axial leads have the advantage of readily available auto insertion equipment while the radial leaded devices may require additional tooling. Also, when converting from metal film (RNC 55) to foil (VMTA 55) boards may already be laid out for the axial leaded device. It is worth noting that for new designs the S102C footprint is the smallest in the industry (taking into account the need for lead exit to board pad length allowance).

Our Application Engineering Department is available to advise and to make recommendations. For non-standard technical requirements and special applications, please contact us.

**TABLE 1 - TCR** (for values under 50R)

| VALUES       | 0 °C to + 60 °C | - 55 to + 125 °C, + 25 °C Ref. |
|--------------|-----------------|--------------------------------|
| 25R - 50R    | ± 5 ppm/°C      | ± 8 ppm/°C                     |
| 15R - 24R999 | ± 6 ppm/°C      | ± 10 ppm/°C                    |
| 5R - 14R999  | ± 8 ppm/°C      | ± 12 ppm/°C                    |
| 1R - 4R999   | ± 15 ppm/°C     | ± 20 ppm/°C                    |


### FEATURES

- Temperature Coefficient of Resistance (TCR):  
± 8 ppm/°C (- 55 °C to + 125 °C, + 25 °C Ref.)  
± 4 ppm/°C (0 °C to + 60 °C)
- Tolerance: to ± 0.01 %
- Load Life Stability:  
± 0.05 % at 25 °C, 2000 hours at Rated Power  
± 0.0025 % at 25 °C, 2000 hours at Low Power
- Electrostatic Discharge (ESD) above 25 000 Volts
- Resistance Range: 5 Ω to 500 kΩ
- Power Rating: 0.2 W to 1.0 W at 70 °C
- Non-Inductive, Non-Capacitive Design
- Thermal EMF: 0.1 μV/°C maximum, 0.05 μV/°C typical
- Voltage Coefficient: < 0.1 ppm/V
- Terminal Finishes available: Lead (Pb)-free  
Tin/Lead
- For better performances, please contact Application Engineering
- Any value available within resistance range (e.g. 1K2345)
- Prototype samples available from 48 hours. For more information, please contact [foil@vishaypg.com](mailto:foil@vishaypg.com)



**RoHS\***  
COMPLIANT

**FIGURE 1 - POWER DERATING CURVE**



**TABLE 2 - MODEL SELECTION**


| VISHAY MODEL | MIL STYLE | POWER      |             | MAXIMUM WORKING VOLTAGE | RESISTANCE RANGE <sup>1)</sup> (Ω) | TIGHTEST TOLERANCE  | TCR RANGE <sup>2)</sup> |
|--------------|-----------|------------|-------------|-------------------------|------------------------------------|---------------------|-------------------------|
|              |           | at + 70 °C | at + 125 °C |                         |                                    |                     |                         |
| VTA56        | RBR56     | 0.25 W     | 0.125 W     | 300 V                   | 5 to 24R9<br>25 to 150K            | ± 0.1 %<br>± 0.01 % | V4<br>V3, V2            |
| VTA55        | RBR55     | 0.3 W      | 0.15 W      | 300 V                   | 5 to 24R9<br>25 to 150K            | ± 0.1 %<br>± 0.01 % | V4<br>V3, V2            |
| VTA54        | RBR54     | 0.5 W      | 0.25 W      | 300 V                   | 5 to 24R9<br>25 to 300K            | ± 0.1 %<br>± 0.01 % | V4<br>V3, V2            |
| VTA53        | RBR53     | 0.66 W     | 0.33 W      | 300 V                   | 5 to 24R9<br>25 to 300K            | ± 0.1 %<br>± 0.01 % | V4<br>V3, V2            |
| VTA52        | RBR52     | 1.0 W      | 0.5 W       | 300 V                   | 5 to 24R9<br>25 to 500K            | ± 0.1 %<br>± 0.01 % | V4<br>V3, V2            |
| VMTA55       | RNC55     | 0.2 W      | 0.1 W       | 200 V                   | 5 to 49R9<br>50 to 30K             | ± 0.1 %<br>± 0.01 % | V4<br>V3, V2            |
| VMTB60       | RNC60     | 0.25 W     | 0.125 W     | 250 V                   | 5 to 49R9<br>50 to 60K             | ± 0.1 %<br>± 0.01 % | V4<br>V3, V2            |

### Notes


1. For higher/lower resistance values, consult the Application Engineering Department
2. TCR options for values > 50 Ω  
V4 = ± 4 ppm/°C (0 to + 60 °C); ± 8 ppm/°C (- 55 °C to + 125 °C, + 25 °C Ref.)  
V3 = ± 3 ppm/°C (0 to + 60 °C); ± 5 ppm/°C (- 55 °C to + 125 °C, + 25 °C Ref.)  
V2 = ± 2 ppm/°C (0 to + 60 °C); ± 5 ppm/°C (- 55 °C to + 125 °C, + 25 °C Ref.)

\* Pb containing terminations are not RoHS compliant, exemptions may apply

**FIGURE 2 - VTA/VMTA SERIES STANDARD PRINTING**




**FIGURE 3 - TRIMMING TO VALUES**  
(Conceptual Illustration)



**TABLE 3 - VTA/VMTX DIMENSIONS**


| VISHAY<br>MODEL | MIL<br>SIZE | BODY              |                         |                  |                       |              |                         |      |                       | LEAD         |       |              |      |
|-----------------|-------------|-------------------|-------------------------|------------------|-----------------------|--------------|-------------------------|------|-----------------------|--------------|-------|--------------|------|
|                 |             | LENGTH (A)        |                         |                  |                       | DIAMETER (B) |                         |      |                       | LENGTH (C)   |       | DIAMETER (D) |      |
|                 |             | INCH              |                         | mm               |                       | INCH         |                         | mm   |                       | INCH         | mm    | INCH         | mm   |
| VTA56           | RBR56       | 0.356             | $\frac{+0.005}{-0.010}$ | 9.04             | $\frac{+0.13}{-0.25}$ | 0.260        | $\frac{+0.005}{-0.015}$ | 6.60 | $\frac{+0.13}{-0.38}$ | 1.5 Minimum  | 38.10 | 0.032        | 0.81 |
| VTA55           | RBR55       | $0.500 \pm 0.020$ |                         | $12.70 \pm 0.51$ |                       | 0.260        | $\frac{+0.005}{-0.010}$ | 6.60 | $\frac{+0.13}{-0.25}$ | 1.5 Minimum  | 38.10 | 0.032        | 0.81 |
| VTA54           | RBR54       | 0.750             | $\frac{+0.020}{-0.032}$ | 19.05            | $\frac{+0.51}{-0.81}$ | 0.260        | $\frac{+0.005}{-0.010}$ | 6.60 | $\frac{+0.13}{-0.25}$ | 1.5 Minimum  | 38.10 | 0.032        | 0.81 |
| VTA53           | RBR53       | $0.750 \pm 0.020$ |                         | $19.05 \pm 0.51$ |                       | 0.375        | $\pm 0.015$             | 9.53 | $\pm 0.38$            | 1.5 Minimum  | 38.10 | 0.032        | 0.81 |
| VTA52           | RBR52       | 1.000             | $\frac{+0.020}{-0.032}$ | 25.40            | $\frac{+0.51}{-0.81}$ | 0.375        | $\pm 0.015$             | 9.53 | $\pm 0.38$            | 1.35 Minimum | 34.29 | 0.032        | 0.81 |
| VMTA55          | RNC55       | $0.270 \pm 0.005$ |                         | $6.86 \pm 0.13$  |                       | 0.120        | $\frac{+0.005}{-0.010}$ | 3.05 | $\frac{+0.13}{-0.25}$ | 1.5 Minimum  | 38.10 | 0.025        | 0.64 |
| VMTB60          | RNC60       | $0.375 \pm 0.005$ |                         | $9.53 \pm 0.13$  |                       | 0.160        | $\pm 0.005$             | 4.06 | $\pm 0.13$            | 1.5 Minimum  | 38.10 | 0.025        | 0.64 |

**FIGURE 4 - TEMPERATURE COEFFICIENT OF RESISTANCE**



**TABLE 4 - GLOBAL PART NUMBER INFORMATION**

**NEW GLOBAL PART NUMBER: Y0058150K000Q19L (preferred part number format)**



FOR EXAMPLE: ABOVE GLOBAL ORDER Y0058 150K000 Q 19 L:

TYPE: VTA55

VALUE: 150.0 k $\Omega$

ABSOLUTE TOLERANCE:  $\pm 0.02\%$

TCR: V3

TERMINATION: Lead (Pb)-free

PACKAGING: Bulk

**HISTORICAL PART NUMBER: VTA55V3T 150K00 Q B (will continue to be used)**

| VTA55                                                         | V3             | T                                           | 150K00                    | Q                                                                                                                                     | B         |
|---------------------------------------------------------------|----------------|---------------------------------------------|---------------------------|---------------------------------------------------------------------------------------------------------------------------------------|-----------|
| MODEL                                                         | TCR            | TERMINATION                                 | OHMIC VALUE               | RESISTANCE TOLERANCE                                                                                                                  | PACKAGING |
| VTA52<br>VTA53<br>VTA54<br>VTA55<br>VTA56<br>VMTA55<br>VMTB60 | V4<br>V3<br>V2 | T = Lead (Pb)-free<br>None = Tin/Lead alloy | 150K00 = 150.0 k $\Omega$ | T = $\pm 0.01\%$<br>Q = $\pm 0.02\%$<br>A = $\pm 0.05\%$<br>B = $\pm 0.1\%$<br>C = $\pm 0.25\%$<br>D = $\pm 0.5\%$<br>F = $\pm 1.0\%$ | B = Bulk  |

**Note**

\* For non-standard requests, please contact Application Engineering.

## Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase.

**To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.**

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at [vpgsensors.com](http://vpgsensors.com).

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.