




**microLED<sup>®</sup> Optopipe<sup>™</sup>**

**Optical Light Pipe, Illuminated Corner**

**Dialight**

**515-1036**



## MicroLED SMT LEDs for use with 515-1036

<u>PART NO.</u>	<u>PAGE #</u>
<b>Recommended</b>	
597-3xx1-2xx	1-21
597-77x1-2xx	1-23 & 1-24

<b>Alternatives</b>	
597-3xxx-4xx	1-27 & 1-28
597-3xx1-4xx	1-28
597-3xx1-5xx	1-30
597-5004-4xx	1-26
597-5x11-4xx	1-27
597-5x12-4xx	1-26
597-5202-4xx	1-27
597-52x3-4xx	1-26
597-77x1-5xx	1-31

LED alternatives may not produce optimum light output

### Features

- High transmissivity polycarbonate material
- UL94V-0 compliance
- ESD protection (circuit isolation from front panel)
- Even illumination of both panel faces
- Secures to panel by ultrasonic welding

### LED Data

For absolute maximum ratings and other electrical and optical data on the recommended LEDs, refer to LED data sheets.

### Operating/Storage Temperature

–30°C to +100°C

### Dialight Optopipe Light Pipe Description

This Optopipe<sup>™</sup> is ultrasonically welded inside the customer's plastic housing. The light pipe is welded to case at the L-shaped tab at the front of the part. The light pipe is not attached to the PCB at any point but floats above it. The squared-off end sticks through the plastic panel. The surface is textured to diffuse the light passing through it. The multi-guided design insures even illumination of the two indicating surfaces. The light pipe material is water clear transmissive polycarbonate rated UL94-V0, and has a 35% oxygen index.

Dialight can provide custom Optopipe<sup>™</sup> solutions for your applications.