

IEC Appliance Inlet C14 or C18 with Filter, high attenuation, ECO design, Front- or Rear Side Mounting

Standard- or Medical-Filter



new



Description

- Panel Mount:
Screw-on version from front or rear side, snap-in version from front side, PCB Version from rear side
- 2 Functions:
Appliance Inlet protection class I or II, Line filter in standard and medical version
- Solder, quick connect or wire (stranded)
- PCB Mounting
- Earth Terminal

Approvals

- VDE Certificate Number: 40016382
- UL File Number: E72928

Characteristics

- Compact filter with high asymmetrical attenuation
- Optimal shielding due to completely closed filter case, unpotted
- Designed for standard and medical applications
- Suitable for assembly in metal plated plastic housings
- Suitable for use in equipment according to IEC/UL 60950
- Suitable for use in medical equipment according to IEC/UL 60601-1

Other versions on request

- Snap-in for panel thickness >2mm to 3mm
- flexible wire with various lengths
- Class X1- and Y1-capacitors for enhanced withstand voltage
- Variant with notch for V-Lock mating Cordsets

Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Accessories](#), [Wire Harnessing](#)


Newly available variants corresponding to V-Lock mating cordset. The connector is equipped with a notch intended for use with the latching cordset. The cord latching system prevents against accidental removal of the cordset.

Technical Data


Ratings IEC	1 - 10A @ Ta 40 °C / 250VAC; 50Hz
Ratings UL/CSA	1 - 15A @ Ta 40 °C / 250VAC; 60Hz
Leakage Current	standard < 0.5mA (250 V / 60Hz) medical < 5 µA (250 V / 60 Hz)
Dielectric Strength	> 1.7 kVDC between L-N > 2.7 kVDC between L/N-PE Test voltage (2 sec)
Allowable Operation Temp.	-25 °C to 85 °C
Climatic Category	25/085/21 acc. to IEC 60068-1
Degree of Protection	from front side IP 40 acc. to IEC 60529
Protection Class	Suitable for appliances with protection class I or II acc. to IEC 61140
Terminal	Quick connect terminals 6.3 x 0.8 mm Solder terminals Flexible wire AWG18 (15A AWG16), 150 mm
Panel Thickness s	Screw: max 8 mm Mounting screw torque max 0.5 Nm Snap-in: 0.8 mm to 2 mm (all steps with one variant)
Material: Housing	Thermoplast / steel tin-plated, black / metallic, UL 94V-0

Appliance-Inlet/-Outlet	C14 / C18 acc. to IEC 60320, UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 10A, Protection Class I or II
Line Filter	Standard and Medical Version, IEC 60939, UL 1283, CSA C22.2 no. 8 Technical Details
MTBF	> 3'000'000 h acc. to MIL-HB-217 F


PCB snap-in rear side mounting, protection class I




PCB rear side mounting, protection class I




PCB snap-in rear side mounting, protection class II



PCB rear side mounting, protection class II



Screw and snap-in mounting with flexible wire




- 1) Flexible wire, standard length 150 mm or special length on request
- 2) Nonexistent for protection class II
- 3) Panel cut-out screw-on version, back-side mounting
- 4) Panel cut-out screw-on version, front- or back-side mounting
- 5) Panel cut-out snap-in version, front-side mounting

Technical Data of Filter-Components


Rated Current [A]	Filter-Type	Inductances L [mH]	Capacitance CX [nF]	Capacitance CY [nF]	R [MΩ]
1	Standard Version	2 x 20	100	2.2	-
2	Standard Version	2 x 9	100	2.2	-
4	Standard Version	2 x 3.4	100	2.2	-
6	Standard Version	2 x 1.6	100	2.2	-
10	Standard Version	2 x 0.65	100	2.2	-
15	Standard Version	2 x 0.2	100	2.2	-
1	Medical Version (M5)	2 x 20	100	-	1
2	Medical Version (M5)	2 x 9	100	-	1
4	Medical Version (M5)	2 x 3.4	100	-	1
6	Medical Version (M5)	2 x 1.6	100	-	1
10	Medical Version (M5)	2 x 0.65	100	-	1
15	Medical Version (M5)	2 x 0.2	100	-	1
6	Medical Version (M80)	2 x 1.6	100	0.47	1
1	Medical (M5)	2 x 20	100	-	1
2	Medical (M5)	2 x 9	100	-	1
4	Medical (M5)	2 x 3.4	100	-	1
6	Medical (M5)	2 x 1.6	100	-	1
10	Medical (M5)	2 x 0.65	100	-	1
15	Medical (M5)	2 x 0.2	100	-	1

Diagrams


Standard version




Bleed resistor version



Medical version M5



Medical version M5, prot. class II




Attenuation Loss


Standard version

--- differential mode ____ common mode


1 A




2 A




3 A




4 A




6 A




8 A



10 A




15 A




Medical version (M5)


1 A




2 A




3 A




4 A




6 A




8 A



10 A




15 A




Medical version (M80)


1 A




2 A




3 A




4 A




6 A




8 A



10 A



15 A



All Variants

Rated Current [A]	Filter-Type	Mounting	Mounting side	Terminal	Protection Class	Order Number
1	Standard Version	Snap-in	Front Side	Quick connect	I	5123.2000.0
1	Standard Version	Snap-in	Front Side	Quick connect	I	5123.2000.0.21
2	Standard Version	Snap-in	Front Side	Quick connect	I	5123.2001.0
4	Standard Version	Snap-in	Front Side	Quick connect	I	5123.2003.0
6	Standard Version	Snap-in	Front Side	Quick connect	I	5123.2004.0
10	Standard Version	Snap-in	Front Side	Quick connect	I	5123.2006.0
15	Standard Version	Snap-in	Front Side	Quick connect	I	5123.2007.0
6	Standard Version	Screw/PCB	Rear Side	PCB pin and earth	I	5123.4074.0
1	Standard Version	Screw	Rear Side	Quick connect	I	5123.1000.0.21
2	Standard Version	Screw	Rear Side	Quick connect	I	5123.1001.0.21
4	Standard Version	Screw	Rear Side	Quick connect	I	5123.1003.0.21
6	Standard Version	Screw	Rear Side	Quick connect	I	5123.1004.0.21
10	Standard Version	Screw	Rear Side	Quick connect	I	5123.1006.0.21
10	Standard Version	Screw	Rear Side	Flexible wire con-	I	5123.1046.0
15	Standard Version	Screw	Rear Side	Quick connect	I	5123.1007.0.21
1	Standard Version	Screw	Front-/Rear-Side	Quick connect	I	5123.0000.0
2	Standard Version	Screw	Front-/Rear-Side	Quick connect	I	5123.0001.0

Rated Current [A]	Filter-Type	Mounting	Mounting side	Terminal	Protection Class	Order Number
4	Standard Version	Screw	Front-/Rear-Side	Quick connect	I	5123.0003.0
4	Standard Version	Screw	Front-/Rear-Side	Flexible wire	I	5123.0233.0
6	Standard Version	Screw	Front-/Rear-Side	Quick connect	I	5123.0004.0
10	Standard Version	Screw	Front-/Rear-Side	Quick connect	I	5123.0006.0
15	Standard Version	Screw	Front-/Rear-Side	Quick connect	I	5123.0007.0
1	Medical Version (M5)	Screw	Rear Side	Quick connect	I	5123.1300.0.21
2	Medical Version (M5)	Screw	Rear Side	Quick connect	I	5123.1301.0.21
4	Medical Version (M5)	Screw	Rear Side	Quick connect	I	5123.1303.0.21
6	Medical Version (M5)	Screw	Rear Side	Quick connect	I	5123.1304.0.21
10	Medical Version (M5)	Screw	Rear Side	Quick connect	I	5123.1306.0.21
15	Medical Version (M5)	Screw	Rear Side	Quick connect	I	5123.1307.0.21
1	Medical Version (M5)	Screw	Front-/Rear-Side	Quick connect	I	5123.0300.0
2	Medical Version (M5)	Screw	Front-/Rear-Side	Quick connect	I	5123.0301.0
4	Medical Version (M5)	Screw	Front-/Rear-Side	Quick connect	I	5123.0303.0
6	Medical Version (M5)	Screw	Front-/Rear-Side	Quick connect	I	5123.0304.0
10	Medical Version (M5)	Screw	Front-/Rear-Side	Quick connect	I	5123.0306.0
15	Medical Version (M5)	Screw	Front-/Rear-Side	Quick connect	I	5123.0307.0
6	Medical Version (M80)	Screw	Front-/Rear-Side	Quick connect	I	5123.0504.0
1	Medical (M5)	Snap-in	Front Side	Quick connect	I	5123.2300.0
2	Medical (M5)	Snap-in	Front Side	Quick connect	I	5123.2301.0
4	Medical (M5)	Snap-in	Front Side	Quick connect	I	5123.2303.0
6	Medical (M5)	Snap-in	Front Side	Quick connect	I	5123.2304.0
10	Medical (M5)	Snap-in	Front Side	Quick connect	I	5123.2306.0
15	Medical (M5)	Snap-in	Front Side	Quick connect	I	5123.2307.0

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

- 15 A version only according UL/CSA

- Type for screw-on mounting from rear side has pre-threaded holes for M3 screws

Suffix ".21" corresponds to the version with V-Lock mating cordset. The connector is equipped with a notch intended for use with the latching cordset. The cord latching system prevents against accidental removal of the cordset.


Packaging unit 10 Pcs

Accessories

Description



Wire Harness
Wire harness for SCHURTER products



Assorted Covers
Rear Cover



[Cord retaining kits](#)
Cord retaining strain relief

Mating Outlets/Connectors

Category / Description



[Appliance Outlet Overview complete](#)

IEC Appliance Outlet F, Screw-on Mounting, Front Side, Solder Terminal	4787
IEC Appliance Outlet F, Snap-in Mounting, Front Side, Solder or Quick-connect Terminal	4788
IEC Appliance Outlet F or H, Screw-on Mounting, Front Side, Solder, PCB or Quick-connect Terminal	5091

[Appliance Outlet further types to 5123](#)



[Connector Overview complete](#)

IEC Connector C13, Rewireable, Straight	4782
IEC Connector C13, Rewireable, Straight	4022
IEC Connector C13, Rewireable, Angled	4785
IEC Connector C13, Rewireable, Angled	4300-06
IEC Connector C13, Rewireable, Angled	4012

[Connector further types to 5123](#)

Mating Outlets/Connectors shuttered



[Power Cord Overview complete](#)

Overview Power Supply Cord with IEC Connector C13, V-Lock, straight	VAC13KS
---	---------

[Power Cord further types to 5123](#)