

SPECIFICATIONS

Material: HEXSEALS: Silicone rubber conforms to A-A-59588 Class III, GR 50 (unless otherwise specified)

Mounting Nut: HEXSEALS: Brass, nickel-plated

Temperature Range: HEXSEALS: -94°F to +400°F

Pressure Range: Exceeds 15 psi internal and 1500 psi external.


Operational Life: 30,000 actuations (minimum).

Shelf Life: Excess of 25 years.

Resistant to: Salt spray, sunlight, ozone, weather, fungus, and most acids and lubricating oils

Agency Recognition: E-SEELS and HEXSEALS are UL-listed to UL Std. 50 types 1-13, and meet CSA standards.

Installation: If a reducing adaptor is required - see page 14 of HEXSEAL catalog HEX200 for part numbers and drawing.



O	REDRAWN and MAT'L CHANGED			S.GOK	05-15-09		
N	CAD COMPUTER GENERATED				9-23-02		
M	MAT'L. NUT WAS ALUMINUM			NICK	8-27-69		
L	ALUM. SPEC. WAS QQ-A22-15A			NICK	8-9-69		
K	REDRAWN, ADDED SPECS, CORRECT BOOT AND ADAPTER P/N CALLOUT			NICK	1-13-67		
REV.	DESCRIPTION				DATE		
MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON EACH DIMENSION.		TITLE:	BOOT, INDICATOR AND LIGHTED PUSHBUTTON (4086)		ENG.	M.M.	12-15-59
					DWN.	ANDREWS	12-15-59
					CHKD.	B.G.	12-15-59
MAT'L: SILICONE RUBBER A-A-59588 CLIII GR50			APM-HEXSEAL CORPORATION		SCALE 2 : 1	DWG. NO. (4086) HEXSEAL ®	
FINISH: TRANSPARENT CLEAR							

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.
THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE WRITTEN APPROVAL OF AN OFFICER OF THE APM-HEXSEAL CORPORATION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[APM HEXSEAL:](#)

[4086](#)