



DESCRIPTION: 0.085 RIBBON - SOLDER CUP

	014	024	036	050
A	1.728	2.154	2.667	3.264
	43.90	54.70	67.75	82.90
B	0.992	1.417	1.925	2.624
	25.20	36.00	48.90	64.10
C	1.417	1.843	2.352	2.947
	36.00	46.80	59.74	74.85



WILL ACCEPT 26-20 AWG WIRE

## MATERIAL:

INSULATION: PBT - UL 94V-0 RATED  
CONTACTS: PHOSPHOR BRONZE  
SHELL: STEEL, NICKEL PLATED

## ELECTRICAL:

CURRENT RATING: 1 AMPS  
VOLTAGE RATING: 1,000V AC r.m.s.  
INSULATION RESISTANCE: 1,000MegOhms Min. @ 500VDC  
CONTACT RESISTANCE: 30MilliOhms Max.  
OPERATING TEMPERATURE: -55°C TO +125°C

111-YYY-203L001

SERIES POSITIONS  
014  
024  
036  
050  
GENDER  
2 = FEMALE  
TERMINATION  
0 = SOLDER CUP  
SHELL PLATING  
3 = NICKEL  
RoHS COMPLIANT  
L = LOW TEMP. PROCESS  
HARDWARE  
00 = NO HARDWARE  
PLATING  
1 = GOLD FLASH

DO NOT SCALE FROM DRAWING




THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OF SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: WAYNE ROBBINS	DATE: 09-15-05
CHECKED:	DATE:
SCALE: NONE	SHEET OF 1 2
REV 7	
DWG NO. 111-YYY-203L001	


NorComp

RoHS COMPLIANT


	014	024	036	050
C	1.417	1.843	2.352	2.947
	36.00	46.80	59.74	74.85




14 POSITION



36 POSITION



24 POSITION



50 POSITION

\*\*\*NOTE\*\*\*DIMENSION "C" =  
CENTER TO CENTER OF MOUNTING HOLES  
CENTER OF RADII  
OVERALL LENGTH OF CUTOUT

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OF SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
M. SIGMON

DATE:  
01-14-11

CHECKED:

DATE:

SCALE:  
NONE

DWG. NO.

SHEET  
2  
OF  
2

REV  
7

111-YYY-203L001

# NorComp

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

[111-014-203L001](#) [111-024-203L001](#) [111-036-203L001](#) [111-050-203L001](#)