


PAC

UL 1213 Cable (30 AWG) Specification

7/0.10 SPC		Part No.:P1213A30100	
Cross Section		Performance	
 Conductor Jacket		Electrical Characteristics: Spark Test: AC-1.5KV Dielectric Strength : AC-500V/60sec Conductor Resistance: 385 OHM/KM At 20°C Insulation Resistance: DC-500V 10 Mohm/KM At 20°C	
Packing			
100M/reel			
Description			
Rated Temperature (°C)	-60~105		
Rated Voltage(V)	300		
Product Standard Certification	UL AWM Styles1213		
Flammability Test	FT1		
UL file Number	E300956		
Construction			
Conductor	Silvery plated copper		
AWG	30		
Conductor Dia. (±0.005mm)	7/0.10		
Jacket	PTFE		
Average Thickness(mm)	0.25	Mechanical Characteristics: Test ObjectJacket Test MaterialPTFE BeforeTensile Strength (kgf/mm²)>=0.5 AgingElongation (%)>=100 Aging Condition () AfterTensile Strength (%)>=60 AgingElongation (%)>=60	
Outer Dia.(±0.05mm)	0.81		
Color			
As request			
Marking			
No			
Revision History			