


1-1825142-6 Product Details

 Share Print Email



Toggle Switches
☐ Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- AE Series
- Single Pole - Double Throw Configuration (Pole-Throw)
- Current Rating = 5 A
- Mount Style = Through-Hole
- Termination Type = Right Angle

[View all Features](#)

[Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#) [Buy Product](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information	
Product Drawings: • GEMINI AE SERIES TOGGLE SWITCH, SINGLE POLE (PDF, English) Catalog Pages/Data Sheets: • SWITCHES_CORE_PROGRAM_CATALOG (PDF, English) • GEMINI_SERIES_SWITCHES_QUICK_REF_GUIDE_2-1773458-5 (PDF, English) Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: • None Available	Additional Information: • Product Line Information Additional Product Images: • Product Photo • Dimensional Drawing Related Products: • Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Series = AE • Configuration (Pole-Throw) = Single Pole - Double Throw • Termination Type = Right Angle Electrical Characteristics: • Current Rating (A) = 5 Termination Features: • Seal Type = Terminal Seal (epoxy) Body Features: • Mount Style = Through-Hole Contact Features: • Contact Plating = Silver Housing Features: • Toggle Actuation = Horizontal • Toggle Style = Baton Long • Toggle Length (mm [in]) = 12.70 [0.500] • Process Sealed = Yes • Bushing Style = Unthreaded • Bushing Type = Plain • UL Flammability Rating = UL 94V-0	Configuration Features: • Operating Function = On On Industry Standards: • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C • RoHS/ELV Compliance History = Always was RoHS compliant • UL Rating = Contact Only Other: • Brand = Alcoswitch • Comment = Process seal meets MIL-STD-202, Method 112 test cond. A & D at 85°C.