








[illegible]

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



SECTION A-A

PART 8-5530843-6

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AWF/GRZYBOWSKI	30OCT2009	 TE Connectivity	
DIMENSIONS: INCHES		CHK E.HOWARD	-		
		APVD M.PERCHEK	30OCT2009	NAME CONNECTOR ASSEMBLY STANDARD EDGE II, .100 CENTERLINE	
		PRODUCT SPEC			
		108-9039			
		APPLICATION SPEC			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		114-13018		SIZE A100779	
0 PLC ±"		WEIGHT			
1 PLC ±.005		CUSTOMER DRAWING		SCALE 4:1	
2 PLC ±"					
3 PLC ±"				SHEET 2 OF 4	
4 PLC ±"					
ANGLES #2				REV F4	
FINISH					


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

OBSOLETE	8-5530843-2
OBSOLETE	8-5530843-1
OBSOLETE	4-5530843-1
OBSOLETE	1-5530843-9
OBSOLETE	1-5530843-2
	PART NUMBER

⚠	OBSOLETE	F4	3,4,5,6,9,10,13,14,17,18,19,20, 21,22	-	⚠ ₆	1.286	.125	1.100	1.300	1.350	1.460	11	12	8-5530843-9
			11,12,23,24,29,30,35,36,37,38	-	⚠ ₆	2.086	.125	1.900	2.100	2.150	2.260	19	20	8-5530843-8
			17,18,19,20	-	⚠ ₆	1.286	.125	1.100	1.300	1.350	1.460	11	12	8-5530843-7
					⚠ ₆	0.686	-	.500	.700	-	-	5	6	8-5530843-6
					⚠ ₆	1.286	.187	1.100	1.300	1.350	1.460	11	12	8-5530843-5
			19,20,21,22,23,24,27,28,31,32,35,36,39 40,43,44,45,46,47,48,51,52,55,56,59,60	-	⚠ ₆	3.186	.125	3.000	3.200	3.250	3.360	30	31	8-5530843-4
				3,4,5,6,19,20,21,22	⚠ ₆	1.286	.125	1.100	1.300	1.350	1.460	11	12	8-5530843-3
				-	⚠ ₆	.386	.125	.200	.400	.450	.560	2	3	7-5530843-7
				-	⚠ ₆	.686	.187	.500	.700	.750	.860	5	6	7-5530843-6
				-	⚠ ₆	.686	.125	.500	.700	.750	.860	5	6	7-5530843-5
				-	⚠ ₅	3.186	.125	3.000	3.200	3.250	3.360	30	31	7-5530843-0
				-	⚠ ₆	3.186	.125	3.000	3.200	3.250	3.360	30	31	6-5530843-5
				-	⚠ ₆	6.086	.125	5.900	6.100	6.150	6.260	59	60	5-5530843-5
				-	⚠ ₆	2.086	.125	1.900	2.100	2.150	2.260	19	20	5-5530843-4
				-	⚠ ₆	1.786	.125	1.600	1.800	1.850	1.960	16	17	5-5530843-3
				-	⚠ ₆	1.086	.125	.900	1.100	1.150	1.260	9	10	5-5530843-0
				-	⚠ ₅	1.886	.125	1.700	1.900	1.950	2.060	17	18	2-5530843-7
				-	⚠ ₆	3.586	.125	3.400	3.600	3.650	3.760	34	35	2-5530843-3
				-	⚠ ₆	5.086	.187	4.900	5.100	5.150	5.260	49	50	2-5530843-2
				-	⚠ ₆	4.086	.187	3.900	4.100	4.150	4.260	39	40	2-5530843-0
				-	⚠ ₆	3.086	.187	2.900	3.100	3.150	3.260	29	30	1-5530843-8
				-	⚠ ₆	2.586	.187	2.400	2.600	2.650	2.760	24	25	1-5530843-6
				-	⚠ ₆	4.386	.125	4.200	4.400	4.450	4.560	42	43	1-5530843-0
				-	⚠ ₆	3.686	.125	3.500	3.700	3.750	3.860	35	36	5530843-8
				-	⚠ ₆	3.086	.125	2.900	3.100	3.150	3.260	29	30	5530843-7
				-	⚠ ₆	2.886	.125	2.700	2.900	2.950	3.060	27	28	5530843-6
				-	⚠ ₆	2.586	.125	2.400	2.600	2.650	2.760	24	25	5530843-5
				-	⚠ ₆	2.286	.125	2.100	2.300	2.350	2.460	21	22	5530843-4
				-	⚠ ₆	1.886	.125	1.700	1.900	1.950	2.060	17	18	5530843-3
				-	⚠ ₆	1.586	.125	1.400	1.600	1.650	1.760	14	15	5530843-2
				-	⚠ ₆	1.286	.125	1.100	1.300	1.350	1.460	11	12	5530843-1
			OMITTED PIN	BOARD RETENTION FEATURE LOCATION (SEE DETAIL Y)	FINISH	Z	J	D	C	B	A	X	NO. OF DUAL POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES



MATERIAL
-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±.005
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH #2

-
-

DWN
JAW/GRZYBOWSKI

CHK
E.HOWARD

APVD
M.PERCHEK

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

30OCT2009

30OCT2009

108-9039

114-13018

100779

4:1

3

4

F4

TE Connectivity



CONNECTOR ASSEMBLY
STANDARD EDGE 11,
.100 CENTERLINE

SIZE
A1

CAGE CODE
C=5530843

RESTRICTED TO
-

REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AWF/GRZYBOWSKI	30OCT2009	 TE Connectivity	
DIMENSIONS: INCHES		CHK E.HOWARD	-		
		APVD M.PERCHEK	30OCT2009	NAME CONNECTOR ASSEMBLY STANDARD EDGE II, .100 CENTERLINE	
		PRODUCT SPEC			
		108-9039			
		APPLICATION SPEC			
MATERIAL -		WEIGHT -		SIZE A100779C=5530843	
FINISH -		CUSTOMER DRAWING			
		SCALE 4:1		SHEET 4 OF 4	
				REV F4	