


Silicon Bridge Rectifier



Features:

- Rating to 1,000V PRV
- Surge Overload Rating to 200A Peak
- Ideal for Printed Circuit Board
- Reliable Low Cost Construction Utilizing Moulded Plastic Technique Results in Inexpensive Product
- Lead Solderable per MIL-STD-202 Method 208
- Glass Passivated Junctions

Maximum Ratings and Electrical Characteristics:

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate by 20%.

Characteristics	Symbol	GBU810	Units
Maximum recurrent peak reverse voltage	V_{RRM}	1,000	V
Maximum RMS voltage	V_{RMS}	700	V
Maximum DC blocking voltage	V_{DC}	1,000	V
Maximum average forward output current at $T_C=100^{\circ}C$	$I_{F(AV)}$	8	A
Peak forward surge current 8.3ms single half-sine-wave Super imposed on rated load	I_{FSM}	200	A
Maximum instantaneous forward voltage at 4A	V_F	1	V
Maximum reverse current at $T_A = 25^{\circ}C$ At rated DC blocking voltage at $T_A = 100^{\circ}C$	I_R	10 1	μA mA
Storage and Operating junction temperature range	T_J, T_{STG}	-50 to +150	$^{\circ}C$

Silicon Bridge Rectifier



FIG.5 – TYPICAL JUNCTION CAPACITANCE PER ELEMENT




FIG.1 – TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2 – MAXIMUM FORWARD SURGE CURRENT




FIG.3 – TYPICAL FORWARD CHARACTERISTIC






FIG.4 – TYPICAL REVERSE CHARACTERISTIC



Package Outline Dimensions:



GBU		
Dim	Min	Max
A	22	22.4
B	18.4	18.8
C	3.4	3.95
C1	2.5	3
E	0.4	0.6
F	17 min	
F1	1.7	2.3
I1	2.3	2.6
I2	0.95	1.25
K	4.7	5.3
P	1.9 Typical	
All Dimensions in mm		

Package Information

Device	Package	Shipping
GBU810	GBU	500 Units/Box

Part Number Table

Description	Part Number
Silicon Bridge Rectifier	GBU810

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.