



CASE FINISH	CURRENT (AMPS)	WORKING VOLTAGE				MAXIMUM DC RESISTANCE (OHMS)	MAXIMUM VOLTAGE DROP		MINIMUM CAPACITANCE (uF)	MIN. INSERTION LOSS PER MIL-STD-220 FULL LOAD, +25°C												
		-55°C TO +85°C		-55°C TO +125°C			DC	AC		14	30	50	75	100	150	300	500	1	100	1	10	
		AC	DC	AC	DC					KHz	KHz	KHz	KHz	KHz	KHz	KHz	MHz	MHz	MHz	GHz	GHz	
SOLDER	10.0	--	--	35	50	0.01	--	--	--	--	15	--	--	--	28	33	--	44	60	--	--	--

PART MARKING:
SCI
9200-303-0095
DATE CODE

PACKAGE MARKING:

STANDARD

MARKING NOTES:
N/A



MTG. HARDWARE

NOTES:
1) MOUNTING TORQUE NOT TO EXCEED 7in-lbs.

										10	9	REV.	UNLESS OTHERWISE SPECIFIED	TOLERANCES UNLESS OTHERWISE SPECIFIED	ERIE, FAIRVIEW PENNSYLVANIA
										CN 188947	CN 183685	CHANGE NOTICE NO.	Dimensions	Dec. .xx±	SPECTRUM CONTROL INC.
													IN INCHES. [MILLIMETERS]	Dec. .xxx±010	Dwn MAYNARD
													DO NOT SCALE.	Angles ±0° 30'	Ckd 2/27/98
														CODE IDENT. NO. DLSP2	Sheet 1 of 1
															Description Pass EMI Filter
															9200-303-0095

Quality Products From The Specialists In Electro-Magnetic Compatibility