

Plug-In RF Transformer

50Ω 0.01 to 150 MHz

T1-6-X65+
T1-6-X65




Maximum Ratings

Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	250mW
DC Current	30mA

Pin Connections

PRIMARY DOT	4
PRIMARY	6
SECONDARY DOT	3
SECONDARY	1
SECONDARY CT	—
NOT USED	2,5

Outline Drawing




Outline Dimensions (inch)

A	B	C	D	E	F	G
.30	.27	.23	.010	.042	.020	.100
7.62	6.86	5.84	0.25	1.07	0.51	2.54

H	J	K	L	M	wt
.05	.04	.11	.300	.35	grams
1.27	1.02	2.79	7.62	8.89	0.50

Config. C



Features

- good return loss
- also available with flat-pack (W38) and surface mount gull-wing (KK81) leads

Applications

- HF/VHF
- receivers/transmitters

CASE STYLE: X65

PRICE: \$5.65 ea. QTY (1-9)

+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

Transformer Electrical Specifications

Ω RATIO	FREQUENCY (MHz)	INSERTION LOSS*		
		3 dB MHz	2 dB MHz	1 dB MHz
1	0.01-150	0.01-150	0.02-100	0.05-50

* Insertion Loss is referenced to mid-band loss, 0.15 dB typ.

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)
0.01	1.53	3.51
0.02	0.58	7.36
0.05	0.18	14.35
0.10	0.13	20.32
0.20	0.13	26.00
50.00	0.54	9.38
76.89	0.97	6.19
100.00	1.37	4.61
143.59	2.26	2.79
150.00	2.43	2.57

T1-6-X65
INSERTION LOSS

