





OSSM
JACK

.190-36, UNS-2A
TYP

.250 HEX
6.4

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₁	REDRAWN ON CAD ECN 94-0474 <i>PRB</i>	1/17/95	<i>PRB</i> 1/17/95



RECOMMENDED
MOUNTING HOLE

HOUSING MOUNTING NUT LOCKWASHER		STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303		GOLD PLATE PER MIL-G-45204	
DIELECTRIC		TFE FLUOROCARBON PER ASTM-D-1457		N/A	
CENTER CONTACT		BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H		GOLD PLATE PER MIL-G-45204	
COMPONENT		MATERIAL		FINISH	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°		DRAWN BY	EJC	DATE	7/24/68
		CHECKED BY	PRB	DATE	7/24/68
		APPD BY	EJD	DATE	8/12/68
These drawings and speci- fications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale o f item(s) without written permission.		USE ASSY PROCEDURE N/A NO. A.P. _____		AMP AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	
		TITLE		OSSM BULKHEAD FEEDTHRU JACK RECEPTACLE-SOLDER TERMINAL	
		SIZE	CODE IDENT NO.	1058-0000-00	REV 01 ₁
		B	26805		
		SCALE	10/1	SHEET 1 OF 1	

NOTES:

1. CAPTURED CENTER CONTACT

.XXX = in
XX.X = mm

COPY IN PUERTO RICO

CUSTOMER DRAWING

AMP PART # 1045636-1
SHEET 1 OF 1 REV A