

**HIGH EFFICIENCY GLASS PASSIVATED RECTIFIER**

**VOLTAGE RANGE 50 to 1000 Volts CURRENT 2.0 Ampere**

**FEATURES**

- \* Low power loss, high efficiency
- \* Low leakage
- \* Low forward voltage drop
- \* High current capability
- \* High speed switching
- \* High surge capability
- \* High reliability

**MECHANICAL DATA**


- \* Case: Molded plastic
- \* Epoxy: UL 94V-O rate flame retardant
- \* Lead: MIL-STD-202E method 208C guaranteed
- \* Mounting position: Any
- \* Weight: 0.4 gram

**MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS**

Ratings at 25 °C ambient temperature unless otherwise specified.  
Single phase, half wave, 60 Hz, resistive or inductive load.  
For capacitive load, derate current by 20%.



**DO-15**



Dimensions in inches and (millimeters)

**MAXIMUM RATINGS** (At TA = 25°C unless otherwise noted)

| RATINGS                                                                                              | SYMBOL   | HER201G      | HER202G | HER203G | HER204G | HER205G | HER206G | HER207G | HER208G | UNITS |    |
|------------------------------------------------------------------------------------------------------|----------|--------------|---------|---------|---------|---------|---------|---------|---------|-------|----|
| Maximum Recurrent Peak Reverse Voltage                                                               | VRRM     | 50           | 100     | 200     | 300     | 400     | 600     | 800     | 1000    | Volts |    |
| Maximum RMS Voltage                                                                                  | VRMS     | 35           | 70      | 140     | 210     | 280     | 420     | 560     | 700     | Volts |    |
| Maximum DC Blocking Voltage                                                                          | VDC      | 50           | 100     | 200     | 300     | 400     | 600     | 800     | 1000    | Volts |    |
| Maximum Average Forward Rectified Current<br>at TA= 50°C                                             | IO       | 2.0          |         |         |         |         |         |         |         | Amps  |    |
| Peak Forward Surge Current 8.3 ms single half sine-wave<br>superimposed on rated load (JEDEC method) | IFSM     | 60           |         |         |         |         |         |         |         | Amps  |    |
| Typical Junction Capacitance (Note 2)                                                                | CJ       | 30           |         |         |         |         | 20      |         |         | pF    |    |
| Operating and Storage Temperature Range                                                              | TJ, TSTG | -55 to + 150 |         |         |         |         |         |         |         |       | °C |

**ELECTRICAL CHARACTERISTICS** (At TA = 25°C unless otherwise noted)


| CHARACTERISTICS                                                                                             | SYMBOL         | HER201G | HER202G | HER203G | HER204G | HER205G | HER206G | HER207G | HER208G | UNITS |
|-------------------------------------------------------------------------------------------------------------|----------------|---------|---------|---------|---------|---------|---------|---------|---------|-------|
| Maximum Instantaneous Forward Voltage at 2.0A DC                                                            | V <sub>F</sub> | 1.0     |         |         | 1.3     |         | 1.7     |         |         | Volts |
| Maximum DC Reverse Current<br>at Rated DC Blocking Voltage T <sub>A</sub> = 25°C                            | I <sub>R</sub> | 5.0     |         |         |         |         |         |         |         | uAmps |
| Maximum Full Load Reverse Current<br>Average, Full Cycle .375" (9.5mm) lead length at T <sub>L</sub> = 55°C |                | 100     |         |         |         |         |         |         |         | uAmps |
| Maximum Reverse Recovery Time (Note 1)                                                                      | trr            | 50      |         |         |         |         | 75      |         |         | nSec  |

NOTES : 1. Test Conditions: IF = 0.5A, IR = -1.0A, IRR = -0.25A

2. Measured at 1 MHz and applied reverse voltage of 4.0 volts

# RATING AND CHARACTERISTIC CURVES ( HER201G THRU HER208G )

FIG. 1 - TEST CIRCUIT DIAGRAM AND REVERSE RECOVERY TIME CHARACTERISTIC



NOTES: 1. Rise Time = 7ns max. Input Impedance = 1 megohm, 22pF.  
2. Rise Time = 10ns max. Source Impedance = 50 ohms.




FIG. 2 - TYPICAL FORWARD CURRENT DERATING CURVE




FIG. 3 - TYPICAL REVERSE CHARACTERISTICS




FIG. 4 - TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG. 5 - MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT





FIG. 6 - TYPICAL JUNCTION CAPACITANCE



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rectron:](#)

[HER204-B](#) [HER206-B](#) [HER208-B](#) [HER201G-B](#) [HER201G-T](#) [HER208G-B](#) [HER208G-T](#) [HER207-T](#) [HER207-B](#)  
[HER205-B](#) [HER205-T](#) [HER204G-T](#) [HER204G-B](#) [HER206G-B](#) [HER206G-T](#) [HER205G-B](#) [HER205G-T](#) [HER203G-T](#)  
[HER203G-B](#) [HER207G-T](#) [HER207G-B](#) [HER202G-T](#) [HER202G-B](#) [HER206-T](#) [HER202-B](#) [HER202-T](#) [HER208-T](#)  
[HER203-B](#) [HER203-T](#) [HER201G](#) [HER202G](#) [HER203G](#) [HER204G](#) [HER205G](#) [HER206G](#) [HER207G](#) [HER208G](#)