

Type M15 to M50 Multilayer Ceramic Capacitors

COG (NPO). X7R & Z5U Capacitors



Type M15 to M50 conformally coated radial leaded capacitors cover a wide range of temperature coefficients for a wide variety of applications.

Highlights

- Conformally coated, radial leaded
- Coating meets UL94V-0
- IECQ approved to:
QC300601/US0002 - NPO
QC300701/US0002 - X7R
QC300701/US0004 - Z5U

Specifications

Capacitance Range	1 pF to 6.8 μ F
Capacitance Tolerance	See ratings tables
Rated Voltage	50, 100, 200 Vdc
Temperature Coefficient	COG (NPO), X7R & Z5U
Available in Tape and Ammo Pack Configuration	Add 'TA' to end of catalog part number
RoHS Compliant	

Ratings

COG (NPO) Temperature Coefficient 200 Vdc																				
Catalog		Sizes (Inches)					Catalog		Sizes (Inches)					Catalog		Sizes (Inches)				
Part Number	Cap	L	H	T	S	Part Number	Cap	L	H	T	S	Part Number	Cap	L	H	T	S			
M15G109D2-F	1.0 pF	.150	.210	.130	.100	M15G120*2-F	12 pF	.150	.210	.130	.100	M15G101*2-F	100 pF	.150	.210	.130	.100			
M20G109D2-F	1.0 pF	.200	.260	.150	.100	M20G120*2-F	12 pF	.200	.260	.150	.100	M20G101*2-F	100 pF	.200	.260	.150	.100			
M22G109D2-F	1.0 pF	.200	.260	.150	.200	M22G120*2-F	12 pF	.200	.260	.150	.200	M22G101*2-F	100 pF	.200	.260	.150	.200			
M15G159D2-F	1.5 pF	.150	.210	.130	.100	M15G150*2-F	15 pF	.150	.210	.130	.100	M15G121*2-F	120 pF	.150	.210	.130	.100			
M20G159D2-F	1.5 pF	.200	.260	.150	.100	M20G150*2-F	15 pF	.200	.260	.150	.100	M20G121*2-F	120 pF	.200	.260	.150	.100			
M22G159D2-F	1.5 pF	.200	.260	.150	.200	M22G150*2-F	15 pF	.200	.260	.150	.200	M22G121*2-F	120 pF	.200	.260	.150	.200			
M15G229D2-F	2.2 pF	.150	.210	.130	.100	M15G180*2-F	18 pF	.150	.210	.130	.100	M15G151*2-F	150 pF	.150	.210	.130	.100			
M20G229D2-F	2.2 pF	.200	.260	.150	.100	M20G180*2-F	18 pF	.200	.260	.150	.100	M20G151*2-F	150 pF	.200	.260	.150	.100			
M22G229D2-F	2.2 pF	.200	.260	.150	.200	M22G180*2-F	18 pF	.200	.260	.150	.200	M22G151*2-F	150 pF	.200	.260	.150	.200			
M15G279D2-F	2.7 pF	.150	.210	.130	.100	M15G220*2-F	22 pF	.150	.210	.130	.100	M15G181*2-F	180 pF	.150	.210	.130	.100			
M20G279D2-F	2.7 pF	.200	.260	.150	.100	M20G220*2-F	22 pF	.200	.260	.150	.100	M20G181*2-F	180 pF	.200	.260	.150	.100			
M22G279D2-F	2.7 pF	.200	.260	.150	.200	M22G220*2-F	22 pF	.200	.260	.150	.200	M22G181*2-F	180 pF	.200	.260	.150	.200			
M15G339D2-F	3.3 pF	.150	.210	.130	.100	M15G270*2-F	27 pF	.150	.210	.130	.100	M15G221*2-F	220 pF	.150	.210	.130	.100			
M20G339D2-F	3.3 pF	.200	.260	.150	.100	M20G270*2-F	27 pF	.200	.260	.150	.100	M20G221*2-F	220 pF	.200	.260	.150	.100			
M22G339D2-F	3.3 pF	.200	.260	.150	.200	M22G270*2-F	27 pF	.200	.260	.150	.200	M22G221*2-F	220 pF	.200	.260	.150	.200			
M15G399D2-F	3.9 pF	.150	.210	.130	.100	M15G330*2-F	33 pF	.150	.210	.130	.100	M15G271*2-F	270 pF	.150	.210	.130	.100			
M20G399D2-F	3.9 pF	.200	.260	.150	.100	M20G330*2-F	33 pF	.200	.260	.150	.100	M20G271*2-F	270 pF	.200	.260	.150	.100			
M22G399D2-F	3.9 pF	.200	.260	.150	.200	M22G330*2-F	33 pF	.200	.260	.150	.200	M22G271*2-F	270 pF	.200	.260	.150	.200			
M15G479D2-F	4.7 pF	.150	.210	.130	.100	M15G390*2-F	39 pF	.150	.210	.130	.100	M15G331*2-F	330 pF	.150	.210	.130	.100			
M20G479D2-F	4.7 pF	.200	.260	.150	.100	M20G390*2-F	39 pF	.200	.260	.150	.100	M20G331*2-F	330 pF	.200	.260	.150	.100			
M22G479D2-F	4.7 pF	.200	.260	.150	.200	M22G390*2-F	39 pF	.200	.260	.150	.200	M22G331*2-F	330 pF	.200	.260	.150	.200			
M15G569D2-F	5.6 pF	.150	.210	.130	.100	M15G470*2-F	47 pF	.150	.210	.130	.100	M15G391*2-F	390 pF	.150	.210	.130	.100			
M20G569D2-F	5.6 pF	.200	.260	.150	.100	M20G470*2-F	47 pF	.200	.260	.150	.100	M20G391*2-F	390 pF	.200	.260	.150	.100			
M22G569D2-F	5.6 pF	.200	.260	.150	.200	M22G470*2-F	47 pF	.200	.260	.150	.200	M22G391*2-F	390 pF	.200	.260	.150	.200			
M15G689D2-F	6.8 pF	.150	.210	.130	.100	M15G560*2-F	56 pF	.150	.210	.130	.100	M15G471*2-F	470 pF	.150	.210	.130	.100			
M20G689D2-F	6.8 pF	.200	.260	.150	.100	M20G560*2-F	56 pF	.200	.260	.150	.100	M20G471*2-F	470 pF	.200	.260	.150	.100			
M22G689D2-F	6.8 pF	.200	.260	.150	.200	M22G560*2-F	56 pF	.200	.260	.150	.200	M22G471*2-F	470 pF	.200	.260	.150	.200			
M15G829D2-F	8.2 pF	.150	.210	.130	.100	M15G680*2-F	68 pF	.150	.210	.130	.100	M20G561*2-F	560 pF	.200	.260	.150	.100			
M20G829D2-F	8.2 pF	.200	.260	.150	.100	M20G680*2-F	68 pF	.200	.260	.150	.100	M22G561*2-F	560 pF	.200	.260	.150	.200			
M22G829D2-F	8.2 pF	.200	.260	.150	.200	M22G680*2-F	68 pF	.200	.260	.150	.200	M20G681*2-F	680 pF	.200	.260	.150	.100			
M15G100*2-F	10 pF	.150	.210	.130	.100	M15G820*2-F	82 pF	.150	.210	.130	.100	M22G681*2-F	680 pF	.200	.260	.150	.200			
M20G100*2-F	10 pF	.200	.260	.150	.100	M20G820*2-F	82 pF	.200	.260	.150	.100	M20G821*2-F	820 pF	.200	.260	.150	.100			
M22G100*2-F	10 pF	.200	.260	.150	.200	M22G820*2-F	82 pF	.200	.260	.150	.200	M22G821*2-F	820 pF	.200	.260	.150	.200			

*Insert proper letter symbol for tolerance

Add 'TR' to end of part number for Tape & Reel

M15, M20, M22 - 2,500 per reel

M30 - 1,500; M40 - 1,000 per reel; M50 - N/A

(Available in full reels only)

*Insert proper letter symbol for tolerance

1 pF to 8.2 pF available in D = ± 5 pF only

10 pF to 22 pF: J = $\pm 5\%$; K = $\pm 10\%$

27 pF to 47 pF: G = $\pm 2\%$; J = $\pm 5\%$; K = $\pm 10\%$

56 pF & Up: F = $\pm 1\%$; G = $\pm 2\%$; J = $\pm 5\%$; K = $\pm 10\%$

Type M15 to M50 Multilayer Ceramic Capacitors

Ratings

RoHS Compliant

COG (NPO) Temperature Coefficient											
Catalog		Sizes (Inches)				Catalog		Sizes (Inches)			
Part Number	Cap	L	H	T	S	Part Number	Cap	L	H	T	S
200 Vdc											
M20G102*2-F	1000 pF	.200	.260	.150	.100	M30G272*2-F	2700 pF	.300	.360	.200	.200
M22G102*2-F	1000 pF	.200	.260	.150	.200	M20G332*2-F	3300 pF	.200	.260	.150	.100
M20G122*2-F	1200 pF	.200	.260	.150	.100	M22G332*2-F	3300 pF	.200	.260	.150	.200
M22G122*2-F	1200 pF	.200	.260	.150	.200	M30G332*2-F	3300 pF	.300	.360	.200	.200
M20G152*2-F	1500 pF	.200	.260	.150	.100	M30G392*2-F	3900 pF	.300	.360	.200	.200
M22G152*2-F	1500 pF	.200	.260	.150	.200	M30G472*2-F	4700 pF	.300	.360	.200	.200
M20G182*2-F	1800 pF	.200	.260	.150	.100	M30G562*2-F	5600 pF	.300	.360	.200	.200
M22G182*2-F	1800 pF	.200	.260	.150	.200	M30G682*2-F	6800 pF	.300	.360	.200	.200
M20G222*2-F	2200 pF	.200	.260	.150	.100	M30G822*2-F	8200 pF	.300	.360	.200	.200
M22G222*2-F	2200 pF	.200	.260	.150	.200	M30G103*2-F	.010 uF	.300	.360	.200	.200
M20G272*2-F	2700 pF	.200	.260	.150	.100	M30G123*2-F	.012 uF	.300	.360	.200	.200
M22G272*2-F	2700 pF	.200	.260	.150	.200	M40G123*2-F	.012 uF	.400	.460	.200	.200
M30G153*2-F						M40G153*2-F		.015 uF			
M30G183*2-F						M40G183*2-F		.018 uF			
M40G223*2-F						M40G273*2-F		.027 uF			
M40G333*2-F						M40G393*2-F		.039 uF			
M50G393*2-F						M50G473*2-F		.047 uF			
M50G563*2-F						M50G683*2-F		.068 uF			

*Insert proper letter symbol for tolerance

K = 10%; M = ±20%

100 Vdc											
M15G121*1-F	120 pF	.150	.210	.130	.100	M20G152*1-F	1500 pF	.200	.260	.150	.100
M15G151*1-F	150 pF	.150	.210	.130	.100	M22G152*1-F	1500 pF	.200	.260	.150	.200
M15G181*1-F	180 pF	.150	.210	.130	.100	M20G182*1-F	1800 pF	.200	.260	.150	.100
M15G221*1-F	220 pF	.150	.210	.130	.100	M22G182*1-F	1800 pF	.200	.260	.150	.200
M15G271*1-F	270 pF	.150	.210	.130	.100	M20G222*1-F	2200 pF	.200	.260	.150	.100
M15G331*1-F	330 pF	.150	.210	.130	.100	M22G222*1-F	2200 pF	.200	.260	.150	.200
M15G391*1-F	390 pF	.150	.210	.130	.100	M20G272*1-F	2700 pF	.200	.260	.150	.100
M15G471*1-F	470 pF	.150	.210	.130	.100	M22G272*1-F	2700 pF	.200	.260	.150	.200
M15G561*1-F	560 pF	.150	.210	.130	.100	M20G332*1-F	3300 pF	.200	.260	.150	.100
M15G681*1-F	680 pF	.150	.210	.130	.100	M22G332*1-F	3300 pF	.200	.260	.150	.200
M20G681*1-F	680 pF	.200	.260	.150	.100	M30G332*1-F	3300 pF	.300	.360	.200	.200
M22G681*1-F	680 pF	.200	.260	.150	.200	M20G392*1-F	3900 pF	.200	.260	.150	.100
M15G821*1-F	820 pF	.150	.210	.130	.100	M22G392*1-F	3900 pF	.200	.260	.150	.200
M20G821*1-F	820 pF	.200	.260	.150	.100	M30G392*1-F	3900 pF	.300	.360	.200	.200
M22G821*1-F	820 pF	.200	.260	.150	.200	M20G472*1-F	4700 pF	.200	.260	.150	.100
M15G102*1-F	1000 pF	.150	.210	.130	.100	M22G472*1-F	4700 pF	.200	.260	.150	.200
M20G102*1-F	1000 pF	.200	.260	.150	.100	M30G472*1-F	4700 pF	.300	.360	.200	.200
M22G102*1-F	1000 pF	.200	.260	.150	.200	M20G562*1-F	5600 pF	.200	.260	.150	.100
M20G122*1-F	1200 pF	.200	.260	.150	.100	M22G562*1-F	5600 pF	.200	.260	.150	.200
M22G122*1-F	1200 pF	.200	.260	.150	.200	M30G562*1-F	5600 pF	.300	.360	.200	.200
M30G682*1-F						M40G682*1-F		8200 pF			
M30G822*1-F						M40G822*1-F		.01 uF			
M30G103*1-F						M30G123*1-F		.012 uF			
M30G153*1-F						M30G183*1-F		.018 uF			
M30G223*1-F						M30G273*1-F		.027 uF			
M40G273*1-F						M40G333*1-F		.033 uF			
M40G393*1-F						M40G473*1-F		.047 uF			
M50G473*1-F						M50G563*1-F		.056 uF			
M50G683*1-F						M50G823*1-F		.082 uF			
M50G104*1-F						M50G124*1-F		.12 uF			

*Insert proper letter symbol for tolerance

K = 10%; M = ±20%

X7R Temperature Coefficient											
200 Vdc											
Catalog		Sizes (Inches)				Catalog		Sizes (Inches)			
Part Number	Cap	L	H	T	S	Part Number	Cap	L	H	T	S
M15R101*2-F	100 pF	.150	.210	.130	.100	M15R561*2-F	560 pF	.150	.210	.130	.100
M15R121*2-F	120 pF	.150	.210	.130	.100	M15R681*2-F	680 pF	.150	.210	.130	.100
M15R151*2-F	150 pF	.150	.210	.130	.100	M15R821*2-F	820 pF	.150	.210	.130	.100
M15R181*2-F	180 pF	.150	.210	.130	.100	M15R102*2-F	1000 pF	.150	.210	.130	.100
M15R221*2-F	220 pF	.150	.210	.130	.100	M20R102*2-F	1000 pF	.200	.260	.150	.100
M15R271*2-F	270 pF	.150	.210	.130	.100	M22R102*2-F	1000 pF	.200	.260	.150	.200
M15R331*2-F	330 pF	.150	.210	.130	.100	M15R122*2-F	1200 pF	.150	.210	.130	.100
M15R391*2-F	390 pF	.150	.210	.130	.100	M20R122*2-F	1200 pF	.200	.260	.150	.100
M15R471*2-F	470 pF	.150	.210	.130	.100	M22R122*2-F	1200 pF	.200	.260	.150	.200
M15R152*2-F						M20R152*2-F		1500 pF			
M20R182*2-F						M22R182*2-F		1800 pF			
M15R222*2-F						M20R222*2-F		2200 pF			
M20R272*2-F						M22R272*2-F		2700 pF			

Add 'TR' to end of part number for Tape & Reel

M15, M20, M22 - 2,500 per reel

M30 - 1,500 per reel Full reels only on all

M40 - 1,000 per reel; sizes.

M50 - N/A

*Insert proper letter symbol for tolerance

K = 10%; M = ±20%

Type M15 to M50 Multilayer Ceramic Capacitors

Ratings

RoHS Compliant

X7R Temperature Coefficient 200 Vdc																	
Catalog		Sizes (Inches)				Catalog		Sizes (Inches)				Catalog		Sizes (Inches)			
Part Number	Cap	L	H	T	S	Part Number	Cap	L	H	T	S	Part Number	Cap	L	H	T	S
M20R272*2-F	2700 pF	.200	.260	.150	.100	M22R103*2-F	.010 uF	.200	.260	.150	.200	M30R473*2-F	.047 uF	.300	.360	.200	.200
M22R272*2-F	2700 pF	.200	.260	.150	.200	M20R123*2-F	.012 uF	.200	.260	.150	.100	M30R563*2-F	.056 uF	.300	.360	.200	.200
M20R332*2-F	3300 pF	.200	.260	.150	.100	M22R123*2-F	.012 uF	.200	.260	.150	.200	M30R683*2-F	.068 uF	.300	.360	.200	.200
M22R332*2-F	3300 pF	.200	.260	.150	.200	M20R153*2-F	.015 uF	.200	.260	.150	.100	M30R823*2-F	.082 uF	.300	.360	.200	.200
M20R392*2-F	3900 pF	.200	.260	.150	.100	M22R153*2-F	.015 uF	.200	.260	.150	.200	M40R823*2-F	.082 uF	.400	.460	.200	.200
M22R392*2-F	3900 pF	.200	.260	.150	.200	M30R153*2-F	.015 uF	.300	.360	.200	.200	M30R104*2-F	.10 uF	.300	.360	.200	.200
M20R472*2-F	4700 pF	.200	.260	.150	.100	M20R183*2-F	.018 uF	.200	.260	.150	.100	M40R104*2-F	.10 uF	.400	.460	.200	.200
M22R472*2-F	4700 pF	.200	.260	.150	.200	M22R183*2-F	.018 uF	.200	.260	.150	.200	M40R124*2-F	.12 uF	.400	.460	.200	.200
M20R562*2-F	5600 pF	.200	.260	.150	.100	M30R183*2-F	.018 uF	.300	.360	.200	.200	M40R154*2-F	.15 uF	.400	.460	.200	.200
M22R562*2-F	5600 pF	.200	.260	.150	.200	M20R223*2-F	.022 uF	.200	.260	.150	.100	M40R184*2-F	.18 uF	.400	.460	.200	.200
M20R682*2-F	6800 pF	.200	.260	.150	.100	M22R223*2-F	.022 uF	.200	.260	.150	.200	M40R224*2-F	.22 uF	.400	.460	.200	.200
M22R682*2-F	6800 pF	.200	.260	.150	.200	M30R223*2-F	.022 uF	.300	.360	.200	.200	M50R224*2-F	.22 uF	.500	.560	.250	.400
M20R822*2-F	8200 pF	.200	.260	.150	.100	M30R273*2-F	.027 uF	.300	.360	.200	.200	M40R274*2-F	.27 uF	.400	.460	.200	.200
M22R822*2-F	8200 pF	.200	.260	.150	.200	M30R333*2-F	.033 uF	.300	.360	.200	.200	M50R274*2-F	.27 uF	.500	.560	.250	.400
M20R103*2-F	.010 uF	.200	.260	.150	.100	M30R393*2-F	.039 uF	.300	.360	.200	.200	M50R334*2-F	.33 uF	.500	.560	.250	.400
*Insert proper letter symbol for tolerance												M50R394*2-F	.39 uF	.500	.560	.250	.400
K = 10%; M = ±20%												M50R474*2-F	.47 uF	.500	.560	.250	.400

100 Vdc X7R																	
Catalog		Sizes (Inches)				Catalog		Sizes (Inches)				Catalog		Sizes (Inches)			
Part Number	Cap	L	H	T	S	Part Number	Cap	L	H	T	S	Part Number	Cap	L	H	T	S
M15R821*1-F	820 pF	.150	.210	.130	.100	M20R123*1-F	.012 uF	.200	.260	.150	.100	M20R104*1-F	.10 uF	.200	.260	.150	.100
M15R102*1-F	1000 pF	.150	.210	.130	.100	M22R123*1-F	.012 uF	.200	.260	.150	.200	M22R104*1-F	.10 uF	.200	.260	.150	.200
M15R122*1-F	1200 pF	.150	.210	.130	.100	M20R153*1-F	.015 uF	.200	.260	.150	.100	M30R104*1-F	.10 uF	.300	.360	.200	.200
M15R152*1-F	1500 pF	.150	.210	.130	.100	M22R153*1-F	.015 uF	.200	.260	.150	.200	M30R124*1-F	.12 uF	.300	.360	.200	.200
M15R182*1-F	1800 pF	.150	.210	.130	.100	M20R183*1-F	.018 uF	.200	.260	.150	.100	M30R154*1-F	.15 uF	.300	.360	.200	.200
M15R222*1-F	2200 pF	.150	.210	.130	.100	M22R183*1-F	.018 uF	.200	.260	.150	.200	M30R184*1-F	.18 uF	.300	.360	.200	.200
M15R272*1-F	2700 pF	.150	.210	.130	.100	M20R223*1-F	.022 uF	.200	.260	.150	.100	M30R224*1-F	.22 uF	.300	.360	.200	.200
M15R332*1-F	3300 pF	.150	.210	.130	.100	M22R223*1-F	.022 uF	.200	.260	.150	.200	M30R274*1-F	.27 uF	.300	.360	.200	.200
M15R392*1-F	3900 pF	.150	.210	.130	.100	M20R273*1-F	.027 uF	.200	.260	.150	.100	M30R334*1-F	.33 uF	.300	.360	.200	.200
M15R472*1-F	4700 pF	.150	.210	.130	.100	M22R273*1-F	.027 uF	.200	.260	.150	.200	M40R334*1-F	.33 uF	.400	.460	.200	.200
M20R472*1-F	4700 pF	.200	.260	.150	.100	M20R333*1-F	.033 uF	.200	.260	.150	.100	M30R394*1-F	.39 uF	.300	.360	.200	.200
M22R472*1-F	4700 pF	.200	.260	.150	.200	M22R333*1-F	.033 uF	.200	.260	.150	.200	M40R394*1-F	.39 uF	.400	.460	.200	.200
M15R562*1-F	5600 pF	.150	.210	.130	.100	M20R393*1-F	.039 uF	.200	.260	.150	.100	M30R474*1-F	.47 uF	.300	.360	.200	.200
M20R562*1-F	5600 pF	.200	.260	.150	.100	M22R393*1-F	.039 uF	.200	.260	.150	.200	M40R474*1-F	.47 uF	.400	.460	.200	.200
M22R562*1-F	5600 pF	.200	.260	.150	.200	M20R473*1-F	.047 uF	.200	.260	.150	.100	M40R564*1-F	.56 uF	.400	.460	.200	.200
M15R682*1-F	6800 pF	.150	.210	.130	.100	M22R473*1-F	.047 uF	.200	.260	.150	.200	M40R684*1-F	.68 uF	.400	.460	.200	.200
M20R682*1-F	6800 pF	.200	.260	.150	.100	M20R563*1-F	.056 uF	.200	.260	.150	.100	M50R684*1-F	.68 uF	.500	.560	.250	.400
M22R682*1-F	6800 pF	.200	.260	.150	.200	M22R563*1-F	.056 uF	.200	.260	.150	.200	M40R824*1-F	.82 uF	.400	.460	.200	.200
M15R822*1-F	8200 pF	.150	.210	.130	.100	M20R683*1-F	.068 uF	.200	.260	.150	.100	M50R824*1-F	.82 uF	.500	.560	.250	.400
M20R822*1-F	8200 pF	.200	.260	.150	.100	M22R683*1-F	.068 uF	.200	.260	.150	.200	M40R105*1-F	1.0 uF	.400	.460	.200	.200
M22R822*1-F	8200 pF	.200	.260	.150	.200	M30R683*1-F	.068 uF	.300	.360	.200	.200	M50R105*1-F	1.0 uF	.500	.560	.250	.400
M15R103*1-F	.010 uF	.150	.210	.130	.100	M20R823*1-F	.082 uF	.200	.260	.150	.100	M50R125*1-F	1.2 uF	.500	.560	.250	.400
M20R103*1-F	.010 uF	.200	.260	.150	.100	M22R823*1-F	.082 uF	.200	.260	.150	.200	*Insert proper letter symbol for tolerance					
M22R103*1-F	.010 uF	.200	.260	.150	.200	M30R823*1-F	.082 uF	.300	.360	.200	.200	K = 10%; M = ±20%					

50 Vdc X7R																	
Catalog		Sizes (Inches)				Catalog		Sizes (Inches)				Catalog		Sizes (Inches)			
Part Number	Cap	L	H	T	S	Part Number	Cap	L	H	T	S	Part Number	Cap	L	H	T	S
M15R332*5-F	3300 pF	.150	.210	.130	.100	M15R682*5-F	6800 pF	.150	.210	.130	.100	M20R123*5-F	.012 uF	.200	.260	.150	.100
M15R392*5-F	3900 pF	.150	.210	.130	.100	M15R822*5-F	8200 pF	.150	.210	.130	.100	M22R123*5-F	.012 uF	.200	.260	.150	.200
M15R472*5-F	4700 pF	.150	.210	.130	.100	M15R103*5-F	.010 uF	.150	.210	.130	.100	M15R153*5-F	.015 uF	.150	.210	.130	.100
M15R562*5-F	5600 pF	.150	.210	.130	.100	M15R123*5-F	.012 uF	.150	.210	.130	.100	M20R153*5-F	.015 uF	.200	.260	.150	.100

Add 'TR' to end of part number for Tape & Reel

M15, M20, M22 - 2,500 per reel

M30 - 1,500 per reel Full reels only on all sizes

M40 - 1,000 per reel

M50 - N/A

*Insert proper letter symbol for tolerance

K = 10%; M = ±20%

Type M15 to M50 Multilayer Ceramic Capacitors

Ratings

RoHS Compliant

X7R Temperature Coefficient 50 Vdc X7R																	
Catalog		Sizes (Inches)				Catalog		Sizes (Inches)				Catalog		Sizes (Inches)			
Part Number	Cap	L	H	T	S	Part Number	Cap	L	H	T	S	Part Number	Cap	L	H	T	S
M22R153*5-F	.015 uF	.200	.260	.150	.200	M20R683*5-F	.068 uF	.200	.260	.150	.100	M22R274*5-F	.27 uF	.200	.260	.150	.200
M15R183*5-F	.018 uF	.150	.210	.130	.100	M22R683*5-F	.068 uF	.200	.260	.150	.200	M30R274*5-F	.27 uF	.300	.360	.200	.200
M20R183*5-F	.018 uF	.200	.260	.150	.100	M20R823*5-F	.082 uF	.200	.260	.150	.100	M30R334*5-F	.33 uF	.300	.360	.200	.200
M22R183*5-F	.018 uF	.200	.260	.150	.200	M22R823*5-F	.082 uF	.200	.260	.150	.200	M30R394*5-F	.39 uF	.300	.360	.200	.200
M15R223*5-F	.022 uF	.150	.210	.130	.100	M20R104*5-F	.10 uF	.200	.260	.150	.100	M30R474*5-F	.47 uF	.300	.360	.200	.200
M20R223*5-F	.022 uF	.200	.260	.150	.100	M22R104*5-F	.10 uF	.200	.260	.150	.200	M30R564*5-F	.56 uF	.300	.360	.200	.200
M22R223*5-F	.022 uF	.200	.260	.150	.200	M20R124*5-F	.12 uF	.200	.260	.150	.100	M30R684*5-F	.68 uF	.300	.360	.200	.200
M15R273*5-F	.027 uF	.150	.210	.130	.100	M22R124*5-F	.12 uF	.200	.260	.150	.200	M30R824*5-F	.82 uF	.300	.360	.200	.200
M20R273*5-F	.027 uF	.200	.260	.150	.100	M20R154*5-F	.15 uF	.200	.260	.150	.100	M30R105*5-F	1.0 uF	.300	.360	.200	.200
M22R273*5-F	.027 uF	.200	.260	.150	.200	M22R154*5-F	.15 uF	.200	.260	.150	.200	M40R105*5-F	1.0 uF	.400	.460	.200	.200
M15R333*5-F	.033 uF	.150	.210	.130	.100	M30R154*5-F	.15 uF	.300	.360	.200	.200	M40R125*5-F	1.2 uF	.400	.460	.200	.200
M20R333*5-F	.033 uF	.200	.260	.150	.100	M20R184*5-F	.18 uF	.200	.260	.150	.100	M40R155*5-F	1.5 uF	.400	.460	.200	.200
M22R333*5-F	.033 uF	.200	.260	.150	.200	M22R184*5-F	.18 uF	.200	.260	.150	.200	M40R185*5-F	1.8 uF	.400	.460	.200	.200
M20R393*5-F	.039 uF	.200	.260	.150	.100	M30R184*5-F	.18 uF	.300	.360	.200	.200	M40R225*5-F	2.2 uF	.400	.460	.200	.200
M22R393*5-F	.039 uF	.200	.260	.150	.200	M20R224*5-F	.22 uF	.200	.260	.150	.100	M50R225*5-F	2.2 uF	.500	.560	.250	.400
M20R473*5-F	.047 uF	.200	.260	.150	.100	M22R224*5-F	.22 uF	.200	.260	.150	.200	M50R275*5-F	2.7 uF	.500	.560	.250	.400
M22R473*5-F	.047 uF	.200	.260	.150	.200	M30R224*5-F	.22 uF	.300	.360	.200	.200	M50R335*5-F	3.3 uF	.500	.560	.250	.400
M20R563*5-F	.056 uF	.200	.260	.150	.100	M20R274*5-F	.27 uF	.200	.260	.150	.100	M50R395*5-F	3.9 uF	.500	.560	.250	.400
M22R563*5-F	.056 uF	.200	.260	.150	.200							*Insert proper letter symbol for tolerance					

*Insert proper letter symbol for tolerance

K = 10%; M = ±20%

Z5U Temperature Coefficient 100 Vdc																	
Catalog		Sizes (Inches)				Catalog		Sizes (Inches)				Catalog		Sizes (Inches)			
Part Number	Cap	L	H	T	S	Part Number	Cap	L	H	T	S	Part Number	Cap	L	H	T	S
M15U102*1-F	1000 pF	.150	.210	.130	.100	M20U223*1-F	.022 uF	.200	.260	.150	.100	M22U154*1-F	.15 uF	.200	.260	.150	.200
M15U122*1-F	1200 pF	.150	.210	.130	.100	M22U223*1-F	.022 uF	.200	.260	.150	.200	M30U154*1-F	.15 uF	.300	.360	.200	.200
M15U152*1-F	1500 pF	.150	.210	.130	.100	M20U273*1-F	.027 uF	.200	.260	.150	.100	M30U184*1-F	.18 uF	.300	.360	.200	.200
M15U182*1-F	1800 pF	.150	.210	.130	.100	M22U273*1-F	.027 uF	.200	.260	.150	.200	M30U224*1-F	.22 uF	.300	.360	.200	.200
M15U222*1-F	2200 pF	.150	.210	.130	.100	M20U333*1-F	.033 uF	.200	.260	.150	.100	M30U274*1-F	.27 uF	.300	.360	.200	.200
M15U272*1-F	2700 pF	.150	.210	.130	.100	M22U333*1-F	.033 uF	.200	.260	.150	.200	M30U334*1-F	.33 uF	.300	.360	.200	.200
M15U332*1-F	3300 pF	.150	.210	.130	.100	M20U393*1-F	.039 uF	.200	.260	.150	.100	M40U334*1-F	.33 uF	.400	.460	.200	.200
M15U392*1-F	3900 pF	.150	.210	.130	.100	M22U393*1-F	.039 uF	.200	.260	.150	.200	M30U394*1-F	.39 uF	.300	.360	.200	.200
M15U472*1-F	4700 pF	.150	.210	.130	.100	M20U473*1-F	.047 uF	.200	.260	.150	.100	M40U394*1-F	.39 uF	.400	.460	.200	.200
M15U562*1-F	5600 pF	.150	.210	.130	.100	M22U473*1-F	.047 uF	.200	.260	.150	.200	M30U474*1-F	.47 uF	.300	.360	.200	.200
M15U682*1-F	6800 uF	.150	.210	.130	.100	M20U563*1-F	.056 uF	.200	.260	.150	.100	M40U474*1-F	.47 uF	.400	.460	.200	.200
M15U822*1-F	8200 pF	.150	.210	.130	.100	M22U563*1-F	.056 uF	.200	.260	.150	.200	M40U564*1-F	.56 uF	.400	.460	.200	.200
M15U103*1-F	.010 Uf	.150	.210	.130	.100	M20U683*1-F	.068 uF	.200	.260	.150	.100	M40U684*1-F	.68 uF	.400	.460	.200	.200
M20U103*1-F	.010 uF	.200	.260	.150	.100	M22U683*1-F	.068 uF	.200	.260	.150	.200	M40U824*1-F	.82 uF	.400	.460	.200	.200
M22U103*1-F	.010 uF	.200	.260	.150	.200	M20U823*1-F	.082 uF	.200	.260	.150	.100	M40U105*1-F	1.0 uF	.400	.460	.200	.200
M15U123*1-F	.012 uF	.150	.210	.130	.100	M22U823*1-F	.082 uF	.200	.260	.150	.200	M50U105*1-F	1.0 uF	.500	.560	.250	.400
M20U123*1-F	.012 uF	.200	.260	.150	.100	M20U104*1-F	.10 uF	.200	.260	.150	.100	M40U125*1-F	1.2 uF	.400	.460	.200	.200
M22U123*1-F	.012 uF	.200	.260	.150	.200	M22U104*1-F	.10 uF	.200	.260	.150	.200	M50U125*1-F	1.2 uF	.500	.560	.250	.400
M15U153*1-F	.015 uF	.150	.210	.130	.100	M30U104*1-F	.10 uF	.300	.360	.200	.200	M40U155*1-F	1.5 uF	.400	.460	.200	.200
M20U153*1-F	.015 uF	.200	.260	.150	.100	M20U124*1-F	.12 uF	.200	.260	.150	.100	M50U155*1-F	1.5 uF	.500	.560	.250	.400
M22U153*1-F	.015 uF	.200	.260	.150	.200	M22U124*1-F	.12 uF	.200	.260	.150	.200	M50U185*1-F	1.8 uF	.500	.560	.250	.400
M15U183*1-F	.018 uF	.150	.210	.130	.100	M30U124*1-F	.12 uF	.300	.360	.200	.200	M50U225*1-F	2.2 uF	.500	.560	.250	.400
M20U183*1-F	.018 uF	.200	.260	.150	.100	M20U154*1-F	.15 uF	.200	.260	.150	.100	*Insert proper letter symbol for tolerance					
M22U183*1-F	.018 uF	.200	.260	.150	.200							K = 10%; M = ±20%					

*Insert proper letter symbol for tolerance

K = 10%; M = ±20%

Add 'TR' to end of part number for Tape & Reel

M15, M20, M22 - 2,500 per reel

M30 - 1,500 per reel Full reels only on all

M40 - 1,000 per reel; sizes.

M50 - N/A

Type M15 to M50 Multilayer Ceramic Capacitors

Ratings

RoHS Compliant

Z5U Temperature Coefficient 50 Vdc																				
Catalog		Sizes (Inches)					Catalog		Sizes (Inches)					Catalog		Sizes (Inches)				
Part Number	Cap	L	H	T	S		Part Number	Cap	L	H	T	S		Part Number	Cap	L	H	T	S	
M15U472*5-F	4700 pF	.150	.210	.130	.100		M15U683*5-F	.068 uF	.150	.210	.130	.100		M20U474*5-F	.47 uF	.200	.260	.150	.100	
M15U562*5-F	5600 pF	.150	.210	.130	.100		M20U683*5-F	.068 uF	.200	.260	.150	.100		M22U474*5-F	.47 uF	.200	.260	.150	.200	
M15U682*5-F	6800 pF	.150	.210	.130	.100		M22U683*5-F	.068 uF	.200	.260	.150	.200		M30U474*5-F	.47 uF	.300	.360	.200	.200	
M15U822*5-F	8200 pF	.150	.210	.130	.100		M20U823*5-F	.082 uF	.200	.260	.150	.100		M20U564*5-F	.56 uF	.200	.260	.150	.100	
M15U103*5-F	.010 uF	.150	.210	.130	.100		M22U823*5-F	.082 uF	.200	.260	.150	.200		M22U564*5-F	.56 uF	.200	.260	.150	.200	
M15U123*5-F	.012 uF	.150	.210	.130	.100		M15U104*5-F	.10 uF	.150	.210	.130	.100		M30U564*5-F	.56 uF	.300	.360	.200	.200	
M15U153*5-F	.015 uF	.150	.210	.130	.100		M20U104*5-F	.10 uF	.200	.260	.150	.100		M30U684*5-F	.68 uF	.300	.360	.200	.200	
M15U183*5-F	.018 uF	.150	.210	.130	.100		M22U104*5-F	.10 uF	.200	.260	.150	.200		M30U824*5-F	.82 uF	.300	.360	.200	.200	
M15U223*5-F	.022 uF	.150	.210	.130	.100		M20U124*5-F	.12 uF	.200	.260	.150	.100		M30U105*5-F	1.0 uF	.300	.360	.200	.200	
M15U273*5-F	.027 uF	.150	.210	.130	.100		M22U124*5-F	.12 uF	.200	.260	.150	.200		M30U125*5-F	1.2 uF	.300	.360	.200	.200	
M20U273*5-F	.027 uF	.200	.260	.150	.100		M20U154*5-F	.15 uF	.200	.260	.150	.100		M40U125*5-F	1.2 uF	.400	.460	.200	.200	
M22U273*5-F	.027 uF	.200	.260	.150	.200		M22U154*5-F	.15 uF	.200	.260	.150	.200		M30U155*5-F	1.5 uF	.300	.360	.200	.200	
M15U333*5-F	.033 uF	.150	.210	.130	.100		M20U184*5-F	.18 uF	.200	.260	.150	.100		M40U155*5-F	1.5 uF	.400	.460	.200	.200	
M20U333*5-F	.033 uF	.200	.260	.150	.100		M22U184*5-F	.18 uF	.200	.260	.150	.200		M30U185*5-F	1.8 uF	.300	.360	.200	.200	
M22U333*5-F	.033 uF	.200	.260	.150	.200		M20U224*5-F	.22 uF	.200	.260	.150	.100		M40U185*5-F	1.8 uF	.400	.460	.200	.200	
M15U393*5-F	.039 uF	.150	.210	.130	.100		M22U224*5-F	.22 uF	.200	.260	.150	.200		M40U225*5-F	2.2 uF	.400	.460	.200	.200	
M20U393*5-F	.039 uF	.200	.260	.150	.100		M20U274*5-F	.27 uF	.200	.260	.150	.100		M40U275*5-F	2.7 uF	.400	.460	.200	.200	
M22U393*5-F	.039 uF	.200	.260	.150	.200		M22U274*5-F	.27 uF	.200	.260	.150	.200		M40U335*5-F	3.3 uF	.400	.460	.200	.200	
M15U473*5-F	.047 uF	.150	.210	.130	.100		M30U274*5-F	.27 uF	.300	.360	.200	.200		M40U395*5-F	3.9 uF	.400	.460	.200	.200	
M20U473*5-F	.047 uF	.200	.260	.150	.100		M20U334*5-F	.33 uF	.200	.260	.150	.100		M50U395*5-F	3.9 uF	.500	.560	.250	.400	
M22U473*5-F	.047 uF	.200	.260	.150	.200		M22U334*5-F	.33 uF	.200	.260	.150	.200		M40U475*5-F	4.7 uF	.400	.460	.200	.200	
M15U563*5-F	.056 uF	.150	.210	.130	.100		M30U334*5-F	.33 uF	.300	.360	.200	.200		M50U475*5-F	4.7 uF	.500	.560	.250	.400	
M20U563*5-F	.056 uF	.200	.260	.150	.100		M20U394*5-F	.39 uF	.200	.260	.150	.100		M50U565*5-F	5.6 uF	.500	.560	.250	.400	
M22U563*5-F	.056 uF	.200	.260	.150	.200		M22U394*5-F	.39 uF	.200	.260	.150	.200		M50U685*5-F	6.8 uF	.500	.560	.250	.400	
Add 'TR' to end of part number for Tape & Reel							M30U394*5-F	.39 uF	.300	.360	.200	.200		*Insert proper letter symbol for tolerance						

Add 'TR' to end of part number for Tape & Reel

M15, M20, M22 - 2,500 per reel

M30 - 1,500 per reel Full reels only on all


M40 - 1,000 per reel; sizes.

M50 - N/A

*Insert proper letter symbol for tolerance

K = 10%; M = ±20%

Outline Drawing



M30 Z5U 100 V 104 - 334 leads are formed to .200"

M30 X7R 50 V 154-105 leads are formed to .200"

Type M15 to M50 Multilayer Ceramic Capacitors

Notice and Disclaimer: All product drawings, descriptions, specifications, statements, information and data (collectively, the "Information") in this datasheet or other publication are subject to change. The customer is responsible for checking, confirming and verifying the extent to which the Information contained in this datasheet or other publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without any guarantee, warranty, representation or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on the knowledge that the Cornell Dubilier company providing such statements ("Cornell Dubilier") has of operating conditions that such Cornell Dubilier company regards as typical for such applications, but are not intended to constitute any guarantee, warranty or representation regarding any such matter – and Cornell Dubilier specifically and expressly disclaims any guarantee, warranty or representation concerning the suitability for a specific customer application, use, storage, transportation, or operating environment. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by Cornell Dubilier with reference to the use of any Cornell Dubilier products is given gratis (unless otherwise specified by Cornell Dubilier), and Cornell Dubilier assumes no obligation or liability for the advice given or results obtained. Although Cornell Dubilier strives to apply the most stringent quality and safety standards regarding the design and manufacturing of its products, in light of the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies or other appropriate protective measures) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage. Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated in such warnings, cautions and notes, or that other safety measures may not be required.