


Thick Film Resistor Networks, Military, MIL-PRF-83401 Qualified, Type RZ030, Flat Pack



FEATURES

- Isolated, bussed and dual terminator schematics available
- Hot-solder dipped leads
- MIL-PRF-83401 qualified
- Thick film resistive elements
- TCR available in "K" (± 100 ppm/ $^{\circ}\text{C}$) or "M" (± 300 ppm/ $^{\circ}\text{C}$) characteristic
- 100 % screen tested per group A, subgroup 1 of MIL-PRF-83401
- 0.065" (1.65 mm) height for high density packaging

STANDARD ELECTRICAL SPECIFICATIONS									
VISHAY DALE MODEL/ PIN NO.	MIL STYLE	MIL SPEC. SHEET	SCHEMATIC	POWER RATING ELEMENT $P_{70\text{ }^{\circ}\text{C}}$ W	POWER RATING PACKAGE $P_{70\text{ }^{\circ}\text{C}}$ W	RESISTANCE RANGE Ω	TOLERANCE ⁽²⁾ \pm %	TEMPERATURE COEFFICIENT ⁽¹⁾ (-55 $^{\circ}\text{C}$ to +125 $^{\circ}\text{C}$) \pm ppm/ $^{\circ}\text{C}$	WEIGHT g
DFM14	RZ030	03	11 (A)	0.050	0.350	10 to 1M	1, 2, 5	100, 300	0.4
			12 (B)	0.025	0.325	10 to 1M			
			15 (J)	0.015	0.350	Consult factory			





Notes

- Consult factory for stocked values.
- (1) $K = \pm 100$ ppm/ $^{\circ}\text{C}$; $M = \pm 300$ ppm/ $^{\circ}\text{C}$.
- (2) ± 2 % standard, ± 1 % and ± 5 % available.

GLOBAL PART NUMBER INFORMATION							
New Global Part Numbering: M8340103M6801GAD05 (preferred part numbering format)							
M	8	3	4	0	1	3	M
MIL STYLE	SPEC SHEET	CHARACTERISTIC	RESISTANCE VALUE	TOLERANCE	SCHEMATIC	PACKAGING	
M83401	03	K = 100 ppm M = 300 ppm	3 digit significant figure, followed by a multiplier 10R0 = 10 Ω 3302 = 33 k Ω 1004 = 1 M Ω	F = ± 1 % G = ± 2 % J = ± 5 %	A = Isolated B = Bussed	D05 = Tin/lead, tube DSL = Tin/lead, tube, single lot date code	
Historical Part Number Example: M8340103M6801GA (will continue to be accepted)							
M83401	03	M	6801	G	A	D05	
MIL STYLE	SPEC SHEET	CHARACTERISTIC	RESISTANCE VALUE	TOLERANCE	SCHEMATIC	PACKAGING	
New Global Part Numbering: M8340103KA001GJD05 (preferred part numbering format)							
M	8	3	4	0	1	0	5
MIL STYLE	SPEC SHEET	CHARACTERISTIC	RESISTANCE VALUE	TOLERANCE	SCHEMATIC	PACKAGING	
M83401	03	K = 100 ppm M = 300 ppm	Per Std. MIL. Spec. (see Impedance Codes table)	F = ± 1 % G = ± 2 % J = ± 5 %	J = Dual terminator	D05 = Tin/lead, tube DSL = Tin/lead, tube, single lot date code	
Historical Part Number Example: M8340103KA001GJ (will continue to be accepted)							
M83401	03	M	A001	G	J	D05	
MIL STYLE	SPEC SHEET	CHARACTERISTIC	RESISTANCE VALUE	TOLERANCE	SCHEMATIC	PACKAGING	

Note

- For additional information on packaging, refer to the Surface Mount Network Packaging document (www.vishay.com/doc?31540).

DIMENSIONS in inches (millimeters)

11 Schematic

Derating
12 Schematic

15 Schematic

MECHANICAL SPECIFICATIONS


Marking resistance to solvents	Permanency testing per MIL-PRF-83401
Solderability	Per MIL-PRF-83401
Terminals	Per MIL-STD-1276 DFM1411, DFM1412 and DFM1415 = Type G (hot solder dipped) Hot solder dipped leads supplied as standard finish
Body	Epoxy filled ceramic sandwich

TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	MDM SERIES
Maximum operating voltage	V _{DC}	50
Voltage coefficient of resistance	V _{eff}	< 50 ppm
Dielectric strength	V _{AC}	100 min.
Insulation resistance	Ω	10 000M
Operating temperature range	°C	-55 to +125
Storage temperature range	°C	-55 to +150


IMPEDANCE CODES

CODE	R ₁ (Ω)	R ₂ (Ω)	CODE	R ₁ (Ω)	R ₂ (Ω)
A001	82	130	A010	330	470
A002	120	200	A011	330	680
A003	130	210	A012	1.5K	3.3K
A004	160	260	A013	3K	6.2K
A005	180	240	A014	180	270
A006	180	390	A015	270	270
A007	220	270	A016	560	560
A008	220	330	A017	560	1.2K
A009	330	390	A018	620	2.7K

CIRCUIT APPLICATIONS
11 Schematic

DFM1411 (M8340103xxxxxA)
7 isolated resistors


The DFM1411 provides the user with 7 nominally equal resistors with each resistor isolated from all others. Commonly used in the following applications:

- “Wired OR” pull-up
- Power driven pull-up
- TTL input pull-down
- Line termination
- ECL output pull-down
- Long-line impedance balancing
- LED current limiting
- Power gate pull-up

12 Schematic

DFM1412 (M8340103xxxxxB)
13 resistors with one pin common

The DFM1412 provides the user with a choice of 13 nominally equal resistors, each connected to a common pin. Commonly used in the following applications:

- MOS/ROM pull-up/pull-down
- Open Collector pull-up
- TTL unused gate pull-up
- “Wired OR” pull-up
- Power driven pull-up
- High speed parallel pull-up
- Digital pulse squaring
- TTL input pull-down

15 Schematic

DFM1415 (M8340103xxxxxJ)
12 pairs of resistors

The DFM1415 provides the user with a choice of 12 pairs of R1/R2 resistor values for pulse squaring and TTL dual-line terminating requirements.

CAGE CODE: 91637

PERFORMANCE		
TEST	CONDITIONS	MAX. ΔR (TYPICAL TEST LOTS)
Power conditioning	1.5 x rated power, applied 1.5 h "ON" and 0.5 h "OFF" for 100 h ± 4 h at +25 °C ambient temperature	$\pm 0.50\% \Delta R$
Thermal shock	5 cycles between -65 °C and +125 °C	$\pm 0.50\% \Delta R$
Short time overload	2.5 x rated working voltage for 5 s	$\pm 0.25\% \Delta R$ (char. K) $\pm 0.50\% \Delta R$ (char. M)
Low temperature operation	45 min at full rated working voltage at -65 °C	$\pm 0.25\% \Delta R$ (char. K) $\pm 0.50\% \Delta R$ (char. M)
Moisture resistance	240 h with humidity ranging from 80 % RH to 98 % RH	$\pm 0.50\% \Delta R$
Resistance to soldering heat	Leads immersed in +260 °C solder to within 1/16" of body for 10 s	$\pm 0.25\% \Delta R$
Shock	Total of 18 shocks at 100 g's	$\pm 0.25\% \Delta R$
Vibration	12 h at maximum of 20 g's between 10 Hz and 2000 Hz	$\pm 0.25\% \Delta R$
Load life	1000 h at +70 °C, rated power applied 1.5 h "ON", 0.5 h "OFF" for full 1000 h period	$\pm 0.50\% \Delta R$ (char. K) $\pm 2.0\% \Delta R$ (char. M)
Terminal strength	1.5 pound pull for 30 s	$\pm 0.25\% \Delta R$
Insulation resistance	10 000 MΩ (minimum)	-
Dielectric withstanding voltage	No evidence of arcing or damage (200 V _{RMS} for 1 min)	-

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.