



1. MATERIALS AND FINISHES:
BODY - BERYLLIUM COPPER, GOLD .000010" THICK OVER WHITE BRONZE .000080 " THICK
CONTACT - BERYLLIUM COPPER, GOLD .000030 " THICK OVER WHITE BRONZE .000080" THICK.
INSULATOR - PTFE

2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC - 6 GHz
C. DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS, MIN.

3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -55° C TO 155° C

4. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL, 908-NM22100, AND DATE CODE"
AND "NON-MAGNETIC CONNECTORS"

← .290
[7.37]



NON-MAGNETIC **CUSTOMER OUTLINE DRAWING**
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES ±.015 (0.381 mm) ±.005 (0.127 mm) ± 1°			MATERIAL SEE NOTES		DRAWN R. RAJAN		DATE 12-Feb-09		TITLE MICROMATE JACK PCB EDGEMOUNT NON-MAGNETIC			Amphenol RF Danbury, CT, USA Tainan, Taiwan Shenzhen, China www.amphenolrf.com		
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.					ENGINEER G. TILTON		DATE 21-Jun-95							
			REFERENCE EAR 3372 908-22100 GEN# ASSYF3_MMCX GEN# PCB_CUTOUT			APPROVED K. CAPOZZI		DATE 5/12/09						
CAD FILE I:\MMCX\908-NM22100						CODE ID 74868		DWG SIZE B	DRAWING NO. 908-NM22100			REV B		