

DUAL ENTRY SOLENOID KEY OPERATED SAFETY INTERLOCK NOMENCLATURE

GK

GK

BODY / INDICATOR		CONDUIT / SEAL		BASIC 		HEAD		KEY		TYPE / OVER-RIDE		SOLENOID VOLTAGE	MODIFICATION CODE 	
L	HEAD TO LEFT - WITH INDICATORS	A	1/2 NPT - VITON SEALS	2	2 SNAP ACTION DPDT	L	OPENING TO FRONT AND TOP	6	STRAIGHT	A	SOLENOID UNLOCK WITH SCREWDRIVER	1	12 VDC	F04
R	HEAD TO RIGHT - WITH INDICATORS	B	PG 13.5 - VITON SEALS	3	2 SLOW ACTING SPDT BBM	M	OPENING TO RIGHT AND TOP	7	90 DEGREE		SLOT OVER-RIDE	2	24 VDC	F05
F	HEAD TO LEFT - WITHOUT INDICATORS	C	20 MM - VITON SEALS	6	SLOW ACTING 2 NC	N	OPENING TO BACK AND TOP	8	UP - DOWN, SPRING LOADED	B	SOLENOID UNLOCK WITHOUT OVER-RIDE	3	48 VDC	FW
G	HEAD TO RIGHT - WITHOUT INDICATORS	D	PF 1/2 - VITON SEALS	10	SLOW ACTING 4 NC	P	OPENING TO LEFT AND TOP	9	SIDE - SIDE, SPRING LOADED	S	SOLENOID LOCK WITH SCREWDRIVER	4	120 VAC	
		E	1/2 NPT - BUNA-N SEALS	12	SLOW ACTING 2 NC - 1 NO BBM			X	NO KEY		SLOT OVER-RIDE	6	240 VAC	
		F	PG 13.5 - BUNA-N SEALS	14	SLOW ACTING 2 NC - 2 NO BBM					T	SOLENOID LOCK WITHOUT OVER-RIDE			
		G	20 MM - BUNA-N SEALS	15	SLOW ACTING 2 NC - 2 NO BBM - GOLD									
		H	PF 1/2 - BUNA-N SEALS	16	SLOW ACTING 3 NC - 1 NO BBM									
				30	2 SLOW ACTING 4 NC - GOLD									
				32	2 SLOW ACTING 2 NC - 1 NO BBM - GOLD									
				34	2 SLOW ACTING 2 NC - 2 NO BBM - GOLD									
				36	2 SLOW ACTING 3 NC - 1 NO BBM - GOLD									
				40	2 SLOW ACTING 4 NC									
				42	2 SLOW ACTING 2 NC - 1 NO BBM									
				44	2 SLOW ACTING 2 NC - 2 NO BBM									
				46	2 SLOW ACTING 3 NC - 1 NO BBM									

NOTES

- 1 - ZINC DIECAST BODY AND HEAD WITH STEEL COVER. BODY, HEAD AND COVER FINISHED WITH EPOXY PAINT
- 2 - PROVIDED WITH PLASTIC SNAP FIT COVER TO PLUG UNUSED KEY ENTRY WINDOW
-  THE LEFT INDICATOR IS GREEN AND THE RIGHT INDICATOR IS RED. NOT PRESENT ON BODY/INDICATOR CODES F OR G
- 4 - MAXIMUM OPERATING FREQUENCY (Fmax) = 100 OPS/MIN
- 5 - INSERTION FORCE = 35 N
- EXTRACTION FORCE = 28 N
- 6 LB
- MAXIMUM SOLENOID LOCKING FORCE = 1000 N
- 224 LB
-  ROTATE 1/4 TURN CLOCKWISE TO UNLOCK DEVICES WITH HEAD TO LEFT, SOLENOID UNLOCK AND DEVICES WITH HEAD TO RIGHT, SOLENOID LOCK. ROTATE 1/4 TURN COUNTERCLOCKWISE TO UNLOCK DEVICES WITH HEAD TO LEFT, SOLENOID LOCK AND DEVICES WITH HEAD TO RIGHT, SOLENOID UNLOCK.
-  NOT PRESENT ON TYPE/OVER-RIDE CODES B OR T
-  SWITCH MUST OPERATE BEFORE REACHING MINIMUM INSERTION DISTANCE
- 8 - T-15 TAMPERPROOF TORX DRIVER BIT PROVIDED
-  ELECTRICAL RATINGS ARE FOR BASIC SWITCHES
- 10 - MINIMUM SOLENOID VOLTAGE = 80% DC / 85% AC OF RATED VOLTAGE
- MAXIMUM SOLENOID VOLTAGE = 110% OF RATED VOLTAGE
- SOLENOID POWER = 12 WATTS NOMINAL
-  SEE PAGES 10, 11, 12 AND 13 FOR CIRCUIT DIAGRAMS
- 12 - NO CHANGES CAN BE MADE TO THIS DRAWING WITHOUT JOINT FREEPORT / NEWHOUSE APPROVAL
-  THE LEFT INDICATOR IS YELLOW AND THE RIGHT INDICATOR IS RED
-  10-PIN CONNECTOR, BRAD HARRISON PART NO.3R1006AZ1F010 OR EQUIVALENT
-  4-PIN CONNECTOR, WOODHEAD PART NO.80599-19 OR MOLEX PART NO.08631MZ1 OR EQUIVALENT
-  5-PIN CONNECTOR, BRAD HARRISON PART NO.41310 OR EQUIVALENT
-  CONNECTOR INSTALLED IN BOTTOM CONDUIT HOLE
-  CONNECTOR INSTALLED IN SIDE CONDUIT HOLE
-  FOR CONNECTOR AND CIRCUIT DETAILS OF MODIFICATION CODE, REFER PAGE 14 FOR CODE F05, PAGE 15 FOR CODE FW AND PAGE 16 FOR CODE F04

ELECTRICAL RATING 				ENVIRONMENTAL RATINGS	APPROVALS
AC		DC		IP68 NEMA 1, 4, 6P, 12 & 13	   IEC 947-5-1 EN60947-5-1
A300	AC 15	O300	DC 13	TEMP RANGE -25°C TO 40°C	
Ue	Ie	Ue	Ie	-13°F TO 104°F	
(VOLTS)	(AMPS)	(VOLTS)	(AMPS)	STORAGE -40°C TO 120°C	
120	6	24	2.9	-40°F TO 248°F	
240	3	125	.55	SHOCK: 50G PER IEC 68-2-27	
		250	.27	VIBRATION: 10G PER IEC 68-2-6	
Ith = 10 A					

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

FED. MFG. CODE 91929

 **MICRO SWITCH**
a Honeywell Division

CATALOG LISTING

SWITCH - DOOR INTERLOCK

GK SERIES CHART 4

DESIGN UNITS ☒ SI METRIC ☐ US CUSTOMARY

WEIGHT 1,5 kg / 3,3 LB

THIRD ANGLE PROJECTION





SCALE NTS

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 1

NO PLACES	ONE PLACE	TWO PLACES	THREE PLACES	ANGLES
Ø	±	±	±	±
1/16	1/32	1/64	1/128	1/16
0.0156	0.0078	0.0039	0.0019	0.0625

SI METRIC ☒ US CUSTOMARY ☐



FRONT KEY ENTRY




TOP KEY ENTRY

BODY / INDICATOR CODES R OR G

PTC / CAD	3D	DRAWN	WAM	129SEP	98	CHECK	CMH	11MAY99	CHECK	PRS	04FEB09	CHECK	CMH	10NOV11	RELEASE NO. PR-23758	PAGE	2 OF 16	REPLACES	-					
REVISIONS															M									
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.															M									
ISSUE															5254					DRAWING NUMBER				
N															0047583					SSE				
P															0065737					31MAY10				
R															0083578					NOV 10NOV11				


THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		FED. MFG. CODE 91929		CATALOG LISTING	
MICRO SWITCH a Honeywell Division		SWITCH - DOOR INTERLOCK		GK SERIES CHART 4	
DESIGN UNITS		SI METRIC		US CUSTOMARY	
WEIGHT		1,5 kg / 3,3 LB			

THIRD ANGLE PROJECTION			
SCALE 1:1			
DO NOT SCALE PRINT			
TOLERANCES			
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE, UNLESS NOTED. TOLERANCES ARE 1			
NO PLACES	ONE PLACE	TWO PLACES	THREE PLACES
ANGLES	2, XX	2, XX	2, XX
SI METRIC	1/16, 04	0,01, 016	0,151, 006
US CUSTOMARY	1/16, 04	0,01, 016	0,151, 006




BODY / INDICATOR CODES L OR F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		<table><tr><td>QUN</td><td>TOL</td><td>QUN</td><td>TOL</td></tr><tr><td>IN</td><td>MM</td><td>IN</td><td>MM</td></tr><tr><td>NO PLACES</td><td>0</td><td>NO PLACES</td><td>0</td></tr><tr><td>ONE PLACE</td><td>1.0</td><td>ONE PLACE</td><td>0.001/0.01</td></tr><tr><td>TWO PLACES</td><td>2.0</td><td>TWO PLACES</td><td>0.002/0.015</td></tr><tr><td>THREE PLACES</td><td>3.0</td><td>THREE PLACES</td><td>0.003/0.015</td></tr><tr><td>ANGLES</td><td>0.151/0.06</td><td>ANGLES</td><td>0.151/0.06</td></tr></table>		QUN	TOL	QUN	TOL	IN	MM	IN	MM	NO PLACES	0	NO PLACES	0	ONE PLACE	1.0	ONE PLACE	0.001/0.01	TWO PLACES	2.0	TWO PLACES	0.002/0.015	THREE PLACES	3.0	THREE PLACES	0.003/0.015	ANGLES	0.151/0.06	ANGLES	0.151/0.06
QUN	TOL	QUN	TOL																												
IN	MM	IN	MM																												
NO PLACES	0	NO PLACES	0																												
ONE PLACE	1.0	ONE PLACE	0.001/0.01																												
TWO PLACES	2.0	TWO PLACES	0.002/0.015																												
THREE PLACES	3.0	THREE PLACES	0.003/0.015																												
ANGLES	0.151/0.06	ANGLES	0.151/0.06																												
FED. MFG. CODE 91929	CATALOG LISTING	<table><tr><td>SI METRIC</td><td>US CUSTOMARY</td></tr><tr><td>☒</td><td>☐</td></tr></table>		SI METRIC	US CUSTOMARY	☒	☐																								
SI METRIC	US CUSTOMARY																														
☒	☐																														
 MICRO SWITCH a Honeywell Division	SWITCH - DOOR INTERLOCK	GK SERIES CHART 4																													
		DESIGN UNITS ☒																													
		WEIGHT 1.5 kg / 3.3 lb																													





WITH KEY IN FRONT ENTRY POSITION




WITH KEY IN TOP ENTRY POSITION

HEAD CODE L





WITH KEY IN FRONT ENTRY POSITION




WITH KEY IN TOP ENTRY POSITION

HEAD CODE M







WITH KEY IN FRONT ENTRY POSITION




WITH KEY IN TOP ENTRY POSITION

HEAD CODE N




WITH KEY IN FRONT ENTRY POSITION



WITH KEY IN TOP ENTRY POSITION

HEAD CODE P









PTC/CAD	3D	DRW	30SEP88	check	CMH	12MAY89	check	PRG	04FEB89	check	CMH	10NOV11	RELEASE NO. PR-23758	5 OF 16	REPLACES	-
5254	ISSUE	5254	0047583	SS	04FEB89	0065737	31MAY10	0083576	10NOV11	0083576	10NOV11	0083576	10NOV11	0083576	10NOV11	0083576

REVISIONS	DATE	BY	CHKD	APPD	REASON
1	04FEB89	SS	CMH	PRG	04FEB89
2	0065737	31MAY10	0083576	10NOV11	0083576

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		CATALOG LISTING	
FED. MFG. CODE 91929		SWITCH - DOOR INTERLOCK	
MICRO SWITCH a Honeywell Division		GK SERIES CHART 4	
DESIGN UNITS ☒ SI METRIC ☐ US CUSTOMARY		WEIGHT 1.5 KG / 3.3 LB	

THIRD ANGLE PROJECTION			
SCALE 1:1			
DO NOT SCALE PRINT			
TOLERANCES			
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 1			
NO PLACES	2	1/4	0.001
ONE PLACE	1	0.001	0.001
TWO PLACES	0.01	0.01	0.01
THREE PLACES	0.001	0.001	0.001
ANGLES	1	1	1

KEY CODE 6




FRONT KEY ENTRY


TOP KEY ENTRY

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.				CATALOG LISTING			
FED. MFG. CODE 91929		MICRO SWITCH a Honeywell Division		SWITCH - DOOR INTERLOCK		GK SERIES CHART 4	
DESIGN UNITS		SI METRIC		US CUSTOMARY		WEIGHT 1,5 KG / 3.3 LB	
NO PLACES		TOL.		TOL.		TOL.	
ONE PLACE		1/16		1/16		0.0156	
TWO PLACES		1/32		1/32		0.0078	
THREE PLACES		1/64		1/64		0.0039	
ANGLES		1/16		1/16		0.0039	


KEY CODE 7








FRONT KEY ENTRY



TOP KEY ENTRY




THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.			
FED. MFG. CODE 91929		CATALOG LISTING	
MICRO SWITCH a Honeywell Division		SWITCH - DOOR INTERLOCK	
GK SERIES CHART 4		DESIGN UNITS ☒ SI METRIC ☐ US CUSTOMARY	
WEIGHT 1,5 KG / 3,3 LB			



PTC/CAD	30	DRAWN										
MAN	1 OCT 98	CHECK	CWH	2 MAY 99	CHECK	PRS	04 FEB 09	CHECK	CWH	1 NOV 11	RELEASE NO. PR-23758	REPLACES -
		ISSUED 5254 DRAWING NUMBER PAGES 8 OF 16										
REVISIONS N 00471583 SKK 04 FEB 09 P 00567337 PRS 31 MAY 10 R 0063578 NHT 1 NOV 11 												

PTC/CAD		30	DRAWING									
MAN	1 OCT 98	CHECK	CWH	2 MAY 99	CHECK	PRS	04 FEB 09	CHECK	CWH	1 NOV 11	RELEASE NO. PR-23758	REPLACES -
ISSUE 5254 DRAWING NUMBER REVISED N 0047583 SKK 04 FEB 09 P 0056737 PRS 31 MAY 10 R 0003578 NSH 1 NOV 11 16 PAGE 8 OF 16												
ISSUE 5254 DRAWING NUMBER REVISED N 0047583 SKK 04 FEB 09 P 0056737 PRS 31 MAY 10 R 0003578 NSH 1 NOV 11 16 PAGE 8 OF 16												

KEY CODE 9









BODY / INDICATOR CODES - L OR R
TYPE / OVER-RIDE CODES - S OR T
DIAGRAMS SHOWN WITH KEY INSERTED AND LOCKED

PTC/CAD 3D
DRAWN
MAM
LOC 198
21 SEP 06
DVM
CHECK
0803578
31 MAY 10
0065737
04 FEB 09
SS
0047583
M
12 OF 16
PAGE
10 NOV 11
RELEASE NO. PR-23758
CMH
REPLACES

M GK SERIES CHART 4


5254

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		FED. MFG. CODE 91929		CATALOG LISTING	
MICRO SWITCH a Honeywell Division		SWITCH - DOOR INTERLOCK		GK SERIES CHART 4	
DESIGN UNITS ☒ SI METRIC ☐ US CUSTOMARY		WEIGHT 1.5 KG / 3.3 LB			



THIRD ANGLE PROJECTION					
SCALE NTS					
DO NOT SCALE PRINT					
TOLERANCES APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 1					
NO PLACES	2	1/4	2.2	0.001	0.001
ONE PLACE	1.2	0.01	0.01	0.01	0.01
TWO PLACES	1.22	0.015	0.015	0.015	0.015
THREE PLACES	1.222	0.015	0.015	0.015	0.015




MODIFICATION CODE: F05



SWITCH DIAGRAM STATE
IS CLOSED AND LOCKED




300V 7A
BRAD-HARRISON PART NO. 3R1006A21F010
OR EQUIVALENT


THIRD ANGLE PROJECTION				
				
SCALE NTS				
DO NOT SCALE PRINT				
TOLERANCES				
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE :				
	DIM. mm	TOL mm / in	DIM. in	TOL mm / in
NO PLACES	X	1 / 0.04	X.X	0.8 / 0.03
ONE PLACE	X.X	0.1 / 0.016	X.XX	0.38 / 0.015
TWO PLACES	X.XX	0.15 / 0.008	X.XXX	0.13 / 0.005
THREE PLACES				
ANGLES				
SI METRIC		US CUSTOMARY		
DESIGN UNITS		☒		☐
WEIGHT 2,3 kg / 5 LB MAX				


[illegible]

AC SOLENOID VOLTAGE DEVICES



DIAGRAMS SHOWN WITH KEY INSERTED AND LOCKED



THIRD ANGLE PROJECTION			
			
SCALE		NTS	
DO NOT SCALE PRINT			
TOLERANCES			
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE :			
DIM. mm		TOL. mm / μ s	
NO PLACES	1.0	0.1 / 0.01	0.8 / 0.03
ONE PLACE	1.1	0.4 / 0.016	0.38 / 0.01
TWO PLACES	1.2	0.15 / 0.006	0.13 / 0.002
THREE PLACES	1.3		
ANGLES			
SI METRIC		US CUSTOMARY	
DESIGN UNITS 			
WEIGHT 2.3 kg / 5 lb MAX			

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CATALOG LISTING

MICRO SWITCH
a Honeywell Division

SWITCH - DOOR INTERLOCK

GK SERIES CHART 4

ANSI Y14.5M-1982 APPLIES

FED. MFG. CODE 91929

PTC/CAD 3D
DRAWN

RS 17DEC04
CHECK

AK

17DEC04
CHECK

MBH 10NOV11
PR

0083578
R

31MAY10
PRS

0065737
P

04FEB09
SSK

0047583
N

REVISIONS

54
ISSUE

CMH

10NOV11
CHECK


RELEASE NO.

PAGE 16 OF 16



CATALOG LISTING

GK SERIES CHART 4

MODIFICATION CODE: F04



SWITCH DIAGRAM STATE
IS CLOSED AND LOCKED



300V 7A
BRAD-HARRISON PART NO. 3R1006A21F010
OR EQUIVALENT

THIRD ANGLE PROJECTION

SCALE NTS

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE :

	DIM.	TOL.	DIM.	TOL.
	mm	mm / in	in	mm / in
NO PLACES	X	1 / .04	X	0.8 / .03
ONE PLACE	X	0.17 / .016	X	0.38 / .015
TWO PLACES	X	0.15 / .006	X	0.13 / .005
THREE PLACES				
ANGLES				

SI METRIC US CUSTOMARY

DESIGN UNITS

WEIGHT 2,3 kg / 5 LB MAX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Honeywell:

[GKFE16LXA2](#) [GKFE16LXA6](#) [GKLA2K1A2-F04](#) [GKLA2K1A2-F04-C](#) [GKLA2K2A2-F04-C](#) [GKLA3J1A2-F03-C](#)
[GKLA40F1C2-F05-C](#) [GKRA2K1A2-F03](#) [GKRA2K1A2-F04-C](#) [GKRA3K1A2-F03-C](#) [GKFE3P7T4](#) [GKGE3LXB4](#)
[GKLE44P7S4](#) [GKLG44LXS2](#) [GKLG46L7S2](#) [GKLA14L9A2-FW](#) [GKRG46MXA2-F21](#) [GKLE44L6S4](#) [GKLG6L6A2](#)
[GKRA14L6A2-FW](#) [GKLE46L9A4](#) [GKLG16L6A2](#) [GKLE46L7A2](#) [GKLE44L7T4](#) [GKLE36PXA2-F22](#) [GKRA15M6A4-FW](#)
[GKLE44L6A2](#) [GKLE44PXT2](#) [GKFG14LXA2](#) [GKLE44L9A4](#) [GKLG16L7A2](#) [GKLE46L9A2](#) [GKLE44LXS4](#)
[GKLE44P7T4](#) [GKRA14P9A2-FW](#) [GKLG16L6S2](#) [GKLE46L7S4](#) [GKLA15L6A2-FW](#) [GKLA15M6A2-FW](#) [GKLG16L7S2](#)
[GKRA15P9A2-FW](#) [GKLE44LXA2](#) [GKLG46L7A2](#) [GKLA15M9A2-FW](#) [GKLF46PXB2](#) [GKRG16L6A2](#) [GKLE44P6A4](#)
[GKLA14L6A2-FW](#) [GKLG46PXA2-F20](#) [GKLA15L9A2-FW](#) [GKLA15P6A2-FW](#) [GKLA46L6A4](#) [GKLE46P7A4](#)
[GKLG44PXA2](#) [GKLA14M9A2-FW](#) [GKRA15M6A2-FW](#) [GKLA2PXA2-F04](#) [GKRA15L6A2-FW](#) [GKLE44L7A2](#)
[GKLE44LXS2](#) [GKLE46LXA2](#) [GKLA15P6A4-FW](#) [GKLG46P6A2](#) [GKLF44LXS2](#) [GKLD44L6A2](#) [GKLE44L9A2](#)