




LOC	DIST	REVISIONS					
AD	00	P	THR	DESCRIPTION	DATE	OWN	APPD
		U		REV PER 063C-0010-03	09JAN03	MB	JO



5.3	3.4	12.1	106.68	4.200	99.06	3.900	109.22	14.300	80	4	-147	102	-0
50.80	12.000	104.16	4.100	96.52	3.800	106.68	14.200	78	3	-147	102	-8	
50.80	2.000	101.60	4.000	93.98	3.700	104.16	4.100	76	3	-147	102	-8	
48.26	1.900	99.06	3.900	91.44	3.600	101.60	4.000	74	3	-147	102	-7	
48.26	1.900	96.52	3.800	88.90	3.500	99.06	3.900	72	3	-147	102	-6	
45.72	1.800	93.98	3.700	86.36	3.400	96.52	3.800	70	3	-147	102	-5	
$\wedge$	88.90	3.500	83.82	3.300	91.44	3.600	68	3	-147	102	-4		
$\wedge$	86.36	3.400	81.28	3.200	88.90	3.500	66	3	-147	102	-3		
$\wedge$	83.82	3.300	78.74	3.100	86.36	3.400	64	3	-147	102	-2		
$\wedge$	81.28	3.200	76.20	3.000	83.82	3.300	62	3	-147	102	-1		
$\wedge$	78.74	3.100	73.66	2.900	81.28	3.200	60	3	-147	102	-0		
$\wedge$	76.20	3.000	71.12	2.800	78.74	3.100	58	2	-147	102	-9		
$\wedge$	73.66	2.900	68.58	2.700	76.20	3.000	56	2	-147	102	-8		
$\wedge$	71.12	2.800	66.04	2.600	73.66	2.900	54	2	-147	102	-7		
$\wedge$	68.58	2.700	63.50	2.500	71.12	2.800	52	2	-147	102	-6		
$\wedge$	66.04	2.600	60.96	2.400	68.58	2.700	50	2	-147	102	-5		
$\wedge$	63.50	2.500	58.42	2.300	66.04	2.600	48	2	-147	102	-4		
$\wedge$	60.96	2.400	55.88	2.200	63.50	2.500	46	2	-147	102	-3		
$\wedge$	58.42	2.300	53.34	2.100	60.96	2.400	44	2	-147	102	-2		
$\wedge$	55.88	2.200	50.80	2.000	58.42	2.300	42	2	-147	102	-1		
$\wedge$	53.34	2.100	48.26	1.900	55.88	2.200	40	2	-147	102	-0		
$\wedge$	50.80	2.000	45.72	1.800	53.34	2.100	38	1	-147	102	-9		
$\wedge$	48.26	1.900	43.18	1.700	50.80	2.000	36	1	-147	102	-8		
$\wedge$	45.72	1.800	40.64	1.600	48.26	1.900	34	1	-147	102	-7		
$\wedge$	43.18	1.700	38.10	1.500	45.72	1.800	32	1	-147	102	-6		
$\wedge$	40.64	1.600	35.56	1.400	43.18	1.700	30	1	-147	102	-5		
$\wedge$	38.10	1.500	33.02	1.300	40.64	1.600	28	1	-147	102	-4		
$\wedge$	35.56	1.400	30.48	1.200	38.10	1.500	26	1	-147	102	-3		
$\wedge$	33.02	1.300	27.94	1.100	35.56	1.400	24	1	-147	102	-2		
$\wedge$	30.48	1.200	25.40	1.000	33.02	1.300	22	1	-147	102	-1		
$\wedge$	27.94	1.100	22.86	1.000	30.48	1.200	20	1	-147	102	-0		
$\wedge$	25.40	1.000	20.32	1.000	27.94	1.100	18	1	-147	102	-9		
$\wedge$	22.86	1.000	17.78	1.000	25.40	1.000	16	1	-147	102	-8		
$\wedge$	20.32	1.000	15.24	1.000	22.86	1.000	14	1	-147	102	-7		
$\wedge$	17.78	1.000	12.70	1.000	20.32	1.000	12	1	-147	102	-6		
$\wedge$	15.24	1.000	10.16	1.000	17.78	1.000	10	1	-147	102	-5		
$\wedge$	12.70	1.000	7.62	1.000	15.24	1.000	8	1	-147	102	-4		
$\wedge$	10.16	1.000	5.08	1.000	12.70	1.000	6	1	-147	102	-3		
$\wedge$	7.62	1.000	2.54	1.000	10.16	1.000	4	1	-147	102	-2		
$\wedge$	5.08	1.000	-	7.62	1.000	2	6	-147	102	-1			

△1	HOUSING: FLAME RETARDANT, GLASS FILLED, THERMOPLASTIC, COLOR: BLACK CONTACT: PHOSPHOR BRONZE VACUUM COVER: STAINLESS STEEL	△△POINT-OF-MEASUREMENT DIMENSION FOR PLATING THICKNESS (INSIDE CONTACT BEAM).
△2	CONTACT: DUPLEX PLATED 0.25mm[.000010] MIN GOLD IN CONTACT AREA, 3.81-7.62mm[.000150-.000300] BRIGHT TIN-LEAD ON LEADS ALL OVER 1.27mm[.000050] NICKEL	△8POINT-OF-CONTACT DIMENSION.
△9	CONTACT AREA, 3.81-7.62mm[.000150-.000300] BRIGHT TIN-LEAD ON LEADS ALL OVER 1.27mm[.000050] NICKEL	△9.55[.217] MIN TARGET AREA FOR VACUUM PICK UP. COVER TO BE REMOVED AFTER SOLDERING.

OBSOLETE

3 THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY
NOT TO CONTACT LOCATIONS

4 TRADEMARK, AGENCY LOGO, AND DATE CODE ARE MOLDED IN
OR MARKED. THE ORDER AND LOCATION IS OPTIONAL.

5 TOLERANCE IS NON-CUMULATIVE.

10 NO CENTER HOLD DOWN.

11 HOLES Ø1.125±.025/.043±.0010] DRILL SIZE
[0.03-0.08/.001-- .003] COPPER PLATING, 0.0007/.0003]
MIN Ø0.40 THIN LAYER Ø0.94-1.09/.037-.043] AFTER
PLATING, 0.025/.010] ANNUAL RING BOTH SIDES.

AMP 1471-9 REV 31MAR2000

A

