



LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				F	REV & REDRAWN PER 0720-0061-93	4-15-93	10 DAP

METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	 E13288 Listed
16-14 AWG SOLID OR STRANDED	NOT APPLICABLE
 LR7189 Certified	MILITARY P/N AND CLASS
NOT APPLICABLE	NOT APPLICABLE

- 1 STAMP AMP 16-14 APPROX AS SHOWN
- 2 WIRE BARREL COLOR CODED ORANGE
TO DENOTE NICKEL MATERIAL



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			322339		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS			PART NO		
FOR APPLICATION TOOLING INFORMATION			AMP Incorporated Harrisburg, PA 17105-3608		
FOR ORDER ENTRY			NAME TERMINAL, RING TONGUE, HIGH TEMPERATURE, STRATO-THERM™		
PRODUCT INFORMATION CENTER 1-800-522-6752			SIZE 00779		
TOOLING ASSISTANCE CENTER 1-800-722-1111			DRAWING NO C=322339		
1-800-526-5142			SCALE 8:1		
MAX RECOMMENDED OPERATING TEMPERATURE: 649°C MAX			SHEET 1 OF 1		
VOLTAGE RATING: NOT APPLICABLE			CUSTOMER DRAWING		
WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm² [2,050-5,180] CIR MILS SOLID OR STRANDED					
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.					
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -					
MATERIAL NICKEL PER ASTM B-162 ANNEALED					
FINISH -					
DR 4-15-93 TA BRINKMAN					
CHK 4-15-93 DA PATTERSON					
APPD 4-15-93 DE MILLER					
APPD 4-15-93 JL MECKLEY					
PRODUCT SPEC -					
APPLICATION SPEC -					
WEIGHT -					