

PRODUCT NUMBER

20020108-XXXXXXLF

20020108-□□□□A0□LF

PITCH

C : 3.50 mm
D : 3.81 mm
G : 5.00 mm
H : 5.08 mm

POLES

02: 2 POLES
03: 3 POLES
04: 4 POLES

24: 24 POLES

LF : DENOTED ROHS COMPATIBLE

1 : STANDARD PRODUCT
W/ BOX PACKING

HOUSING CODE

PROPERTY TABLE					
FCI SERIES NAME		06-350	06-381	06-500	06-508
PITCH (mm)		3.50	3.81	5.00	5.08
VOLTAGE RATING (VAC)		300	300	300	300
CURRENT RATING (A)	cULus	10	10	12	12
	VDE	10.5	10.5	NA	NA
WITHSTANDING VOLTAGE (kV)	cULus	1.6	1.6	1.6	1.6
	VDE	2.5	2.5	NA	NA
OPERATING TEMP. (°C)		-40~+115	-40~+115	-40~+115	-40~+115
SOLDERING TEMP. (°C)		250±10 (5 sec.)	250±10 (5 sec.)	250±10 (5 sec.)	250±10 (5 sec.)
POLES AVAILABLE		02~24	02~24	02~24	02~24
SAFETY CERTIFICATE					

CODE	COLOR	AVAILABILITY
1	GREEN(RAL 6018/T)	STANDARD
2	BLACK	ON REQUEST ONLY
3	GREY(RAL 7004/P)	ON REQUEST ONLY
4	BLUE(RAL 5015/A)	ON REQUEST ONLY

NOTES:

1. MATERIALS

1-1 HOUSING: THERMALPLASTIC RESIN, UL 94V-0 RATED.

1-2 TERMINAL: COPPER ALLOY, TIN PLATED.

2. PRODUCT SPECIFICATION REFER TO FCI GS-12-625.

3. BOXED PACKAGING,

DETAILED PRODUCT PACKING SPECIFICATION REFER TO FCI GS-14-1394.


4. FCI, SAFETY CERTIFICATE LOGO AND SERIES NAME TO BE SHOWN ON PRODUCT SURFACE.

5. THE PRODUCTS WHERE THE PART NUMBER END IN "LF" MEET THE EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

6. RECOMENDED SOLDERING PROCESS BY WAVE SOLDER.

mat'l. code				surface	tolerance	projection	product family	
				ASME Y14.5	ASME Y14.5		TERMINAL BLOCK	
ltr	ecn no	dr	date	angles	tolerances unless otherwise specified		title	
A	T10-0062	WL	050710		X.±0.5[.020]	MM	TERMINAL BLOCK	
B	T10-0155	WL	093010		X.X±0.3[.012]	INCH	PLUGGABLE, SOCKET, SIGNAL, STRAIGHT	
C	T10-0187	WL	121410	X'±1"	X.XX±0.1[.004]	scale	W/FLANGE	
D	T11-0019	WL	040611	dr	WENDY CHEN	042310	sheet 1 of 5	
E	T-004860	WL	080411	enr	JASON HSU	042310	20020108	
				chr	GARY HSIEH	042310	A4	
				appd	JOSEPH HSIA	042310	type	
sheet index		revision	sheet	E	E	E	CUSTOMER Drawing	
				1	2	3		



PRODUCT NUMBER	SERIES NAME	PITCH
20020108-CXXXXXL	06-350	3.50 mm




N= Number of poles

Dim A	$(N-1)*3.5[.138]+13.8[.543]$
Dim B	$(N-1)*3.5[.138]$
Dim C	$(N-1)*3.5[.138]+8.6[.339]$
Dim D	$(N-1)*3.5[.138]$


Poles	Tolerance
2p-6p	$\pm 0.15[.006]$
7p-12p	$\pm 0.20[.008]$
13p-16p	$\pm 0.25[.010]$
17p-24p	$\pm 0.30[.012]$



SECTION P-P



SECTION Q-Q



RECOMMENDED P.C.B LAYOUT





mat'l. code	surface ASME Y14.5	tolerance ASME Y14.5	projection MM INCH	product family TERMINAL BLOCK
ltr	ecn no	dr	date	title TERMINAL BLOCK PLUGGABLE, SOCKET, SIGNAL, STRAIGHT W/FLANGE
E				dwg no 20020108
				sheet 2 of 5
				size A4
				type CUSTOMER Drawing
sheet index	revision	sheet		

N= Number of poles


PRODUCT NUMBER	SERIES NAME	PITCH
20020108-DXXXXXXLF	06-381	3.81 mm

Dim A	$(N-1) \cdot 3.81[.150] + 14.2[.559]$
Dim B	$(N-1) \cdot 3.81[.150]$
Dim C	$(N-1) \cdot 3.81[.150] + 9.0[.354]$
Dim D	$(N-1) \cdot 3.81[.150]$

Poles	Tolerance
2p-6p	$\pm 0.15[.006]$
7p-12p	$\pm 0.20[.008]$
13p-16p	$\pm 0.25[.010]$
17p-24p	$\pm 0.30[.012]$








SECTION P-P



SECTION Q-Q

mat'l. code				surface ASME Y14.5✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK					
ltr		ecn no		dr		date		tolerances unless otherwise specified		title TERMINAL BLOCK PLUGGABLE, SOCKET, SIGNAL, STRAIGHT W/FLANGE dwg no sheet 3 of 5 size 20020108 A4 type CUSTOMER Drawing					
E								angles lineal X.±0.5[.020] X.X±0.3[.012] X'±1" X.XX±0.1[.004]						MM [INCH]	
								scale						FCI 	
								dr WENDY CHEN 042310 enr JASON HSU 042310 chr GARY HSIEH 042310 appd JOSEPH HSIA 042310							
sheet index		revision sheet													

PRODUCT NUMBER	SERIES NAME	PITCH
20020108-GXXXXXXLF	06-500	5.00 mm





N= Number of poles

Dim A	(N+2)*5.0
Dim B	(N-1)*5.0
Dim C	(N+1)*5.0
Dim D	(N-1)*5.0




Poles	Tolerance
2P-6P	±0.15
7P-12P	±0.20
13P-18P	±0.30
19P-24P	±0.40

mat'l. code	surface ASME Y14.5	tolerance ASME Y14.5	projection	product family
ltr	ecn no	dr	date	TERMINAL BLOCK
E				title
				TERMINAL BLOCK
				PLUGGABLE, SOCKET, SIGNAL, STRAIGHT
				W/FLANGE
				dwg no
				20020108
				sheet 4 of 5
				size
				A4
				type
				CUSTOMER Drawing
sheet index	revision	sheet		

PRODUCT NUMBER	SERIES NAME	PITCH
20020108-HXXXXXXLF	06-508	5.08 mm



RECOMMENDED P.C.B LAYOUT

Ø1.60 Typ.
Ø.063

N= NUMBER OF POLES

Dim A	(N+2)*5.08
Dim B	(N-1)*5.08
Dim C	(N+1)*5.08
Dim D	(N-1)*5.08

Poles	Tolerance
2P-6P	±0.15
7P-12P	±0.20
13P-18P	±0.30
19P-24P	±0.40

mat'l. code	surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM INCH	product family TERMINAL BLOCK
ltr	ecn no	dr	date	title TERMINAL BLOCK PLUGGABLE, SOCKET, SIGNAL, STRAIGHT W/FLANGE
E				dwg no 20020108
				sheet 5 of 5
				size A4
				type CUSTOMER Drawing
sheet index	revision	sheet		