




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		J1	REVISED PER ECO-11-004917	11MAR11	RK	HMR

1. PARTS COMPLY WITH AMP SOLDERABILITY SPEC 109-11-3.
2. PARTS CAPABLE OF BEING APPLIED BY AMPOMATER.
3. 0.00508 [.000200] MIN BRIGHT TIN-LEAD.
4. WIRE RANGE: 0.12 - 0.4 mm² (26 - 22 AWG).
5. INSULATION RANGE: 1.02 - 1.78 [.040 - .070] DIA.
6. DIMENSIONS IN BRACKETS ARE IN INCHES.
7. 0.00508 [.000200] MIN BRIGHT TIN.



7	0.20[.008] PH BRZ	3-640663-1
3	0.20[.008] PH BRZ	640663-1
FINISH	MATERIAL	PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN S. CARPENTER 21AUG2003
	0 PLC ±	CHK J. ELLIS 21AUG2003
	1 PLC ±	APVD J. ELLIS 21AUG2003
	2 PLC ±	PRODUCT SPEC
	3 PLC ± 0.13 [.005]	APPLICATION SPEC
	4 PLC ±	114-1016
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT
CUSTOMER DRAWING		SCALE 10:1
		SHEET 1 OF 1
		REV J1

A/C BUSINESS GROUP 3323 177-34 RALPH VESTAL