




Continental Device India Limited

An ISO/TS 16949, ISO 9001 and ISO 14001 Certified Company



SILICON GENERAL PURPOSE SWITCHING DIODES AXIAL LEAD

CS 1553
CS 1555
DO-35



General Purpose, Industrial Applications

Hermetically Sealed Glass With A Stud On Either Side Of The Chip Provides Excellent Stability.


ABSOLUTE MAXIMUM RATINGS(TA=25 deg C Unless Otherwise Specified)

DESCRIPTION	SYMBOL	CS1553	CS1555	UNIT
Peak Repetitive Reverse Voltage	VRRM	70	35	V
Reverse Voltage (Continuous)	VR	60	30	V
Average Forward Current	IF(AV)		100	mA
Repetitive Peak Forward Current	IFRM		300	mA
Non Repetitive Peak Surge Current (1us) (1 sec)	IFSM		2000	mA
	IFSM		500	mA
Power Dissipation	PTA		300	mW
Operating & Storage Junction Temperature Range	TJ, Tstg		-65 to +200	deg C

ELECTRICAL CHARACTERISTICS (Ta=25 deg C Unless Specified)

DESCRIPTION	SYMBOL	TEST CONDITION	MIN	TYP	MAX	UNIT
Forward Voltage	VF	IF=100mA	-	-	1.0	V
Reverse Current	IR	VR=60V	CS 1553	-	500	nA
		VR=30V	CS 1555	-	500	nA
Reverse Breakdown Voltage	VBR	IR=100uA	CS 1553	70	-	V
			CS 1555	35	-	V
Diode Capacitance	Cd	VR=0V, f=1MHz	-	-	3.5	pF


DO-35 Glass Axial Package



NOTES
 1. Cathode is marked by Band.
 2. All dimensions are in mm.

DIM	MIN	MAX
A	25.40	—
B	3.03	4.44
C	0.46	0.56
D	1.52	2.29


DO-35, 52mm Taping Specification



All dimensions in mm.

52 mm Taping Specification

1. T & A indicates Axial Tape & Ammo packing (52 mm Tape Spacing).
2. 300 mm (min) leader tape on every spool.
3. No. of empty places allowed 0.25% without consecutive empty places.
4. Ends of leads shall preferably not protrude beyond the tapes.
5. Components shall be held sufficiently in the tape or tapes so that they can not come free in normal handling.



On request also available in 26 mm Tape and Ammo Pack

Packing Detail

PACKAGE	STANDARD PACK		INNER CARTON BOX		OUTER CARTON BOX		
	Details	Net Weight/Qty	Size	Qty	Size	Qty	Gr Wt
DO-35 T&A	5K/ammo box	0.88 kg/5K pcs	10" x 3.5" x 3.5"	5.0K	12.7" x 12.7" x 20"	125.0K	25 kgs

