



Datasheet for part number CA3102R28-22PB

Our Catalog Part Number: CA3102R28-22P-B	
Brand: Cannon	Product Category: Circular Product Line: CA Bayonet Series: CA BAYONET

Product Datasheet	
Bayonet	Connector with bayonet coupling
Shell Style	Box mounting receptacle
Gender	Pin
Shell Size	28
Contact Arrangement	28-22
Number of contacts	3 contacts size 4, 3 contacts size 16
Contact Type	Solder Cup
Contact Plating	Hard silver
Shielding	no
Contact Rating at +20 °C (68 °F) (Size 15/15S/16/16S)	22 A
Contact Rating at +20 °C (68 °F) (Size 160/4)	135 A
Contact Resistance (Size 15/15S/16/16S)	6 mΩ
Contact Resistance (Size 160/4)	0,5 mΩ
Operating Voltage	In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41.
Insulator Resistance	Acc. To VG95319, part 2, test no. 5.12 and VG95210, part 32, test conditions B, standard insulator material > 1000 MΩ
Test Voltage	2500 Vrms
Air and Creepage Paths (Min)	2,8 mm
Ambient Temperature	Standard insulator material -55°/+125°C (-67/257°F)
Safety Provisions	IP67 acc. to DIN 40 050 (1 bar pressure after 12 hrs)
Salt Spray Resistance	500 hours salt spray resistant
Mating Cycles	500 min
Sep. Force per Contact (Size 15/15S/16/16S)	1,0 N
Sep. Force per Contact (Size 160/4)	4,0 N
Gage	For infos on Gage please see catalog VG95234, part 1
Coupling Torque	Closing: 17 Nm max / Opening: 0,92 Nm min
Contact Retention (Size 15/15S/16/16S)	35 N
Contact Retention (Size 160/4)	90 N
Shell Material	Aluminium alloy
Shell Plating	Olive drab chromate over cadmium plating
Insulator and Gromet Material	CR-Elastomere
Contact Material	Copper alloy
Harnessing Info: Contact Cross-Section	See assembly instruction
Harnessing Info: Insulator Diameter	See assembly instruction
Wire Stripping (Size 15/15S/16/16S)	6,2 mm
Wire Stripping (Size 160/4)	11,8 mm

Specifications and dimensions subject to change.



Datasheet for part number CA3102R28-22PB

Our Catalog Part Number: CA3102R28-22P-B	
Brand: Cannon	Product Category: Circular Product Line: CA Bayonet Series: CA BAYONET

Product Datasheet	
General Info	<i>All tests in accordance with VG95319 and/or if applicable with VG95210</i>