



HSX2-180-UPA

0.6 m | 2 ft High Performance, Super High XPD Parabolic Shielded Antenna, dual-polarized, 17.700–19.700 GHz, UG-595/U modified, gray antenna, molded white radome with flash, standard pack—one-piece reflector

General Specifications

Antenna Type	HSX - High Performance, Super High XPD Parabolic Shielded Antenna, dual-polarized
Diameter, nominal	0.6 m 2 ft
Packing	Standard pack
Radome Color	White
Radome Material	Molded
Reflector Construction	One-piece reflector
Antenna Input	UG-595/U Modified
Antenna Color	Gray
Antenna Type	HSX - High Performance, Super High XPD Parabolic Shielded Antenna, dual-polarized
Diameter, nominal	0.6 m 2 ft
Flash Included	Yes
Polarization	Dual

Electrical Specifications

Operating Frequency Band	17.700 – 19.700 GHz
Beamwidth, Horizontal	1.9 °
Beamwidth, Vertical	1.9 °
Cross Polarization Discrimination (XPD)	36 dB
Electrical Compliance	ETSI Class 2 US FCC Part 101A US FCC Part 74A US FCC Part 78A
Front-to-Back Ratio	64 dB
Gain, Low Band	38.0 dBi
Gain, Mid Band	38.4 dBi
Gain, Top Band	38.8 dBi
Operating Frequency Band	17.700 – 19.700 GHz
Radiation Pattern Envelope Reference (RPE)	2052 2053
Return Loss	24.0 dB
VSWR	1.14

Mechanical Specifications

Fine Azimuth Adjustment	±10°
Fine Elevation Adjustment	±25°
Mounting Pipe Diameter	115 mm 4.5 in

HSX2-180-UPA



Net Weight	11 kg 24 lb
Net Weight	31 kg 68 lb
Side Struts, Included	0
Wind Velocity Operational	110 km/h 68 mph
Wind Velocity Survival Rating	200 km/h 124 mph

Wind Forces At Wind Velocity Survival Rating


Angle α for MT Max	110 °
Axial Force (FA)	740 N 166 lbf
Side Force (FS)	460 N 103 lbf
Twisting Moment (MT)	264 N•m
Weight with 1/2 in (12 mm) Radial Ice	39 kg 86 lb
Zcg with 1/2 in (12 mm) Radial Ice	215 mm 8 in
Zcg without Ice	175 mm 7 in

HSX2-180-UPA

POWERED BY



Wind Forces At Wind Velocity Survival Rating Image



Packed Dimensions


Gross Weight, Packed Antenna	15.0 kg		33.1 lb
Height	56.0 cm		22.0 in
Length	70.0 cm		27.6 in
Volume	0.3 m ³		
Width	70.0 cm		27.6 in

HSX2-180-UPA

POWERED BY



Antenna Dimensions And Mounting Information



ANTENNA DIMENSIONS			
All dimensions in mm (inches)			
A	638 (25.1)	D	143 (5.6)
B	310 (12.2)	E	534 (21.0)
C	72 (2.8)		

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Axial Force (FA)	Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
Cross Polarization Discrimination (XPD)	The difference between the peak of the co-polarized main beam and the maximum cross-polarized signal over an angle twice the 3 dB beamwidth of the co-polarized main beam.
Front-to-Back Ratio	Denotes highest radiation relative to the main beam, at $180^\circ \pm 40^\circ$, across the band. Production antennas do not exceed rated values by more than 2 dB unless stated otherwise.
Gain, Mid Band	For a given frequency band, gain is primarily a function of antenna size. The gain of Andrew antennas is determined by either gain by comparison or by computer integration of the measured antenna patterns.

HSX2-180-UPA

POWERED BY



Operating Frequency Band	Bands correspond with CCIR recommendations or common allocations used throughout the world. Other ranges can be accommodated on special order.
Packing	Andrew standard packing is suitable for export. Antennas are shipped as standard in totally recyclable cardboard or wire-bound crates (dependent on product). For your convenience, Andrew offers heavy duty export packing options.
Radiation Pattern Envelope Reference (RPE)	Radiation patterns determine an antenna's ability to discriminate against unwanted signals under conditions of radio congestion. Radiation patterns are dependent on antenna series, size, and frequency.
Return Loss	The figure that indicates the proportion of radio waves incident upon the antenna that are rejected as a ratio of those that are accepted.
Side Force (FS)	Maximum side force exerted on the mounting pipe as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
Twisting Moment (MT)	Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
VSWR	Maximum; is the guaranteed Peak Voltage-Standing-Wave-Ratio within the operating band.
Wind Velocity Operational	The wind speed where the antenna deflection is equal to or less than 0.1 degrees. In the case of ValuLine antennas, it is defined as a maximum deflection of 0.3 x the 3 dB beam width of the antenna.
Wind Velocity Survival Rating	The maximum wind speed the antenna, including mounts and radomes, where applicable, will withstand without permanent deformation. Realignment may be required. This wind speed is applicable to antenna with the specified amount of radial ice.