

Customer Information Sheet

DRAWING No.: D8864-42

SHEET 2 OF 2



IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

**SPECIFICATION:****MATERIAL:**

MOULDING = GLASS FILLED PCT UL94V-0, BLACK

CONTACT SHELL = BRASS

CONTACT CLIP = BERYLLIUM COPPER

FINISH:

CONTACT SHELL = 5µ 100% TIN

CONTACT CLIP = GOLD FLASH

ELECTRICAL:

CURRENT RATING = 1A

VOLTAGE RATING = 100V AC, 150V DC

CONTACT RESISTANCE = 10 MILLIOHMS MAX

INSULATION RESISTANCE = 10,000 MEGOHMS MIN

DIELECTRIC STRENGTH = 700V AC

ENVIRONMENTAL:

TEMPERATURE RANGE = -55°C TO +125°C

MECHANICAL:

INSERTION FORCE (Ø0.43mm GAUGE) = 3.4N MAX

WITHDRAWAL FORCE (Ø0.43mm GAUGE) = 0.6N MIN

NOTES:

1. RECOMMENDED HOLE SIZE = Ø0.80mm.
2. RECOMMENDED MATING PIN SIZE = Ø0.56-0.40mm
OR 0.25mm x 0.45mm.
3. RECOMMENDED PC BOARD THICKNESS = 1.4 TO 2.0mm
4. MAXIMUM CONTACT DEPTH = 2.20mm.
MAXIMUM MATING PIN LENGTH = 3.55mm.

CP	2	15.01.10	10640
NAME	ISS.	DATE	C/NOTE
APPROVED: C.PENROSE			
CHECKED: R.ADDE			
DRAWN: W.J.BOURNE			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm

ANGLES = ±5°

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²**TITLE:**

1.778mm (0.07") PITCH 64-WAY
DIL IC SOCKET (SHRINK-DIP)

DRAWING NUMBER:

D8864-42

SHT

2 OF 2